

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763705

Luminaire Tested: LD6D25D010-EU6DR6520359050-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P763705
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D25D010-EU6DR6520359050-6LBCSSQMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2675.0 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P763705
CATALOG NUMBER: LD6D25D010-EU6DR6520359050-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P763705

CATALOG NUMBER: LD6D25D010-EU6DR6520359050-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141857
5°	141496
10°	141377
15°	137018
20°	124733
25°	108700
30°	90409
35°	71633
40°	51699
45°	32667
50°	17027
55°	9052
60°	4754
65°	2612
70°	1093
75°	1196
80°	841
85°	737

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 32667 cd/sqm



TEST NUMBER: P763705

CATALOG NUMBER: LD6D25D010-EU6DR6520359050-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	229.7	8.6
10°-20°	629.0	23.5
20°-30°	768.8	28.7
30°-40°	623.8	23.3
40°-50°	310.8	11.6
50°-60°	86.7	3.2
60°-70°	19.7	0.7
70°-80°	5.1	0.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1627.5	60.8
0°-40°	2251.3	84.2
0°-60°	2648.8	99.0
0°-90°	2675.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2675.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2429	
5°	2414	230
15°	2266	629
25°	1687	769
35°	1005	624
45°	396	311
55°	89	87
65°	19	20
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P763705

CATALOG NUMBER: LD6D25D010-EU6DR6520359050-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2428.9
2.5°	2427.0
5°	2413.5
7.5°	2405.6
10°	2383.9
12.5°	2339.6
15°	2266.1
17.5°	2151.1
20°	2006.9
22.5°	1851.3
25°	1686.8
27.5°	1510.8
30°	1340.6
32.5°	1172.5
35°	1004.7
37.5°	837.3
40°	678.1
42.5°	528.9
45°	395.5
47.5°	275.5
50°	187.4
52.5°	129.2
55°	88.9
57.5°	60.0
60°	40.7
62.5°	28.2
65°	18.9
67.5°	9.6
70°	6.4
72.5°	6.1
75°	5.3
77.5°	3.6
80°	2.5
82.5°	1.8
85°	1.1
87.5°	0.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)