

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P758535

Luminaire Tested: LD6D05D010-EU6DR550210IC9024-6LBSQW1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P758535  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D05D010-EU6DR550210IC9024-6LBSQW1MW  
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 55° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 537.2 lumens  
Efficiency: N/A  
Efficacy: 71.6 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P758535

CATALOG NUMBER: LD6D05D010-EU6DR550210IC9024-6LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P758535  
 CATALOG NUMBER: LD6D05D010-EU6DR550210IC9024-6LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			94	
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87			87	
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			81	
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75			75	
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			70	
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65			65	
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61			61	
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			57	
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54			54	
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50			50	

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	65808
5°	63197
10°	62962
15°	61150
20°	54834
25°	45317
30°	34228
35°	24823
40°	15889
45°	7247
50°	2380
55°	1029
60°	437
65°	52
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7247 cd/sqm



TEST NUMBER: P758535

CATALOG NUMBER: LD6D05D010-EU6DR550210IC9024-6LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.8	10.2
10°-20°	149.6	27.9
20°-30°	170.5	31.7
30°-40°	116.1	21.6
40°-50°	40.0	7.4
50°-60°	5.5	1.0
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	375.0	69.8
0°-40°	491.1	91.4
0°-60°	536.7	99.9
0°-90°	537.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	537.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	602	
5°	576	55
15°	541	150
25°	376	171
35°	186	116
45°	47	40
55°	5	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P758535

CATALOG NUMBER: LD6D05D010-EU6DR550210IC9024-6LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	602.3
2.5°	588.5
5°	576.2
7.5°	570.2
10°	567.5
12.5°	558.6
15°	540.6
17.5°	512.2
20°	471.6
22.5°	424.7
25°	375.9
27.5°	325.1
30°	271.3
32.5°	225.8
35°	186.1
37.5°	148.3
40°	111.4
42.5°	77.2
45°	46.9
47.5°	25.3
50°	14.0
52.5°	8.3
55°	5.4
57.5°	3.4
60°	2.0
62.5°	0.9
65°	0.2
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)