

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769357

Luminaire Tested: LD6D60D010-EU6DR7055659027-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P769357
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR7055659027-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4333.3 lumens
Efficiency: N/A
Efficacy: 67.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P769357
CATALOG NUMBER: LD6D60D010-EU6DR7055659027-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P769357

CATALOG NUMBER: LD6D60D010-EU6DR7055659027-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	532307
5°	516485
10°	502098
15°	495512
20°	462696
25°	347599
30°	245729
35°	87046
40°	45770
45°	48750
50°	50484
55°	51432
60°	51746
65°	50647
70°	47791
75°	44284
80°	39325
85°	31967

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 51753 cd/sqm



TEST NUMBER: P769357

CATALOG NUMBER: LD6D60D010-EU6DR7055659027-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	444.2	10.3
10°-20°	1218.4	28.1
20°-30°	1341.8	31.0
30°-40°	512.7	11.8
40°-50°	242.1	5.6
50°-60°	240.7	5.6
60°-70°	192.7	4.4
70°-80°	110.7	2.6
80°-90°	30.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3004.4	69.3
0°-40°	3517.1	81.2
0°-60°	3999.8	92.3
0°-90°	4333.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4333.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4872	
5°	4709	444
15°	4381	1218
25°	2883	1342
35°	653	513
45°	316	242
55°	270	241
65°	196	193
75°	105	111
85°	26	30
90°	0	



TEST NUMBER: P769357

CATALOG NUMBER: LD6D60D010-EU6DR7055659027-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	4871.9
2.5°	4821.0
5°	4709.1
7.5°	4615.8
10°	4525.6
12.5°	4449.2
15°	4380.6
17.5°	4214.7
20°	3979.4
22.5°	3471.9
25°	2883.3
27.5°	2510.0
30°	1947.7
32.5°	1258.1
35°	652.6
37.5°	352.5
40°	320.9
42.5°	318.6
45°	315.5
47.5°	308.5
50°	297.0
52.5°	283.9
55°	270.0
57.5°	254.5
60°	236.8
62.5°	216.8
65°	195.9
67.5°	172.8
70°	149.6
72.5°	126.5
75°	104.9
77.5°	82.5
80°	62.5
82.5°	44.0
85°	25.5
87.5°	10.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)