

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768763

Luminaire Tested: LD6D60D010-EU6DR3055659040-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768763
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR3055659040-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6754.8 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P768763

CATALOG NUMBER: LD6D60D010-EU6DR3055659040-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P768763

CATALOG NUMBER: LD6D60D010-EU6DR3055659040-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1662523	1662523	1662523
5°	1614796	1612914	1614881
10°	1398663	1388799	1398328
15°	912553	907656	903091
20°	453774	470798	453163
25°	228581	257761	223894
30°	91522	99716	79741
35°	42451	40657	34078
40°	18325	20354	17266
45°	12925	16042	13044
50°	4442	11682	4704
55°	2562	4844	2709
60°	1791	2128	1791
65°	1159	1159	1159
70°	716	470	716
75°	0	325	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 16042 cd/sqm



TEST NUMBER: P768763

CATALOG NUMBER: LD6D60D010-EU6DR3055659040-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1909.9	28.3
10°-20°	3076.0	45.5
20°-30°	1329.2	19.7
30°-40°	303.0	4.5
40°-50°	104.0	1.5
50°-60°	25.4	0.4
60°-70°	6.6	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6315.2	93.5
0°-40°	6618.1	98.0
0°-60°	6747.6	99.9
0°-90°	6754.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6754.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	21720	21720	21720	21720	21720	
5°	21016	20996	20992	21035	21017	1912
15°	11516	11377	11454	11417	11396	3084
25°	2706	2809	3052	2737	2651	1296
35°	454	464	435	432	365	308
45°	119	148	148	148	120	85
55°	19	20	36	21	20	19
65°	6	6	6	6	6	6
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P768763

CATALOG NUMBER: LD6D60D010-EU6DR3055659040-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	21720.0	21720.0	21720.0	21720.0	21720.0
2.5°	21576.1	21561.1	21569.7	21580.3	21584.6
5°	21016.2	20996.0	20991.7	21035.4	21017.3
7.5°	19886.9	19858.1	19814.4	19913.6	20006.4
10°	17995.2	17963.2	17868.3	17915.2	17990.9
12.5°	15202.3	15098.9	15096.7	15246.0	15225.8
15°	11515.8	11377.2	11454.0	11416.7	11396.4
17.5°	7744.1	7690.7	7793.1	7762.2	7628.9
20°	5570.8	5584.6	5779.8	5681.7	5563.3
22.5°	4065.0	4115.2	4346.6	4093.8	4001.1
25°	2706.5	2808.8	3052.0	2737.4	2651.0
27.5°	1664.6	1711.5	1957.9	1643.3	1596.4
30°	1035.5	1012.0	1128.2	968.3	902.2
32.5°	679.3	649.4	686.7	616.4	563.0
35°	454.3	463.9	435.1	431.9	364.7
37.5°	283.7	326.3	287.9	307.1	234.6
40°	183.4	236.7	203.7	225.0	172.8
42.5°	150.4	182.4	167.4	178.1	153.6
45°	119.4	148.2	148.2	148.2	120.5
47.5°	66.1	99.2	126.9	101.3	70.4
50°	37.3	50.1	98.1	52.3	39.5
52.5°	25.6	28.8	67.2	29.9	26.7
55°	19.2	20.3	36.3	21.3	20.3
57.5°	14.9	16.0	19.2	16.0	14.9
60°	11.7	11.7	13.9	12.8	11.7
62.5°	8.5	8.5	9.6	8.5	8.5
65°	6.4	6.4	6.4	6.4	6.4
67.5°	3.2	4.3	4.3	4.3	4.3
70°	3.2	2.1	2.1	2.1	3.2
72.5°	2.1	1.1	1.1	1.1	1.1
75°	0.0	0.0	1.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)