

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770124

Luminaire Tested: LD6D65D010-EU6DR7055659024-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P770124
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR7055659024-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4230.8 lumens
Efficiency: N/A
Efficacy: 58.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P770124

CATALOG NUMBER: LD6D65D010-EU6DR7055659024-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P770124

CATALOG NUMBER: LD6D65D010-EU6DR7055659024-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	519721
5°	504267
10°	490216
15°	483782
20°	451755
25°	339377
30°	239912
35°	84978
40°	44686
45°	47592
50°	49277
55°	50213
60°	50522
65°	49457
70°	46673
75°	43228
80°	38382
85°	31215

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 50533 cd/sqm



TEST NUMBER: P770124

CATALOG NUMBER: LD6D65D010-EU6DR7055659024-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	433.7	10.3
10°-20°	1189.5	28.1
20°-30°	1310.1	31.0
30°-40°	500.6	11.8
40°-50°	236.3	5.6
50°-60°	235.0	5.6
60°-70°	188.1	4.4
70°-80°	108.1	2.6
80°-90°	29.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2933.3	69.3
0°-40°	3433.8	81.2
0°-60°	3905.1	92.3
0°-90°	4230.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4230.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4757	
5°	4598	434
15°	4277	1190
25°	2815	1310
35°	637	501
45°	308	236
55°	264	235
65°	191	188
75°	102	108
85°	25	29
90°	0	



TEST NUMBER: P770124

CATALOG NUMBER: LD6D65D010-EU6DR7055659024-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4756.7
2.5°	4706.9
5°	4597.7
7.5°	4506.6
10°	4418.5
12.5°	4343.9
15°	4276.9
17.5°	4115.0
20°	3885.3
22.5°	3389.8
25°	2815.1
27.5°	2450.6
30°	1901.6
32.5°	1228.3
35°	637.1
37.5°	344.2
40°	313.3
42.5°	311.0
45°	308.0
47.5°	301.2
50°	289.9
52.5°	277.1
55°	263.6
57.5°	248.5
60°	231.2
62.5°	211.6
65°	191.3
67.5°	168.7
70°	146.1
72.5°	123.5
75°	102.4
77.5°	80.6
80°	61.0
82.5°	42.9
85°	24.9
87.5°	9.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)