

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770426

Luminaire Tested: LD6D70BD010-EU6DR4070959024-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770426
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR4070959024-6LBCSSQMMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6807.7 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P770426
CATALOG NUMBER: LD6D70BD010-EU6DR4070959024-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P770426

CATALOG NUMBER: LD6D70BD010-EU6DR4070959024-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 115 | 112 | 110 | 108 | 112 | 110 | 108 | 107 | 106 | 105 | 103 | 103 | 101 | 100 | 99 | 98 | 97 | 96 | 96 | 96 | 96 |
| 2 | 110 | 106 | 103 | 100 | 108 | 105 | 102 | 99 | 102 | 99 | 97 | 99 | 97 | 95 | 96 | 95 | 93 | 92 | 92 | 92 | 92 |
| 3 | 106 | 101 | 97 | 94 | 104 | 100 | 96 | 93 | 97 | 94 | 92 | 95 | 93 | 90 | 93 | 91 | 89 | 88 | 88 | 88 | 88 |
| 4 | 102 | 97 | 92 | 89 | 101 | 95 | 91 | 88 | 93 | 90 | 87 | 92 | 89 | 86 | 90 | 87 | 85 | 84 | 84 | 84 | 84 |
| 5 | 99 | 92 | 88 | 84 | 97 | 91 | 87 | 84 | 90 | 86 | 83 | 88 | 85 | 83 | 87 | 84 | 82 | 81 | 81 | 81 | 81 |
| 6 | 95 | 88 | 84 | 80 | 94 | 88 | 83 | 80 | 86 | 82 | 80 | 85 | 82 | 79 | 84 | 81 | 79 | 77 | 77 | 77 | 77 |
| 7 | 92 | 85 | 80 | 77 | 91 | 84 | 80 | 77 | 83 | 79 | 76 | 82 | 79 | 76 | 81 | 78 | 76 | 74 | 74 | 74 | 74 |
| 8 | 89 | 82 | 77 | 74 | 88 | 81 | 77 | 74 | 80 | 76 | 73 | 79 | 76 | 73 | 78 | 75 | 73 | 72 | 72 | 72 | 72 |
| 9 | 86 | 79 | 74 | 71 | 85 | 78 | 74 | 71 | 77 | 73 | 71 | 76 | 73 | 70 | 76 | 72 | 70 | 69 | 69 | 69 | 69 |
| 10 | 83 | 76 | 71 | 68 | 82 | 75 | 71 | 68 | 75 | 71 | 68 | 74 | 70 | 68 | 73 | 70 | 68 | 67 | 67 | 67 | 67 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1731794 |
| 5° | 1723372 |
| 10° | 1628969 |
| 15° | 1384822 |
| 20° | 943857 |
| 25° | 393820 |
| 30° | 123829 |
| 35° | 57555 |
| 40° | 31821 |
| 45° | 14587 |
| 50° | 7088 |
| 55° | 3886 |
| 60° | 2032 |
| 65° | 724 |
| 70° | 288 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14587 cd/sqm



TEST NUMBER: P770426

CATALOG NUMBER: LD6D70BD010-EU6DR4070959024-6LBCSSQMMS

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 1467.2 | 21.6 |
| 10°-20° | 3286.9 | 48.3 |
| 20°-30° | 1645.3 | 24.2 |
| 30°-40° | 301.6 | 4.4 |
| 40°-50° | 83.2 | 1.2 |
| 50°-60° | 19.6 | 0.3 |
| 60°-70° | 3.8 | 0.1 |
| 70°-80° | 0.1 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 6399.4 | 94.0 |
| 0°-40° | 6701.1 | 98.4 |
| 0°-60° | 6803.8 | 99.9 |
| 0°-90° | 6807.7 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 6807.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 15850 | |
| 5° | 15713 | ### |
| 15° | 12243 | 3287 |
| 25° | 3267 | 1645 |
| 35° | 432 | 302 |
| 45° | 94 | 83 |
| 55° | 20 | 20 |
| 65° | 3 | 4 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P770426

CATALOG NUMBER: LD6D70BD010-EU6DR4070959024-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|---------|
| 0° | 15850.1 |
| 2.5° | 15826.9 |
| 5° | 15713.0 |
| 7.5° | 15350.0 |
| 10° | 14682.5 |
| 12.5° | 13641.7 |
| 15° | 12242.6 |
| 17.5° | 10423.2 |
| 20° | 8117.6 |
| 22.5° | 5534.3 |
| 25° | 3266.7 |
| 27.5° | 1726.9 |
| 30° | 981.5 |
| 32.5° | 634.3 |
| 35° | 431.5 |
| 37.5° | 308.3 |
| 40° | 223.1 |
| 42.5° | 152.8 |
| 45° | 94.4 |
| 47.5° | 60.2 |
| 50° | 41.7 |
| 52.5° | 29.6 |
| 55° | 20.4 |
| 57.5° | 13.0 |
| 60° | 9.3 |
| 62.5° | 5.6 |
| 65° | 2.8 |
| 67.5° | 1.9 |
| 70° | 0.9 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)