

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772321

Luminaire Tested: LD6D80BD010-EU6DR6070959027-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P772321
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D80BD010-EU6DR6070959027-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7507.6 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P772321
CATALOG NUMBER: LD6D80BD010-EU6DR6070959027-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P772321

CATALOG NUMBER: LD6D80BD010-EU6DR6070959027-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	974202
5°	998159
10°	1010210
15°	962360
20°	848513
25°	686301
30°	464218
35°	232620
40°	37740
45°	36930
50°	37667
55°	38231
60°	39312
65°	40202
70°	41146
75°	41624
80°	40143
85°	33472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 41624 cd/sqm



TEST NUMBER: P772321

CATALOG NUMBER: LD6D80BD010-EU6DR6070959027-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	869.8	11.6
10°-20°	2353.3	31.3
20°-30°	2532.0	33.7
30°-40°	1100.6	14.7
40°-50°	184.8	2.5
50°-60°	179.7	2.4
60°-70°	153.7	2.0
70°-80°	102.8	1.4
80°-90°	30.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5755.1	76.7
0°-40°	6855.7	91.3
0°-60°	7220.3	96.2
0°-90°	7507.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7507.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8916	
5°	9101	870
15°	8508	2353
25°	5693	2532
35°	1744	1101
45°	239	185
55°	201	180
65°	156	154
75°	99	103
85°	27	31
90°	0	



TEST NUMBER: P772321

CATALOG NUMBER: LD6D80BD010-EU6DR6070959027-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	8916.3
2.5°	9166.9
5°	9100.8
7.5°	9121.7
10°	9105.4
12.5°	8917.5
15°	8507.8
17.5°	7957.8
20°	7297.6
22.5°	6590.9
25°	5692.8
27.5°	4553.3
30°	3679.5
32.5°	2835.9
35°	1744.0
37.5°	746.1
40°	264.6
42.5°	243.7
45°	239.0
47.5°	230.9
50°	221.6
52.5°	211.2
55°	200.7
57.5°	190.3
60°	179.9
62.5°	168.3
65°	155.5
67.5°	142.7
70°	128.8
72.5°	113.7
75°	98.6
77.5°	81.2
80°	63.8
82.5°	45.3
85°	26.7
87.5°	9.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)