

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772882

Luminaire Tested: LD6D85BD010-EU6DR4570959035-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P772882
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR4570959035-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10212.3 lumens
Efficiency: N/A
Efficacy: 116.4 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P772882
CATALOG NUMBER: LD6D85BD010-EU6DR4570959035-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P772882

CATALOG NUMBER: LD6D85BD010-EU6DR4570959035-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95	95	
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90	90	
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77	77	
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69	69	
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66	66	
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63	63	
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60	60	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1972200
5°	1916044
10°	1833132
15°	1677700
20°	1330999
25°	830968
30°	457999
35°	205650
40°	80999
45°	38166
50°	18103
55°	9467
60°	4655
65°	1112
70°	447
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 38166 cd/sqm



TEST NUMBER: P772882

CATALOG NUMBER: LD6D85BD010-EU6DR4570959035-6LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1641.4	16.1
10°-20°	4039.8	39.6
20°-30°	3199.1	31.3
30°-40°	1065.3	10.4
40°-50°	211.4	2.1
50°-60°	48.0	0.5
60°-70°	6.9	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8880.3	87.0
0°-40°	9945.7	97.4
0°-60°	10205.1	99.9
0°-90°	10212.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10212.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18050	
5°	17470	###
15°	14832	4040
25°	6893	3199
35°	1542	1065
45°	247	211
55°	50	48
65°	4	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P772882

CATALOG NUMBER: LD6D85BD010-EU6DR4570959035-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

0°	
0°	18050.4
2.5°	17932.5
5°	17469.7
7.5°	17087.8
10°	16522.7
12.5°	15770.3
15°	14831.8
17.5°	13420.6
20°	11447.2
22.5°	9096.2
25°	6892.8
27.5°	5047.1
30°	3630.2
32.5°	2468.9
35°	1541.8
37.5°	914.3
40°	567.9
42.5°	373.4
45°	247.0
47.5°	159.0
50°	106.5
52.5°	71.0
55°	49.7
57.5°	32.7
60°	21.3
62.5°	11.4
65°	4.3
67.5°	1.4
70°	1.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)