

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P683907

Luminaire Tested: **LX6C100D010 EX6C1009040 6LBMH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P683907
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C100D010 EX6C1009040 6LBMH
Description: 6 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBM TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7689.0 lumens
Efficiency: N/A
Efficacy: 67.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 114.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P683907

CATALOG NUMBER: LX6C100D010 EX6C1009040 6LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P683907

CATALOG NUMBER: LX6C100D010 EX6C1009040 6LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92	92	92	92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49	49	49	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	417154
5°	409684
10°	388748
15°	364548
20°	339506
25°	312816
30°	260648
35°	183711
40°	117076
45°	69821
50°	41210
55°	26217
60°	18058
65°	12816
70°	8816
75°	6969
80°	3410
85°	0



TEST NUMBER: P683907

CATALOG NUMBER: LX6C100D010 EX6C1009040 6LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	695.8	9.0
10°-20°	1799.9	23.4
20°-30°	2332.2	30.3
30°-40°	1731.4	22.5
40°-50°	731.0	9.5
50°-60°	259.5	3.4
60°-70°	100.2	1.3
70°-80°	34.7	0.5
80°-90°	4.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4827.8	62.8
0°-40°	6559.3	85.3
0°-60°	7549.7	98.2
0°-90°	7689.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7689.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7610	
5°	7445	696
15°	6423	1800
25°	5172	2332
35°	2745	1731
45°	901	731
55°	274	260
65°	99	100
75°	33	35
85°	0	4
90°	0	



TEST NUMBER: P683907

CATALOG NUMBER: LX6C100D010 EX6C1009040 6LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	7609.5
2.5°	7587.4
5°	7444.8
7.5°	7235.9
10°	6983.6
12.5°	6708.9
15°	6423.3
17.5°	6105.2
20°	5819.6
22.5°	5523.1
25°	5171.6
27.5°	4688.4
30°	4117.6
32.5°	3447.6
35°	2745.1
37.5°	2152.2
40°	1636.0
42.5°	1218.7
45°	900.6
47.5°	658.8
50°	483.2
52.5°	362.3
55°	274.3
57.5°	208.5
60°	164.7
62.5°	120.9
65°	98.8
67.5°	76.7
70°	55.0
72.5°	43.8
75°	32.9
77.5°	22.1
80°	10.8
82.5°	10.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)