

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684793

Luminaire Tested: **LX6C120D010 EX61209027 6LBSLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684793
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C120D010 EX61209027 6LBSLI
Description: 6 INCH 12000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 6LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12848.9 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 142.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684793

CATALOG NUMBER: LX6C120D010 EX61209027 6LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P684793

CATALOG NUMBER: LX6C120D010 EX61209027 6LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	444498
5°	439439
10°	417160
15°	385031
20°	351985
25°	318720
30°	290329
35°	268582
40°	251049
45°	233869
50°	213042
55°	186555
60°	155645
65°	122166
70°	85319
75°	46238
80°	8650
85°	0



TEST NUMBER: P684793

CATALOG NUMBER: LX6C120D010 EX61209027 6LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	747.2	5.8
10°-20°	1902.1	14.8
20°-30°	2425.6	18.9
30°-40°	2515.5	19.6
40°-50°	2317.8	18.0
50°-60°	1743.5	13.6
60°-70°	941.1	7.3
70°-80°	252.4	2.0
80°-90°	3.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5074.9	39.5
0°-40°	7590.4	59.1
0°-60°	11651.7	90.7
0°-90°	12848.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12848.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8108	
5°	7986	747
15°	6784	1902
25°	5269	2426
35°	4013	2515
45°	3017	2318
55°	1952	1743
65°	942	941
75°	218	252
85°	0	4
90°	0	



TEST NUMBER: P684793

CATALOG NUMBER: LX6C120D010 EX61209027 6LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	8108.3
2.5°	8081.2
5°	7985.5
7.5°	7808.0
10°	7494.0
12.5°	7180.2
15°	6784.2
17.5°	6415.9
20°	6033.5
22.5°	5637.8
25°	5269.2
27.5°	4914.3
30°	4586.5
32.5°	4286.2
35°	4013.3
37.5°	3753.8
40°	3508.1
42.5°	3248.9
45°	3016.6
47.5°	2757.5
50°	2498.0
52.5°	2225.1
55°	1951.9
57.5°	1679.0
60°	1419.6
62.5°	1173.8
65°	941.8
67.5°	723.5
70°	532.3
72.5°	368.6
75°	218.3
77.5°	95.4
80°	27.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)