

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684823

Luminaire Tested: **LX6C130D010 EX61309030 6LBSLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684823
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C130D010 EX61309030 6LBSLI
Description: 6 INCH 13000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14698.0 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 144.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684823

CATALOG NUMBER: LX6C130D010 EX61309030 6LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P684823

CATALOG NUMBER: LX6C130D010 EX61309030 6LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	508463
5°	502673
10°	477190
15°	440434
20°	402640
25°	364582
30°	332108
35°	307230
40°	287174
45°	267524
50°	243702
55°	213402
60°	178045
65°	139743
70°	97597
75°	52889
80°	9913
85°	0



TEST NUMBER: P684823

CATALOG NUMBER: LX6C130D010 EX61309030 6LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	854.7	5.8
10°-20°	2175.9	14.8
20°-30°	2774.7	18.9
30°-40°	2877.4	19.6
40°-50°	2651.4	18.0
50°-60°	1994.4	13.6
60°-70°	1076.5	7.3
70°-80°	288.8	2.0
80°-90°	4.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5805.2	39.5
0°-40°	8682.7	59.1
0°-60°	13328.5	90.7
0°-90°	14698.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	14698.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9275	
5°	9135	855
15°	7760	2176
25°	6027	2775
35°	4591	2877
45°	3451	2651
55°	2233	1994
65°	1077	1077
75°	250	289
85°	0	4
90°	0	



TEST NUMBER: P684823

CATALOG NUMBER: LX6C130D010 EX61309030 6LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	9275.1
2.5°	9244.1
5°	9134.6
7.5°	8931.6
10°	8572.4
12.5°	8213.5
15°	7760.4
17.5°	7339.1
20°	6901.8
22.5°	6449.1
25°	6027.4
27.5°	5621.4
30°	5246.5
32.5°	4903.0
35°	4590.8
37.5°	4294.0
40°	4012.9
42.5°	3716.5
45°	3450.7
47.5°	3154.3
50°	2857.5
52.5°	2545.3
55°	2232.8
57.5°	1920.7
60°	1623.9
62.5°	1342.8
65°	1077.3
67.5°	827.6
70°	608.9
72.5°	421.7
75°	249.7
77.5°	109.2
80°	31.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)