

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684029

Luminaire Tested: **LX6C130D010 EX6C1309730 6LBSH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684029
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C130D010 EX6C1309730 6LBSH
Description: 6 INCH 13000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 97CRI LEDS
AND 6LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14200.0 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 144.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684029

CATALOG NUMBER: LX6C130D010 EX6C1309730 6LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P684029

CATALOG NUMBER: LX6C130D010 EX6C1309730 6LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77				77
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				67
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58				58
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51				51
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46				46
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41				41
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37				37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34				34
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31				31

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	407127
5°	405227
10°	396864
15°	382431
20°	364848
25°	345183
30°	325601
35°	306581
40°	288677
45°	269090
50°	245357
55°	216690
60°	183406
65°	144010
70°	102758
75°	56299
80°	9913
85°	0



TEST NUMBER: P684029

CATALOG NUMBER: LX6C130D010 EX6C1309730 6LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	695.6	4.9
10°-20°	1890.7	13.3
20°-30°	2625.7	18.5
30°-40°	2865.3	20.2
40°-50°	2672.9	18.8
50°-60°	2028.8	14.3
60°-70°	1110.9	7.8
70°-80°	305.7	2.2
80°-90°	4.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5212.0	36.7
0°-40°	8077.4	56.9
0°-60°	12779.1	90.0
0°-90°	14200.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	14200.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7427	
5°	7364	696
15°	6738	1891
25°	5707	2626
35°	4581	2865
45°	3471	2673
55°	2267	2029
65°	1110	1111
75°	266	306
85°	0	4
90°	0	



TEST NUMBER: P684029

CATALOG NUMBER: LX6C130D010 EX6C1309730 6LBSH

CANDELA DISTRIBUTION (FULL):

0°	
0°	7426.6
2.5°	7426.6
5°	7363.8
7.5°	7270.0
10°	7129.4
12.5°	6941.8
15°	6738.4
17.5°	6488.4
20°	6254.0
22.5°	5972.5
25°	5706.7
27.5°	5440.9
30°	5143.7
32.5°	4862.3
35°	4581.1
37.5°	4299.6
40°	4033.9
42.5°	3752.4
45°	3470.9
47.5°	3189.4
50°	2876.9
52.5°	2579.7
55°	2267.2
57.5°	1970.0
60°	1672.8
62.5°	1376.0
65°	1110.2
67.5°	859.8
70°	641.1
72.5°	437.7
75°	265.8
77.5°	125.2
80°	31.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)