

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685009

Luminaire Tested: **LX6C40D010 EX6409050 6LBSLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P685009
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C40D010 EX6409050 6LBSLI
Description: 6 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 6LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4596.0 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685009
CATALOG NUMBER: LX6C40D010 EX6409050 6LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P685009

CATALOG NUMBER: LX6C40D010 EX6409050 6LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			68
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			60
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			47
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158995
5°	157181
10°	149212
15°	137725
20°	125906
25°	114001
30°	103851
35°	96068
40°	89797
45°	83652
50°	76202
55°	66731
60°	55675
65°	43701
70°	30518
75°	16542
80°	3094
85°	0



TEST NUMBER: P685009

CATALOG NUMBER: LX6C40D010 EX6409050 6LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.3	5.8
10°-20°	680.4	14.8
20°-30°	867.6	18.9
30°-40°	899.7	19.6
40°-50°	829.1	18.0
50°-60°	623.6	13.6
60°-70°	336.6	7.3
70°-80°	90.3	2.0
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1815.3	39.5
0°-40°	2715.0	59.1
0°-60°	4167.7	90.7
0°-90°	4596.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4596.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2900	
5°	2856	267
15°	2427	680
25°	1885	868
35°	1436	900
45°	1079	829
55°	698	624
65°	337	337
75°	78	90
85°	0	1
90°	0	



TEST NUMBER: P685009

CATALOG NUMBER: LX6C40D010 EX6409050 6LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2900.3
2.5°	2890.6
5°	2856.3
7.5°	2792.9
10°	2680.5
12.5°	2568.3
15°	2426.7
17.5°	2294.9
20°	2158.2
22.5°	2016.6
25°	1884.7
27.5°	1757.8
30°	1640.6
32.5°	1533.1
35°	1435.5
37.5°	1342.7
40°	1254.8
42.5°	1162.1
45°	1079.0
47.5°	986.3
50°	893.5
52.5°	795.9
55°	698.2
57.5°	600.6
60°	507.8
62.5°	419.9
65°	336.9
67.5°	258.8
70°	190.4
72.5°	131.9
75°	78.1
77.5°	34.1
80°	9.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)