

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685027

Luminaire Tested: **LX6C45D010 EX6459040 6LBMLI**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P685027  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C45D010 EX6459040 6LBMLI  
Description: 6 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS  
AND 6LBM TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4327.0 lumens  
Efficiency: N/A  
Efficacy: 87.2 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 49.6  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P685027

CATALOG NUMBER: LX6C45D010 EX6459040 6LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P685027

CATALOG NUMBER: LX6C45D010 EX6459040 6LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	296851
5°	294029
10°	278619
15°	252958
20°	223529
25°	193245
30°	151061
35°	92635
40°	47546
45°	18893
50°	6132
55°	2112
60°	1809
65°	1453
70°	898
75°	1186
80°	0
85°	0



TEST NUMBER: P685027

CATALOG NUMBER: LX6C45D010 EX6459040 6LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	498.8	11.5
10°-20°	1241.9	28.7
20°-30°	1443.7	33.4
30°-40°	884.1	20.4
40°-50°	219.5	5.1
50°-60°	25.6	0.6
60°-70°	9.6	0.2
70°-80°	3.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3184.5	73.6
0°-40°	4068.6	94.0
0°-60°	4313.7	99.7
0°-90°	4327.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4327.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5415	
5°	5343	499
15°	4457	1242
25°	3195	1444
35°	1384	884
45°	244	220
55°	22	26
65°	11	10
75°	6	4
85°	0	0
90°	0	



TEST NUMBER: P685027

CATALOG NUMBER: LX6C45D010 EX6459040 6LBMLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5415.0
2.5°	5409.5
5°	5343.1
7.5°	5199.1
10°	5005.2
12.5°	4750.6
15°	4457.1
17.5°	4141.6
20°	3831.6
22.5°	3521.4
25°	3194.8
27.5°	2818.3
30°	2386.4
32.5°	1882.5
35°	1384.2
37.5°	974.4
40°	664.4
42.5°	415.2
45°	243.7
47.5°	138.5
50°	71.9
52.5°	33.3
55°	22.1
57.5°	16.5
60°	16.5
62.5°	11.2
65°	11.2
67.5°	5.6
70°	5.6
72.5°	5.6
75°	5.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)