

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685099

Luminaire Tested: **LX6C55D010 EX6559035 6LBSLI**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P685099  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C55D010 EX6559035 6LBSLI  
Description: 6 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 6LBS TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6592.0 lumens  
Efficiency: N/A  
Efficacy: 103.2 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 63.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P685099

CATALOG NUMBER: LX6C55D010 EX6559035 6LBSLI

### Luminous Intensity Polar Plot





TEST NUMBER: P685099

CATALOG NUMBER: LX6C55D010 EX6559035 6LBSLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			68
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			60
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			47
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	228046
5°	225445
10°	214019
15°	197532
20°	180581
25°	163515
30°	148947
35°	137795
40°	128798
45°	119981
50°	109301
55°	95710
60°	79851
65°	62679
70°	43773
75°	23723
80°	4451
85°	0



TEST NUMBER: P685099

CATALOG NUMBER: LX6C55D010 EX6559035 6LBSLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	383.3	5.8
10°-20°	975.9	14.8
20°-30°	1244.4	18.9
30°-40°	1290.5	19.6
40°-50°	1189.1	18.0
50°-60°	894.5	13.6
60°-70°	482.8	7.3
70°-80°	129.5	2.0
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2603.6	39.5
0°-40°	3894.2	59.1
0°-60°	5977.8	90.7
0°-90°	6592.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6592.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4160	
5°	4097	383
15°	3480	976
25°	2703	1244
35°	2059	1291
45°	1548	1189
55°	1001	894
65°	483	483
75°	112	130
85°	0	2
90°	0	



TEST NUMBER: P685099

CATALOG NUMBER: LX6C55D010 EX6559035 6LBSLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4159.9
2.5°	4145.9
5°	4096.8
7.5°	4005.8
10°	3844.7
12.5°	3683.7
15°	3480.5
17.5°	3291.6
20°	3095.4
22.5°	2892.4
25°	2703.3
27.5°	2521.2
30°	2353.0
32.5°	2199.0
35°	2059.0
37.5°	1925.9
40°	1799.8
42.5°	1666.8
45°	1547.6
47.5°	1414.7
50°	1281.6
52.5°	1141.6
55°	1001.4
57.5°	861.4
60°	728.3
62.5°	602.2
65°	483.2
67.5°	371.2
70°	273.1
72.5°	189.1
75°	112.0
77.5°	49.0
80°	14.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)