

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684447

Luminaire Tested: **LX6C60D010 EX6C609027 6LBSH**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P684447  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C60D010 EX6C609027 6LBSH  
Description: 6 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 6LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6530.0 lumens  
Efficiency: N/A  
Efficacy: 90.7 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 72  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684447

CATALOG NUMBER: LX6C60D010 EX6C609027 6LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P684447

CATALOG NUMBER: LX6C60D010 EX6C609027 6LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	187222
5°	186347
10°	182501
15°	175864
20°	167775
25°	158737
30°	149732
35°	140987
40°	132749
45°	123742
50°	112832
55°	99648
60°	84346
65°	66220
70°	47252
75°	25883
80°	4546
85°	0



TEST NUMBER: P684447

CATALOG NUMBER: LX6C60D010 EX6C609027 6LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	319.9	4.9
10°-20°	869.4	13.3
20°-30°	1207.5	18.5
30°-40°	1317.7	20.2
40°-50°	1229.2	18.8
50°-60°	933.0	14.3
60°-70°	510.9	7.8
70°-80°	140.6	2.2
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2396.8	36.7
0°-40°	3714.5	56.9
0°-60°	5876.6	90.0
0°-90°	6530.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6530.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3415	
5°	3386	320
15°	3099	869
25°	2624	1207
35°	2107	1318
45°	1596	1229
55°	1043	933
65°	510	511
75°	122	141
85°	0	2
90°	0	



TEST NUMBER: P684447

CATALOG NUMBER: LX6C60D010 EX6C609027 6LBSH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3415.2
2.5°	3415.2
5°	3386.3
7.5°	3343.2
10°	3278.5
12.5°	3192.2
15°	3098.7
17.5°	2983.7
20°	2875.9
22.5°	2746.5
25°	2624.3
27.5°	2502.1
30°	2365.4
32.5°	2236.0
35°	2106.7
37.5°	1977.2
40°	1855.0
42.5°	1725.6
45°	1596.1
47.5°	1466.7
50°	1323.0
52.5°	1186.3
55°	1042.6
57.5°	905.9
60°	769.3
62.5°	632.8
65°	510.5
67.5°	395.4
70°	294.8
72.5°	201.3
75°	122.2
77.5°	57.6
80°	14.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)