

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685119

Luminaire Tested: **LX6C60D010 EX6609030 6LBSLI**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P685119  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C60D010 EX6609030 6LBSLI  
Description: 6 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LBS TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7028.0 lumens  
Efficiency: N/A  
Efficacy: 97.6 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 72  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P685119  
CATALOG NUMBER: LX6C60D010 EX6609030 6LBSLI

### Luminous Intensity Polar Plot





TEST NUMBER: P685119

CATALOG NUMBER: LX6C60D010 EX6609030 6LBSLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			68
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			60
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			47
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	243127
5°	240358
10°	228174
15°	210597
20°	192528
25°	174331
30°	158803
35°	146910
40°	137314
45°	127920
50°	116525
55°	102037
60°	85136
65°	66816
70°	46675
75°	25290
80°	4735
85°	0



TEST NUMBER: P685119

CATALOG NUMBER: LX6C60D010 EX6609030 6LBSLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	408.7	5.8
10°-20°	1040.4	14.8
20°-30°	1326.7	18.9
30°-40°	1375.9	19.6
40°-50°	1267.8	18.0
50°-60°	953.6	13.6
60°-70°	514.7	7.3
70°-80°	138.1	2.0
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2775.8	39.5
0°-40°	4151.7	59.1
0°-60°	6373.1	90.7
0°-90°	7028.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7028.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4435	
5°	4368	409
15°	3711	1040
25°	2882	1327
35°	2195	1376
45°	1650	1268
55°	1068	954
65°	515	515
75°	119	138
85°	0	2
90°	0	



TEST NUMBER: P685119

CATALOG NUMBER: LX6C60D010 EX6609030 6LBSLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4435.0
2.5°	4420.2
5°	4367.8
7.5°	4270.7
10°	4099.0
12.5°	3927.4
15°	3710.7
17.5°	3509.3
20°	3300.2
22.5°	3083.7
25°	2882.1
27.5°	2687.9
30°	2508.7
32.5°	2344.4
35°	2195.2
37.5°	2053.2
40°	1918.8
42.5°	1777.1
45°	1650.0
47.5°	1508.2
50°	1366.3
52.5°	1217.1
55°	1067.6
57.5°	918.4
60°	776.5
62.5°	642.1
65°	515.1
67.5°	395.7
70°	291.2
72.5°	201.6
75°	119.4
77.5°	52.2
80°	15.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)