

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684454

Luminaire Tested: **LX6C60D010 EX6C609030 6LBSH**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P684454  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C60D010 EX6C609030 6LBSH  
Description: 6 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6789.1 lumens  
Efficiency: N/A  
Efficacy: 94.3 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 72  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684454

CATALOG NUMBER: LX6C60D010 EX6C609030 6LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P684454

CATALOG NUMBER: LX6C60D010 EX6C609030 6LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	194650
5°	193737
10°	189743
15°	182839
20°	174432
25°	165034
30°	155670
35°	146575
40°	138016
45°	128649
50°	117301
55°	103595
60°	87690
65°	68853
70°	49127
75°	26921
80°	4735
85°	0



TEST NUMBER: P684454

CATALOG NUMBER: LX6C60D010 EX6C609030 6LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	332.6	4.9
10°-20°	903.9	13.3
20°-30°	1255.4	18.5
30°-40°	1369.9	20.2
40°-50°	1277.9	18.8
50°-60°	970.0	14.3
60°-70°	531.1	7.8
70°-80°	146.2	2.2
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2491.9	36.7
0°-40°	3861.8	56.9
0°-60°	6109.7	90.0
0°-90°	6789.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6789.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3551	
5°	3521	333
15°	3222	904
25°	2728	1255
35°	2190	1370
45°	1659	1278
55°	1084	970
65°	531	531
75°	127	146
85°	0	2
90°	0	



TEST NUMBER: P684454

CATALOG NUMBER: LX6C60D010 EX6C609030 6LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3550.7
2.5°	3550.7
5°	3520.6
7.5°	3475.8
10°	3408.6
12.5°	3318.9
15°	3221.6
17.5°	3102.1
20°	2990.0
22.5°	2855.4
25°	2728.4
27.5°	2601.3
30°	2459.2
32.5°	2324.6
35°	2190.2
37.5°	2055.7
40°	1928.6
42.5°	1794.0
45°	1659.4
47.5°	1524.9
50°	1375.4
52.5°	1233.4
55°	1083.9
57.5°	941.9
60°	799.8
62.5°	657.9
65°	530.8
67.5°	411.1
70°	306.5
72.5°	209.3
75°	127.1
77.5°	59.9
80°	15.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)