

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684462

Luminaire Tested: **LX6C60D010 EX6C609035 6LBWH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P684462
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C60D010 EX6C609035 6LBWH
Description: 6 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LBW TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5847.9 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684462

CATALOG NUMBER: LX6C60D010 EX6C609035 6LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P684462

CATALOG NUMBER: LX6C60D010 EX6C609035 6LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	197725
5°	197661
10°	196139
15°	194825
20°	191858
25°	187475
30°	176515
35°	159745
40°	133393
45°	102212
50°	72390
55°	45638
60°	25744
65°	16707
70°	10915
75°	8028
80°	4830
85°	4780



TEST NUMBER: P684462

CATALOG NUMBER: LX6C60D010 EX6C609035 6LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	340.7	5.8
10°-20°	966.7	16.5
20°-30°	1417.3	24.2
30°-40°	1475.1	25.2
40°-50°	1020.5	17.5
50°-60°	444.3	7.6
60°-70°	136.2	2.3
70°-80°	40.9	0.7
80°-90°	6.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2724.7	46.6
0°-40°	4199.8	71.8
0°-60°	5664.6	96.9
0°-90°	5847.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5847.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3607	
5°	3592	341
15°	3433	967
25°	3099	1417
35°	2387	1475
45°	1318	1021
55°	478	444
65°	129	136
75°	38	41
85°	8	6
90°	0	



TEST NUMBER: P684462

CATALOG NUMBER: LX6C60D010 EX6C609035 6LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3606.8
2.5°	3614.5
5°	3591.9
7.5°	3561.6
10°	3523.5
12.5°	3485.6
15°	3432.8
17.5°	3364.4
20°	3288.7
22.5°	3205.3
25°	3099.4
27.5°	2962.9
30°	2788.5
32.5°	2606.6
35°	2387.0
37.5°	2144.6
40°	1864.0
42.5°	1583.7
45°	1318.4
47.5°	1068.3
50°	848.8
52.5°	644.2
55°	477.5
57.5°	341.0
60°	234.8
62.5°	174.3
65°	128.8
67.5°	98.6
70°	68.1
72.5°	53.1
75°	37.9
77.5°	22.6
80°	15.3
82.5°	7.6
85°	7.6
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)