

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685129

Luminaire Tested: **LX6C60D010 EX6609040 6LBSLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P685129
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C60D010 EX6609040 6LBSLI
Description: 6 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7137.0 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685129
CATALOG NUMBER: LX6C60D010 EX6609040 6LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P685129

CATALOG NUMBER: LX6C60D010 EX6609040 6LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			68
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			60
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			47
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	246899
5°	244084
10°	231709
15°	213866
20°	195509
25°	177034
30°	161265
35°	149185
40°	139447
45°	129905
50°	118333
55°	103624
60°	86451
65°	67854
70°	47396
75°	25692
80°	4799
85°	0



TEST NUMBER: P685129

CATALOG NUMBER: LX6C60D010 EX6609040 6LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	415.0	5.8
10°-20°	1056.5	14.8
20°-30°	1347.3	18.9
30°-40°	1397.2	19.6
40°-50°	1287.4	18.0
50°-60°	968.4	13.6
60°-70°	522.7	7.3
70°-80°	140.2	2.0
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2818.9	39.5
0°-40°	4216.1	59.1
0°-60°	6472.0	90.7
0°-90°	7137.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7137.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4504	
5°	4436	415
15°	3768	1057
25°	2927	1347
35°	2229	1397
45°	1676	1287
55°	1084	968
65°	523	523
75°	121	140
85°	0	2
90°	0	



TEST NUMBER: P685129

CATALOG NUMBER: LX6C60D010 EX6609040 6LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4503.8
2.5°	4488.7
5°	4435.5
7.5°	4337.0
10°	4162.5
12.5°	3988.3
15°	3768.3
17.5°	3563.7
20°	3351.3
22.5°	3131.5
25°	2926.8
27.5°	2729.6
30°	2547.6
32.5°	2380.8
35°	2229.2
37.5°	2085.1
40°	1948.6
42.5°	1804.6
45°	1675.6
47.5°	1531.6
50°	1387.5
52.5°	1235.9
55°	1084.2
57.5°	932.6
60°	788.5
62.5°	652.0
65°	523.1
67.5°	401.9
70°	295.7
72.5°	204.7
75°	121.3
77.5°	53.0
80°	15.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)