

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684475

Luminaire Tested: **LX6C60D010 EX6C609050 6LBSH**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P684475  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C60D010 EX6C609050 6LBSH  
Description: 6 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 6LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7037.0 lumens  
Efficiency: N/A  
Efficacy: 97.7 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 72  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684475

CATALOG NUMBER: LX6C60D010 EX6C609050 6LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P684475

CATALOG NUMBER: LX6C60D010 EX6C609050 6LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	201760
5°	200814
10°	196673
15°	189519
20°	180802
25°	171058
30°	161354
35°	151929
40°	143054
45°	133347
50°	121591
55°	107380
60°	90892
65°	71370
70°	50922
75°	27895
80°	4925
85°	0



TEST NUMBER: P684475

CATALOG NUMBER: LX6C60D010 EX6C609050 6LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	344.7	4.9
10°-20°	937.0	13.3
20°-30°	1301.2	18.5
30°-40°	1419.9	20.2
40°-50°	1324.6	18.8
50°-60°	1005.4	14.3
60°-70°	550.5	7.8
70°-80°	151.5	2.2
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2582.9	36.7
0°-40°	4002.8	56.9
0°-60°	6332.8	90.0
0°-90°	7037.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7037.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3680	
5°	3649	345
15°	3339	937
25°	2828	1301
35°	2270	1420
45°	1720	1325
55°	1124	1005
65°	550	551
75°	132	152
85°	0	2
90°	0	



TEST NUMBER: P684475

CATALOG NUMBER: LX6C60D010 EX6C609050 6LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3680.4
2.5°	3680.4
5°	3649.2
7.5°	3602.8
10°	3533.1
12.5°	3440.1
15°	3339.3
17.5°	3215.4
20°	3099.2
22.5°	2959.7
25°	2828.0
27.5°	2696.3
30°	2549.0
32.5°	2409.6
35°	2270.2
37.5°	2130.7
40°	1999.0
42.5°	1859.5
45°	1720.0
47.5°	1580.6
50°	1425.7
52.5°	1278.4
55°	1123.5
57.5°	976.3
60°	829.0
62.5°	681.9
65°	550.2
67.5°	426.1
70°	317.7
72.5°	216.9
75°	131.7
77.5°	62.1
80°	15.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)