

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685179

Luminaire Tested: **LX6C70D010 EX6709040 6LBSLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P685179
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C70D010 EX6709040 6LBSLI
Description: 6 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7841.0 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685179

CATALOG NUMBER: LX6C70D010 EX6709040 6LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P685179

CATALOG NUMBER: LX6C70D010 EX6709040 6LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			68
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			60
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			47
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	271250
5°	268165
10°	254566
15°	234962
20°	214796
25°	194497
30°	177173
35°	163901
40°	153201
45°	142720
50°	130009
55°	113841
60°	94981
65°	74548
70°	52076
75°	28213
80°	5272
85°	0



TEST NUMBER: P685179

CATALOG NUMBER: LX6C70D010 EX6709040 6LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	456.0	5.8
10°-20°	1160.8	14.8
20°-30°	1480.2	18.9
30°-40°	1535.1	19.6
40°-50°	1414.4	18.0
50°-60°	1064.0	13.6
60°-70°	574.3	7.3
70°-80°	154.0	2.0
80°-90°	2.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3096.9	39.5
0°-40°	4632.0	59.1
0°-60°	7110.4	90.7
0°-90°	7841.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7841.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4948	
5°	4873	456
15°	4140	1161
25°	3216	1480
35°	2449	1535
45°	1841	1414
55°	1191	1064
65°	575	574
75°	133	154
85°	0	2
90°	0	



TEST NUMBER: P685179

CATALOG NUMBER: LX6C70D010 EX6709040 6LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4948.0
2.5°	4931.5
5°	4873.1
7.5°	4764.8
10°	4573.1
12.5°	4381.7
15°	4140.0
17.5°	3915.2
20°	3681.9
22.5°	3440.4
25°	3215.5
27.5°	2998.9
30°	2798.9
32.5°	2615.6
35°	2449.1
37.5°	2290.8
40°	2140.8
42.5°	1982.6
45°	1840.9
47.5°	1682.7
50°	1524.4
52.5°	1357.9
55°	1191.1
57.5°	1024.6
60°	866.3
62.5°	716.3
65°	574.7
67.5°	441.5
70°	324.9
72.5°	224.9
75°	133.2
77.5°	58.2
80°	16.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)