

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685244

Luminaire Tested: **LX6C80D010 EX6809030 6LBSLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P685244
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C80D010 EX6809030 6LBSLI
Description: 6 INCH 8000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9806.0 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 89.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685244
CATALOG NUMBER: LX6C80D010 EX6809030 6LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P685244

CATALOG NUMBER: LX6C80D010 EX6809030 6LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			68
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			60
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			47
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	339227
5°	335367
10°	318364
15°	293844
20°	268625
25°	243238
30°	221572
35°	204972
40°	191595
45°	178484
50°	162587
55°	142380
60°	118784
65°	93240
70°	65123
75°	35287
80°	6598
85°	0



TEST NUMBER: P685244

CATALOG NUMBER: LX6C80D010 EX6809030 6LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	570.2	5.8
10°-20°	1451.7	14.8
20°-30°	1851.2	18.9
30°-40°	1919.7	19.6
40°-50°	1768.9	18.0
50°-60°	1330.6	13.6
60°-70°	718.2	7.3
70°-80°	192.7	2.0
80°-90°	2.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3873.1	39.5
0°-40°	5792.8	59.1
0°-60°	8892.3	90.7
0°-90°	9806.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9806.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6188	
5°	6094	570
15°	5178	1452
25°	4021	1851
35°	3063	1920
45°	2302	1769
55°	1490	1331
65°	719	718
75°	167	193
85°	0	3
90°	0	



TEST NUMBER: P685244

CATALOG NUMBER: LX6C80D010 EX6809030 6LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6188.0
2.5°	6167.3
5°	6094.3
7.5°	5958.9
10°	5719.2
12.5°	5479.8
15°	5177.5
17.5°	4896.4
20°	4604.6
22.5°	4302.6
25°	4021.3
27.5°	3750.4
30°	3500.3
32.5°	3271.1
35°	3062.8
37.5°	2864.8
40°	2677.3
42.5°	2479.5
45°	2302.2
47.5°	2104.4
50°	1906.4
52.5°	1698.1
55°	1489.7
57.5°	1281.4
60°	1083.4
62.5°	895.8
65°	718.8
67.5°	552.2
70°	406.3
72.5°	281.3
75°	166.6
77.5°	72.8
80°	20.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)