

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685274

Luminaire Tested: **LX6C90D010 EX6909035 6LBSLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P685274
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C90D010 EX6909035 6LBSLI
Description: 6 INCH 9000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10590.0 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 97.1
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685274
CATALOG NUMBER: LX6C90D010 EX6909035 6LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P685274

CATALOG NUMBER: LX6C90D010 EX6909035 6LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			68
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			60
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			47
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	366352
5°	362177
10°	343815
15°	317334
20°	290105
25°	262685
30°	239284
35°	221361
40°	206909
45°	192756
50°	175585
55°	153763
60°	128279
65°	100685
70°	70332
75°	38104
80°	7135
85°	0



TEST NUMBER: P685274

CATALOG NUMBER: LX6C90D010 EX6909035 6LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	615.8	5.8
10°-20°	1567.7	14.8
20°-30°	1999.2	18.9
30°-40°	2073.2	19.6
40°-50°	1910.3	18.0
50°-60°	1437.0	13.6
60°-70°	775.6	7.3
70°-80°	208.1	2.0
80°-90°	3.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4182.7	39.5
0°-40°	6255.9	59.1
0°-60°	9603.2	90.7
0°-90°	10590.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10590.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6683	
5°	6582	616
15°	5591	1568
25°	4343	1999
35°	3308	2073
45°	2486	1910
55°	1609	1437
65°	776	776
75°	180	208
85°	0	3
90°	0	



TEST NUMBER: P685274

CATALOG NUMBER: LX6C90D010 EX6909035 6LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6682.8
2.5°	6660.4
5°	6581.5
7.5°	6435.3
10°	6176.4
12.5°	5917.9
15°	5591.4
17.5°	5287.9
20°	4972.8
22.5°	4646.6
25°	4342.8
27.5°	4050.3
30°	3780.1
32.5°	3532.6
35°	3307.7
37.5°	3093.9
40°	2891.3
42.5°	2677.7
45°	2486.3
47.5°	2272.7
50°	2058.8
52.5°	1833.9
55°	1608.8
57.5°	1383.8
60°	1170.0
62.5°	967.5
65°	776.2
67.5°	596.3
70°	438.8
72.5°	303.8
75°	179.9
77.5°	78.7
80°	22.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)