

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685284

Luminaire Tested: **LX6C90D010 EX6909050 6LBSLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P685284
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C90D010 EX6909050 6LBSLI
Description: 6 INCH 9000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 6LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10824.0 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 97.1
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685284

CATALOG NUMBER: LX6C90D010 EX6909050 6LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P685284

CATALOG NUMBER: LX6C90D010 EX6909050 6LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			68
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			60
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			47
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	374449
5°	370178
10°	351413
15°	324349
20°	296511
25°	268485
30°	244576
35°	226254
40°	211482
45°	197013
50°	179465
55°	157156
60°	131119
65°	102916
70°	71871
75°	38952
80°	7293
85°	0



TEST NUMBER: P685284

CATALOG NUMBER: LX6C90D010 EX6909050 6LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	629.4	5.8
10°-20°	1602.4	14.8
20°-30°	2043.3	18.9
30°-40°	2119.0	19.6
40°-50°	1952.5	18.0
50°-60°	1468.7	13.6
60°-70°	792.8	7.3
70°-80°	212.7	2.0
80°-90°	3.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4275.1	39.5
0°-40°	6394.1	59.1
0°-60°	9815.4	90.7
0°-90°	10824.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10824.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6830	
5°	6727	629
15°	5715	1602
25°	4439	2043
35°	3381	2119
45°	2541	1953
55°	1644	1469
65°	793	793
75°	184	213
85°	0	3
90°	0	



TEST NUMBER: P685284

CATALOG NUMBER: LX6C90D010 EX6909050 6LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6830.5
2.5°	6807.6
5°	6726.9
7.5°	6577.5
10°	6312.9
12.5°	6048.6
15°	5715.0
17.5°	5404.7
20°	5082.6
22.5°	4749.3
25°	4438.7
27.5°	4139.8
30°	3863.7
32.5°	3610.7
35°	3380.8
37.5°	3162.2
40°	2955.2
42.5°	2736.9
45°	2541.2
47.5°	2322.9
50°	2104.3
52.5°	1874.4
55°	1644.3
57.5°	1414.4
60°	1195.9
62.5°	988.8
65°	793.4
67.5°	609.5
70°	448.4
72.5°	310.5
75°	183.9
77.5°	80.4
80°	23.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)