

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790064

Luminaire Tested: LER6D20D010-EC6DR1515309040-6LBDP1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P790064  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D20D010-EC6DR1515309040-6LBDP1H  
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 15° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2101.1 lumens  
Efficiency: N/A  
Efficacy: 91.0 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23  
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')  
CIE Type: Direct


Input Watts (W): 23.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P790064  
CATALOG NUMBER: LER6D20D010-EC6DR1515309040-6LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P790064

CATALOG NUMBER: LER6D20D010-EC6DR1515309040-6LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96																			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94																			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93																			
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92																			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90																			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89																			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88																			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87																			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3221210	3221210	3221210
5°	1892940	1868427	1883204
10°	564949	568915	577621
15°	140526	143262	138841
20°	42049	48693	42941
25°	14825	18883	15011
30°	5444	7166	5534
35°	2730	3079	2643
40°	1719	1896	1719
45°	1274	1358	1274
50°	1008	1008	1008
55°	842	842	842
60°	681	681	681
65°	521	521	521
70°	446	446	446
75°	272	272	363
80°	189	189	189
85°	100	100	100

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 1358 cd/sqm



TEST NUMBER: P790064

CATALOG NUMBER: LER6D20D010-EC6DR1515309040-6LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1362.7	64.9
10°-20°	560.5	26.7
20°-30°	111.3	5.3
30°-40°	27.8	1.3
40°-50°	14.6	0.7
50°-60°	10.8	0.5
60°-70°	7.7	0.4
70°-80°	4.3	0.2
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2034.6	96.8
0°-40°	2062.4	98.2
0°-60°	2087.8	99.4
0°-90°	2101.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2101.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	28628	28628	28628	28628	28628	
5°	18626	18434	18385	18512	18530	1360
15°	1618	1648	1649	1620	1598	555
25°	190	216	242	214	193	100
35°	38	40	42	40	36	26
45°	18	18	19	18	18	14
55°	12	12	12	12	12	11
65°	7	7	7	7	7	8
75°	4	4	4	4	5	4
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P790064

CATALOG NUMBER: LER6D20D010-EC6DR1515309040-6LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	28627.9	28627.9	28627.9	28627.9	28627.9
2.5°	25823.6	25845.4	25853.9	25879.3	25973.8
5°	18626.0	18434.5	18384.8	18512.1	18530.2
7.5°	11033.3	11072.1	11213.9	11245.4	11131.5
10°	6054.7	6104.4	6097.2	6140.8	6190.5
12.5°	3096.5	3057.7	3045.6	3095.2	3026.2
15°	1617.9	1648.2	1649.4	1620.3	1598.5
17.5°	870.2	905.3	963.5	916.2	843.5
20°	513.9	545.4	595.1	556.3	524.8
22.5°	317.5	343.0	378.1	347.8	322.4
25°	190.3	215.7	242.4	214.5	192.7
27.5°	112.7	134.5	151.5	133.3	111.5
30°	72.7	84.8	95.7	83.6	73.9
32.5°	50.9	55.7	60.6	55.7	50.9
35°	37.6	40.0	42.4	40.0	36.4
37.5°	29.1	31.5	32.7	30.3	27.9
40°	24.2	25.5	26.7	25.5	24.2
42.5°	20.6	21.8	21.8	21.8	20.6
45°	18.2	18.2	19.4	18.2	18.2
47.5°	15.8	15.8	17.0	15.8	15.8
50°	14.5	14.5	14.5	14.5	14.5
52.5°	13.3	13.3	13.3	13.3	13.3
55°	12.1	12.1	12.1	12.1	12.1
57.5°	10.9	10.9	10.9	10.9	10.9
60°	9.7	9.7	9.7	9.7	9.7
62.5°	8.5	8.5	8.5	8.5	8.5
65°	7.3	7.3	7.3	7.3	7.3
67.5°	7.3	7.3	7.3	7.3	7.3
70°	6.1	6.1	6.1	6.1	6.1
72.5°	4.8	4.8	4.8	4.8	4.8
75°	3.6	3.6	3.6	3.6	4.8
77.5°	3.6	3.6	3.6	3.6	3.6
80°	2.4	2.4	2.4	2.4	2.4
82.5°	2.4	2.4	2.4	2.4	2.4
85°	1.2	1.2	1.2	1.2	1.2
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)