

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792421

Luminaire Tested: LER6D40BD010-EC6DR4040509040-6LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P792421  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D40BD010-EC6DR4040509040-6LBS1LI  
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 40° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5463.7 lumens  
Efficiency: N/A  
Efficacy: 155.2 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P792421

CATALOG NUMBER: LER6D40BD010-EC6DR4040509040-6LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P792421

CATALOG NUMBER: LER6D40BD010-EC6DR4040509040-6LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99	98	97	96
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96	95	93	92
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93	91	89	88
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90	87	85	84
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87	84	82	81
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84	81	79	77
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81	78	76	74
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76	72	70	69
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73	70	68	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1389917
5°	1383162
10°	1307391
15°	1111446
20°	757529
25°	316073
30°	99379
35°	46190
40°	25545
45°	11712
50°	5677
55°	3105
60°	1617
65°	569
70°	224
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11712 cd/sqm



TEST NUMBER: P792421

CATALOG NUMBER: LER6D40BD010-EC6DR4040509040-6LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1177.6	21.6
10°-20°	2638.0	48.3
20°-30°	1320.5	24.2
30°-40°	242.1	4.4
40°-50°	66.8	1.2
50°-60°	15.7	0.3
60°-70°	3.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5136.1	94.0
0°-40°	5378.2	98.4
0°-60°	5460.7	99.9
0°-90°	5463.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5463.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12721	
5°	12611	###
15°	9826	2638
25°	2622	1321
35°	346	242
45°	76	67
55°	16	16
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P792421

CATALOG NUMBER: LER6D40BD010-EC6DR4040509040-6LBS1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	12721.1
2.5°	12702.5
5°	12611.1
7.5°	12319.8
10°	11784.0
12.5°	10948.7
15°	9825.8
17.5°	8365.5
20°	6515.1
22.5°	4441.8
25°	2621.8
27.5°	1386.0
30°	787.7
32.5°	509.1
35°	346.3
37.5°	247.5
40°	179.1
42.5°	122.6
45°	75.8
47.5°	48.3
50°	33.4
52.5°	23.8
55°	16.3
57.5°	10.4
60°	7.4
62.5°	4.5
65°	2.2
67.5°	1.5
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)