

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794047

Luminaire Tested: LER6D55D010-EC6DR6055659040-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794047
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D55D010-EC6DR6055659040-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5439.0 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P794047

CATALOG NUMBER: LER6D55D010-EC6DR6055659040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P794047

CATALOG NUMBER: LER6D55D010-EC6DR6055659040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86		
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80		
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62		
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	705759
5°	723119
10°	731857
15°	697185
20°	614711
25°	497197
30°	336314
35°	168529
40°	27342
45°	26763
50°	27299
55°	27697
60°	28473
65°	29111
70°	29805
75°	30184
80°	29069
85°	24195

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 30184 cd/sqm



TEST NUMBER: P794047

CATALOG NUMBER: LER6D55D010-EC6DR6055659040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	630.1	11.6
10°-20°	1704.9	31.3
20°-30°	1834.3	33.7
30°-40°	797.3	14.7
40°-50°	133.9	2.5
50°-60°	130.2	2.4
60°-70°	111.4	2.0
70°-80°	74.5	1.4
80°-90°	22.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4169.3	76.7
0°-40°	4966.7	91.3
0°-60°	5230.8	96.2
0°-90°	5439.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5439.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6459	
5°	6593	630
15°	6164	1705
25°	4124	1834
35°	1264	797
45°	173	134
55°	145	130
65°	113	111
75°	72	75
85°	19	22
90°	0	



TEST NUMBER: P794047

CATALOG NUMBER: LER6D55D010-EC6DR6055659040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	6459.4
2.5°	6641.0
5°	6593.1
7.5°	6608.2
10°	6596.5
12.5°	6460.3
15°	6163.5
17.5°	5765.1
20°	5286.8
22.5°	4774.8
25°	4124.2
27.5°	3298.7
30°	2665.7
32.5°	2054.5
35°	1263.5
37.5°	540.5
40°	191.7
42.5°	176.5
45°	173.2
47.5°	167.3
50°	160.6
52.5°	153.0
55°	145.4
57.5°	137.9
60°	130.3
62.5°	121.9
65°	112.6
67.5°	103.4
70°	93.3
72.5°	82.4
75°	71.5
77.5°	58.8
80°	46.2
82.5°	32.8
85°	19.3
87.5°	6.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)