

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251194

Luminaire Tested: **LSR8B60D010 EC8B60927 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251194
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B60927 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 2700 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5456.3 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251194

CATALOG NUMBER: LSR8B60D010 EC8B60927 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P251194

CATALOG NUMBER: LSR8B60D010 EC8B60927 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99 | 99 | 97 | 96 | 96 | 94 | 93 | 91 |
| 2 | 105 | 100 | 95 | 91 | 103 | 98 | 93 | 90 | 94 | 91 | 88 | 91 | 88 | 86 | 89 | 86 | 84 | 82 |
| 3 | 99 | 91 | 85 | 80 | 96 | 89 | 84 | 79 | 87 | 82 | 78 | 84 | 80 | 77 | 82 | 78 | 76 | 74 |
| 4 | 92 | 83 | 76 | 71 | 90 | 82 | 76 | 71 | 79 | 74 | 70 | 77 | 73 | 69 | 75 | 71 | 68 | 66 |
| 5 | 86 | 76 | 69 | 64 | 84 | 75 | 68 | 63 | 73 | 67 | 63 | 71 | 66 | 62 | 70 | 65 | 62 | 60 |
| 6 | 80 | 70 | 63 | 57 | 79 | 69 | 62 | 57 | 67 | 61 | 57 | 66 | 60 | 56 | 64 | 60 | 56 | 54 |
| 7 | 75 | 64 | 57 | 52 | 74 | 63 | 57 | 52 | 62 | 56 | 51 | 61 | 55 | 51 | 60 | 55 | 51 | 49 |
| 8 | 71 | 59 | 52 | 47 | 69 | 59 | 52 | 47 | 57 | 51 | 47 | 56 | 51 | 47 | 55 | 50 | 46 | 45 |
| 9 | 66 | 55 | 48 | 43 | 65 | 54 | 48 | 43 | 53 | 47 | 43 | 52 | 47 | 43 | 51 | 46 | 43 | 41 |
| 10 | 63 | 51 | 44 | 40 | 61 | 51 | 44 | 40 | 50 | 44 | 39 | 49 | 43 | 39 | 48 | 43 | 39 | 38 |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P251194

CATALOG NUMBER: LSR8B60D010 EC8B60927 8LBS0WH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 295.1 | 5.4 |
| 10°-20° | 874.3 | 16.0 |
| 20°-30° | 1353.6 | 24.8 |
| 30°-40° | 1466.4 | 26.9 |
| 40°-50° | 1055.2 | 19.3 |
| 50°-60° | 353.0 | 6.5 |
| 60°-70° | 53.4 | 1.0 |
| 70°-80° | 4.6 | 0.1 |
| 80°-90° | 0.7 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2523.0 | 46.2 |
| 0°-40° | 3989.4 | 73.1 |
| 0°-60° | 5397.7 | 98.9 |
| 0°-90° | 5456.3 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 5456.3 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3090 | |
| 5° | 3090 | 295 |
| 15° | 3094 | 874 |
| 25° | 2956 | 1354 |
| 35° | 2364 | 1466 |
| 45° | 1390 | 1055 |
| 55° | 357 | 353 |
| 65° | 47 | 53 |
| 75° | 3 | 5 |
| 85° | 0 | 1 |
| 90° | 0 | |



TEST NUMBER: P251194

CATALOG NUMBER: LSR8B60D010 EC8B60927 8LBS0WH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 3090.5 |
| 2.5° | 3090.5 |
| 5° | 3090.5 |
| 7.5° | 3092.1 |
| 10° | 3093.6 |
| 12.5° | 3096.8 |
| 15° | 3093.6 |
| 17.5° | 3081.0 |
| 20° | 3052.6 |
| 22.5° | 3009.9 |
| 25° | 2956.3 |
| 27.5° | 2871.0 |
| 30° | 2738.4 |
| 32.5° | 2564.7 |
| 35° | 2364.1 |
| 37.5° | 2147.7 |
| 40° | 1912.4 |
| 42.5° | 1659.7 |
| 45° | 1389.7 |
| 47.5° | 1097.6 |
| 50° | 814.8 |
| 52.5° | 559.0 |
| 55° | 356.8 |
| 57.5° | 213.2 |
| 60° | 127.9 |
| 62.5° | 77.4 |
| 65° | 47.4 |
| 67.5° | 23.7 |
| 70° | 11.0 |
| 72.5° | 4.7 |
| 75° | 3.2 |
| 77.5° | 3.2 |
| 80° | 1.6 |
| 82.5° | 1.6 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)