

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244012

Luminaire Tested: **LD8B40D010 ER8B409730 8LBM0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244012
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-11)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B40D010 ER8B409730 8LBM0LI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3362.9 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.72
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244012
CATALOG NUMBER: LD8B40D010 ER8B409730 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P244012

CATALOG NUMBER: LD8B40D010 ER8B409730 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 104 | 102 | | 101 | 100 | 99 | | 98 | 97 | 96 | 94 |
| 2 | 109 | 104 | 101 | 97 | 107 | 103 | 99 | 96 | 99 | 97 | 94 | | 96 | 94 | 92 | | 94 | 92 | 90 | 89 |
| 3 | 104 | 98 | 93 | 90 | 102 | 97 | 92 | 89 | 94 | 90 | 88 | | 92 | 89 | 86 | | 89 | 87 | 85 | 83 |
| 4 | 99 | 92 | 87 | 83 | 97 | 91 | 86 | 83 | 89 | 85 | 82 | | 87 | 84 | 81 | | 85 | 82 | 80 | 78 |
| 5 | 95 | 87 | 82 | 78 | 93 | 86 | 81 | 77 | 84 | 80 | 77 | | 83 | 79 | 76 | | 81 | 78 | 75 | 74 |
| 6 | 90 | 82 | 77 | 73 | 89 | 81 | 76 | 73 | 80 | 75 | 72 | | 79 | 75 | 72 | | 77 | 74 | 71 | 70 |
| 7 | 86 | 78 | 72 | 69 | 85 | 77 | 72 | 68 | 76 | 71 | 68 | | 75 | 71 | 68 | | 74 | 70 | 67 | 66 |
| 8 | 83 | 74 | 68 | 65 | 82 | 73 | 68 | 65 | 72 | 68 | 64 | | 71 | 67 | 64 | | 70 | 67 | 64 | 62 |
| 9 | 79 | 70 | 65 | 61 | 78 | 70 | 65 | 61 | 69 | 64 | 61 | | 68 | 64 | 61 | | 67 | 63 | 60 | 59 |
| 10 | 76 | 67 | 62 | 58 | 75 | 67 | 61 | 58 | 66 | 61 | 58 | | 65 | 61 | 58 | | 64 | 60 | 58 | 56 |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244012

CATALOG NUMBER: LD8B40D010 ER8B409730 8LBM0LI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 513.4 | 15.3 |
| 10°-20° | 1077.1 | 32.0 |
| 20°-30° | 1054.0 | 31.3 |
| 30°-40° | 583.1 | 17.3 |
| 40°-50° | 112.9 | 3.4 |
| 50°-60° | 17.3 | 0.5 |
| 60°-70° | 4.2 | 0.1 |
| 70°-80° | 1.1 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2644.4 | 78.6 |
| 0°-40° | 3227.5 | 96.0 |
| 0°-60° | 3357.6 | 99.8 |
| 0°-90° | 3362.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 3362.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 5867 | |
| 5° | 5593 | 513 |
| 15° | 3879 | 1077 |
| 25° | 2301 | 1054 |
| 35° | 918 | 583 |
| 45° | 129 | 113 |
| 55° | 16 | 17 |
| 65° | 4 | 4 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P244012

CATALOG NUMBER: LD8B40D010 ER8B409730 8LBM0LI

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 5866.7 |
| 2.5° | 5786.0 |
| 5° | 5593.2 |
| 7.5° | 5322.8 |
| 10° | 4922.5 |
| 12.5° | 4416.3 |
| 15° | 3878.6 |
| 17.5° | 3374.6 |
| 20° | 2955.4 |
| 22.5° | 2608.5 |
| 25° | 2301.4 |
| 27.5° | 2012.2 |
| 30° | 1704.0 |
| 32.5° | 1342.5 |
| 35° | 918.0 |
| 37.5° | 552.3 |
| 40° | 323.8 |
| 42.5° | 202.3 |
| 45° | 128.9 |
| 47.5° | 80.7 |
| 50° | 47.2 |
| 52.5° | 26.2 |
| 55° | 15.7 |
| 57.5° | 9.4 |
| 60° | 7.3 |
| 62.5° | 5.2 |
| 65° | 4.2 |
| 67.5° | 3.1 |
| 70° | 2.1 |
| 72.5° | 1.0 |
| 75° | 1.0 |
| 77.5° | 1.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)