

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P368064

Luminaire Tested: **PMM-SA3D-727-U-SLR**

Issue Date: 12/2/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P368064  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1910-543-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/2/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: PMM-SA3D-727-U-SLR  
Description: MESA POST TOP DECORATIVE LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR RIGHT OPTICS.  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 14260 lumens  
Efficiency: N/A  
Efficacy: 74.3 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B2 - U0 - G3


Input Watts (W): 192  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P368064  
 CATALOG NUMBER: PMM-SA3D-727-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.1 fc  
 Type IV - Short - N/A

REPORT NUMBER: P368064  
CATALOG NUMBER: PMM-SA3D-727-U-SLR

### Luminous Intensity Polar Plot



— Vertical Plane Through 270-Deg Lateral    - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P368064

CATALOG NUMBER: PMM-SA3D-727-U-SLR

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2761.9	0.0	2761.9
	% Fixture	19.4	0.0	19.4
<b>Street Side</b>	Lumens	11498.1	0.0	11498.1
	% Fixture	80.6	0.0	80.6
<b>Total</b>	Lumens	14260.0	0.0	14260.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.4	1.2
10°-20°	501.1	3.5
20°-30°	884.5	6.2
30°-40°	1377.6	9.7
40°-50°	2268.0	15.9
50°-60°	3237.2	22.7
60°-70°	3432.6	24.1
70°-80°	1896.0	13.3
80°-90°	490.5	3.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	14260.0	100.0
0°-180°	14260.0	100.0

**Coefficient of Utilization**



REPORT NUMBER: P368064


CATALOG NUMBER: PMM-SA3D-727-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1091.1	7.7			
FM (30°-60°)	5528.1	38.8			
FH (60°-80°)	4462.0	31.3			G2/5000
FVH (80°-90°)	416.9	2.9			G3/500
BL (0°-30°)	466.9	3.3	B1/500		
BM (30°-60°)	1354.8	9.5	B2/2500		
BH (60°-80°)	866.6	6.1	B2/1000		G2/1000
BVH (80°-90°)	73.6	0.5			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G3**

Type IV Short





REPORT NUMBER: P368064

CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1
2.5°	2014.2	2026.6	2038.4	2014.9	1991.3	1967.1	1943.6	1908.3	1872.3	1837.0	1801.0
5°	2419.1	2373.4	2327.0	2308.3	2290.3	2271.7	2253.0	2235.7	2218.4	2200.4	2183.1
7.5°	2545.8	2480.7	2414.9	2387.3	2359.6	2331.2	2303.5	2241.2	2178.9	2115.9	2053.6
10°	2406.6	2338.8	2270.3	2243.3	2215.6	2188.6	2160.9	2084.8	2009.3	1933.2	1857.1
12.5°	2518.8	2449.5	2379.6	2293.8	2208.0	2121.5	2035.6	1993.4	1951.2	1908.3	1866.1
15°	2626.7	2533.3	2439.2	2353.3	2267.5	2181.0	2095.2	2010.7	1926.3	1841.8	1757.4
17.5°	3021.3	2865.5	2709.8	2554.8	2399.0	2244.0	2088.2	1990.6	1892.4	1794.8	1696.5
20°	3502.3	3285.7	3068.3	2833.0	2597.0	2361.6	2125.6	2002.4	1879.9	1756.7	1633.5
22.5°	4074.7	3801.3	3527.9	3231.0	2934.1	2636.4	2339.5	2160.9	1982.3	1803.1	1624.5
25°	4529.5	4266.5	4003.4	3626.9	3250.4	2873.8	2497.3	2294.5	2091.7	1888.2	1685.4
27.5°	4971.1	4552.3	4132.9	3701.7	3271.1	2839.9	2408.7	2221.1	2033.6	1846.0	1658.4
30°	5344.1	5011.9	4679.7	4117.0	3554.2	2990.8	2428.1	2197.6	1967.1	1736.6	1506.1
32.5°	5890.3	5416.1	4941.3	4354.4	3767.4	3180.5	2593.5	2298.7	2003.8	1708.9	1414.1
35°	6529.1	6036.3	5543.5	4817.4	4092.0	3366.0	2639.9	2327.7	2014.9	1702.7	1389.9
37.5°	7720.3	6851.7	5982.3	5189.8	4397.3	3604.1	2811.5	2448.9	2086.2	1722.8	1360.1
40°	8377.2	7574.3	6771.4	5783.7	4796.0	3807.6	2819.8	2448.9	2077.2	1706.2	1334.5
42.5°	9252.8	8237.4	7221.3	6153.3	5086.0	4018.0	2950.0	2538.8	2127.7	1715.9	1304.7
45°	9786.4	8654.7	7522.4	6381.0	5239.6	4098.3	2956.9	2539.5	2122.2	1704.8	1287.4
47.5°	10130.4	9043.7	7956.4	6727.8	5499.2	4269.9	3041.3	2598.4	2154.7	1711.7	1268.0
50°	10456.4	9380.1	8303.1	7027.5	5752.5	4476.9	3201.2	2717.4	2233.6	1749.1	1265.3
52.5°	10856.5	9865.3	8873.5	7505.1	6136.0	4767.6	3398.5	2871.8	2345.0	1818.3	1291.6
55°	11438.6	10462.0	9484.6	8015.9	6546.4	5077.7	3608.2	3023.3	2439.2	1854.3	1269.4
57.5°	11815.8	10825.3	9834.9	8337.0	6839.2	5340.7	3842.9	3195.0	2547.1	1898.6	1250.7
60°	11690.5	10668.9	9646.6	8218.7	6790.8	5362.8	3934.9	3235.1	2536.1	1836.3	1136.5
62.5°	11136.8	10050.8	8964.8	7685.7	6407.3	5128.2	3849.1	3137.6	2426.7	1715.2	1003.6
65°	10363.0	9240.3	8116.9	6963.1	5809.3	4655.5	3501.6	2855.8	2209.4	1563.6	917.1
67.5°	9413.3	8242.9	7071.8	6050.1	5028.5	4006.2	2984.6	2444.7	1905.5	1365.6	825.7
70°	8222.1	7071.8	5921.4	5037.5	4153.6	3269.8	2385.9	1979.6	1574.0	1167.7	761.4
72.5°	6608.7	5616.2	4623.6	3928.0	3232.4	2536.8	1841.1	1558.7	1277.0	994.6	712.2
75°	4700.4	4117.0	3533.5	2992.2	2450.9	1909.0	1367.7	1185.0	1002.2	819.5	636.8
77.5°	3340.4	2996.3	2652.3	2228.1	1803.8	1379.5	955.2	847.9	741.3	634.0	526.7
80°	2469.6	2182.4	1895.1	1575.4	1255.6	935.8	616.0	563.4	511.5	458.9	406.3
82.5°	1625.9	1496.4	1366.3	1113.0	859.7	606.3	353.0	333.6	314.2	294.9	275.5
85°	728.1	769.0	809.1	654.1	498.4	343.3	187.6	178.6	169.6	160.6	151.6
87.5°	69.9	103.1	136.4	117.0	96.9	77.5	57.4	56.8	56.8	56.1	55.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064  
 CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P368064

CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1
2.5°	1810.7	1820.4	1830.1	1839.8	1829.4	1819.0	1807.9	1797.5	1784.4	1771.2	1757.4
5°	2154.0	2124.2	2095.2	2065.4	2021.1	1976.8	1931.8	1887.5	1882.0	1875.7	1870.2
7.5°	1999.0	1945.0	1890.3	1835.6	1766.4	1697.9	1628.6	1559.4	1538.7	1517.9	1497.1
10°	1820.4	1783.0	1746.3	1708.9	1666.0	1623.1	1579.5	1536.6	1479.8	1422.4	1365.6
12.5°	1805.1	1744.2	1682.6	1621.7	1595.4	1569.1	1542.8	1516.5	1466.7	1416.8	1366.3
15°	1708.2	1658.4	1609.3	1559.4	1521.4	1483.3	1445.2	1407.2	1367.0	1326.2	1286.0
17.5°	1639.7	1583.0	1526.2	1469.5	1425.8	1382.2	1337.9	1294.3	1245.9	1196.7	1148.3
20°	1568.4	1504.1	1439.0	1373.9	1318.6	1263.9	1208.5	1153.1	1099.8	1047.2	993.9
22.5°	1539.4	1454.2	1369.1	1284.0	1225.8	1167.0	1108.8	1050.0	1000.9	951.7	902.6
25°	1583.7	1482.6	1380.9	1279.1	1200.9	1122.0	1043.8	964.9	924.0	883.2	841.7
27.5°	1531.7	1404.4	1277.7	1150.4	1066.6	982.2	898.4	814.0	807.7	801.5	794.6
30°	1372.5	1239.0	1105.4	971.8	895.0	817.4	740.6	663.1	648.6	633.3	618.8
32.5°	1277.7	1141.4	1005.0	868.7	800.1	730.9	662.4	593.2	576.6	560.0	543.3
35°	1241.7	1093.6	945.5	797.4	738.5	679.7	620.9	562.0	550.3	539.2	527.4
37.5°	1212.7	1065.9	918.5	771.1	714.3	657.5	600.1	543.3	534.3	525.3	516.3
40°	1185.0	1036.2	886.7	737.1	686.6	636.8	586.3	535.7	530.2	524.7	518.4
42.5°	1160.1	1015.4	870.0	725.4	680.4	636.1	591.1	546.1	540.6	535.0	529.5
45°	1146.2	1005.0	863.8	722.6	690.1	657.5	624.3	591.8	578.6	565.5	551.6
47.5°	1135.8	1003.6	871.4	739.2	705.3	671.4	637.5	603.6	591.8	580.0	567.6
50°	1137.9	1011.2	883.9	756.5	715.7	674.2	633.3	591.8	590.4	589.0	587.6
52.5°	1156.6	1022.3	887.3	752.4	708.1	663.8	618.8	574.5	583.5	591.8	600.8
55°	1129.6	989.8	849.3	709.5	667.2	625.7	583.5	541.3	553.0	564.1	575.9
57.5°	1099.1	947.6	796.0	644.4	612.6	580.7	548.2	516.3	528.8	542.0	554.4
60°	998.1	859.7	721.2	582.8	561.3	539.9	518.4	497.0	502.5	508.0	513.6
62.5°	887.3	770.4	654.1	537.1	520.5	503.2	486.6	469.3	469.3	470.0	470.0
65°	816.7	716.4	616.0	515.7	497.0	478.3	458.9	440.2	437.4	434.7	431.9
67.5°	746.1	667.2	587.6	508.0	481.0	454.7	427.8	400.8	397.3	394.5	391.1
70°	690.8	620.2	549.6	479.0	448.5	418.8	388.3	357.8	355.1	353.0	350.2
72.5°	645.8	580.0	513.6	447.1	415.3	382.8	350.9	318.4	316.3	314.2	311.5
75°	578.0	519.8	461.0	402.1	371.0	340.5	309.4	278.2	275.5	273.4	270.6
77.5°	478.3	429.1	380.7	331.5	307.3	283.8	259.6	235.3	233.9	232.6	230.5
80°	368.2	330.2	291.4	253.3	237.4	220.8	204.9	188.3	187.6	186.9	185.5
82.5°	252.6	229.8	207.0	184.1	172.3	159.9	148.1	135.7	136.4	137.0	137.7
85°	144.0	135.7	128.0	119.7	110.1	101.1	91.4	81.7	83.8	85.8	87.2
87.5°	52.6	49.8	47.1	44.3	39.5	35.3	30.5	25.6	27.0	29.1	30.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064  
 CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064

CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1
2.5°	1744.2	1723.5	1702.7	1681.9	1661.2	1618.3	1576.0	1533.1	1490.2	1516.5	1543.5
5°	1864.0	1828.7	1792.7	1757.4	1721.4	1701.3	1681.3	1661.2	1641.1	1651.5	1662.6
7.5°	1476.4	1455.6	1434.2	1413.4	1391.9	1382.9	1374.6	1365.6	1356.6	1382.2	1407.8
10°	1308.2	1279.1	1250.0	1220.3	1191.2	1173.9	1156.6	1139.3	1122.0	1128.9	1135.8
12.5°	1316.5	1273.6	1230.7	1187.7	1144.8	1119.2	1093.6	1068.0	1042.4	1048.6	1054.8
15°	1245.2	1200.9	1156.6	1112.3	1068.0	1038.2	1007.8	978.0	947.6	937.2	926.1
17.5°	1099.1	1050.7	1002.2	953.8	905.3	885.3	865.2	845.1	825.1	814.0	802.9
20°	940.6	895.7	850.7	805.7	760.7	746.8	733.0	718.5	704.6	697.7	690.1
22.5°	853.4	825.7	797.4	769.7	741.3	725.4	710.2	694.2	678.3	670.7	662.4
25°	800.8	806.4	812.6	818.1	823.7	816.7	809.1	802.2	794.6	797.4	799.4
27.5°	788.4	800.1	812.6	824.4	836.1	842.4	848.6	854.8	861.0	863.1	865.2
30°	603.6	609.8	615.3	621.6	627.1	644.4	661.7	678.3	695.6	722.6	750.3
32.5°	526.7	524.7	522.6	519.8	517.7	521.9	526.0	529.5	533.7	543.3	553.7
35°	515.7	510.8	505.3	500.4	494.9	497.0	499.0	501.1	503.2	510.8	518.4
37.5°	507.4	505.3	503.9	501.8	499.7	504.6	508.7	513.6	517.7	524.0	530.2
40°	512.9	512.2	511.5	510.1	509.4	512.2	515.0	517.7	520.5	528.8	537.1
42.5°	524.0	524.0	523.3	523.3	522.6	525.3	527.4	530.2	532.3	537.1	542.0
45°	538.5	537.1	536.4	535.0	533.7	533.0	533.0	532.3	531.6	534.3	537.8
47.5°	555.8	551.0	545.4	540.6	535.0	533.7	531.6	530.2	528.1	529.5	530.9
50°	586.3	573.1	560.6	547.5	534.3	530.9	527.4	524.0	520.5	519.8	519.8
52.5°	609.1	589.7	570.3	551.0	531.6	525.3	519.1	512.9	506.7	505.3	504.6
55°	586.9	572.4	558.6	544.0	529.5	520.5	510.8	501.8	492.1	490.0	488.0
57.5°	566.9	557.9	548.9	539.9	530.9	521.9	512.2	503.2	493.5	488.7	483.8
60°	519.1	519.1	519.8	519.8	519.8	510.1	500.4	490.7	481.0	476.2	472.1
62.5°	470.0	477.6	484.5	492.1	499.0	485.9	472.1	458.9	445.1	441.6	438.8
65°	429.1	431.2	434.0	436.1	438.1	427.8	417.4	407.0	396.6	394.5	391.8
67.5°	387.6	386.9	386.2	384.8	384.1	377.9	371.0	364.8	357.8	355.1	352.3
70°	347.5	346.8	346.1	344.7	344.0	338.5	332.9	327.4	321.9	319.8	317.7
72.5°	309.4	308.7	307.3	306.6	305.2	300.4	296.2	291.4	286.6	283.8	281.0
75°	267.9	266.5	265.1	263.7	262.3	258.2	254.0	249.2	245.0	242.3	239.5
77.5°	229.1	227.0	225.0	222.2	220.1	216.6	212.5	209.0	204.9	201.4	198.6
80°	184.8	183.4	182.0	180.0	178.6	175.1	171.7	167.5	164.0	159.9	156.4
82.5°	138.4	137.7	136.4	135.7	134.3	130.8	127.4	123.9	120.4	116.3	112.1
85°	89.3	88.6	87.9	87.2	86.5	83.8	81.7	78.9	76.1	72.0	68.5
87.5°	31.8	30.5	29.8	28.4	27.0	26.3	24.9	24.2	22.8	20.8	18.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064  
 CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064

CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1
2.5°	1569.8	1596.1	1596.8	1596.8	1609.3	1621.0	1596.8	1572.6	1547.7	1523.4	1499.2
5°	1672.9	1683.3	1680.6	1677.1	1661.9	1646.6	1630.7	1614.8	1598.9	1583.0	1583.7
7.5°	1433.5	1459.1	1479.8	1499.9	1480.5	1461.1	1450.8	1440.4	1430.0	1419.6	1418.2
10°	1142.1	1149.0	1157.3	1164.9	1153.1	1140.7	1161.4	1182.2	1202.3	1223.0	1200.2
12.5°	1061.1	1067.3	1052.8	1037.5	1032.7	1027.9	1023.0	1017.5	1012.6	1007.1	1004.3
15°	915.7	904.6	893.6	881.8	879.0	875.6	872.1	868.0	864.5	860.4	847.9
17.5°	791.8	780.8	762.1	742.7	735.1	726.8	724.7	722.6	719.8	717.8	706.0
20°	683.2	675.5	670.7	665.2	657.5	649.9	642.3	634.7	626.4	618.8	607.7
22.5°	654.8	646.5	640.2	633.3	631.9	630.6	616.7	602.2	588.3	573.8	567.6
25°	802.2	804.3	766.2	727.5	724.0	720.5	695.6	670.0	645.1	619.5	598.0
27.5°	866.6	868.7	867.3	865.9	854.8	843.0	800.8	757.9	715.7	672.8	642.3
30°	777.3	804.3	814.7	825.1	817.4	809.1	764.8	721.2	676.9	632.6	612.6
32.5°	563.4	573.1	590.4	607.0	616.0	624.3	610.5	596.6	582.8	569.0	565.5
35°	525.3	533.0	536.4	539.9	534.3	528.8	518.4	508.0	497.0	486.6	484.5
37.5°	535.7	542.0	548.9	555.8	540.6	524.7	512.9	501.8	490.0	478.3	468.6
40°	545.4	553.7	557.9	562.0	546.8	531.6	517.0	503.2	488.7	474.1	464.4
42.5°	546.8	551.6	559.3	566.9	545.4	523.3	510.1	496.3	483.1	469.3	459.6
45°	540.6	543.3	550.3	557.2	532.3	506.7	494.9	482.4	470.7	458.2	449.9
47.5°	531.6	533.0	538.5	543.3	517.0	490.0	479.0	467.9	456.1	445.1	436.8
50°	519.1	518.4	522.6	526.0	499.0	472.1	461.0	450.6	439.5	428.4	421.5
52.5°	503.2	501.8	506.0	509.4	481.0	452.7	443.0	434.0	424.3	414.6	409.1
55°	485.2	483.1	486.6	490.0	462.4	434.0	425.7	416.7	408.4	399.4	394.5
57.5°	478.3	473.4	475.5	477.6	446.4	415.3	407.0	398.7	390.4	382.1	378.6
60°	467.2	462.4	464.4	465.8	432.6	398.7	391.1	382.8	375.1	366.8	363.4
62.5°	435.4	431.9	434.7	437.4	407.7	377.2	370.3	364.1	357.2	350.2	345.4
65°	389.7	386.9	392.5	398.0	372.4	346.8	342.6	338.5	333.6	329.5	324.6
67.5°	349.5	346.8	352.3	357.8	339.2	320.5	316.3	312.2	308.0	303.9	301.1
70°	315.6	313.5	318.4	323.2	307.3	291.4	287.2	283.8	279.6	275.5	273.4
72.5°	277.6	274.8	281.0	286.6	273.4	259.6	256.1	251.9	248.5	244.3	242.9
75°	236.7	233.9	239.5	244.3	235.3	225.6	222.2	218.7	215.3	211.8	211.1
77.5°	195.2	191.7	197.3	202.1	196.6	190.3	187.6	184.1	181.3	177.9	177.9
80°	152.3	148.1	152.3	155.7	153.7	151.6	149.5	146.7	144.7	141.9	142.6
82.5°	108.0	103.8	105.9	108.0	109.4	110.7	110.7	110.7	110.7	110.7	110.7
85°	64.4	60.2	60.9	61.6	63.7	65.8	66.4	67.1	67.8	68.5	69.2
87.5°	16.6	14.5	13.2	11.1	13.2	14.5	15.9	16.6	18.0	18.7	18.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064  
 CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064  
 CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1
2.5°	1475.0	1450.1	1425.8	1441.1	1455.6	1470.8	1485.4	1486.1	1486.1	1486.8	1486.8
5°	1585.0	1585.7	1586.4	1571.9	1558.0	1543.5	1529.0	1521.4	1513.7	1505.4	1497.8
7.5°	1416.2	1414.8	1412.7	1398.9	1385.0	1371.2	1357.3	1324.1	1290.2	1257.0	1223.0
10°	1176.7	1153.8	1130.3	1124.8	1119.9	1114.4	1108.8	1099.8	1091.5	1082.5	1073.5
12.5°	1001.6	998.8	996.0	981.5	966.9	951.7	937.2	937.2	937.2	937.2	937.2
15°	834.7	822.3	809.1	802.2	794.6	787.7	780.1	776.6	773.1	769.7	766.2
17.5°	693.5	681.8	669.3	667.9	666.5	665.2	663.8	660.3	656.9	653.4	649.9
20°	596.6	585.6	574.5	578.6	582.8	586.3	590.4	586.9	583.5	579.3	575.9
22.5°	560.6	554.4	547.5	544.0	540.6	536.4	533.0	533.0	533.7	533.7	533.7
25°	577.3	555.8	534.3	524.0	513.6	502.5	492.1	488.0	484.5	480.4	476.2
27.5°	611.9	580.7	550.3	532.3	514.3	496.3	478.3	470.7	462.4	454.7	446.4
30°	591.8	571.7	551.0	530.2	509.4	488.7	467.9	458.2	448.5	438.1	428.4
32.5°	562.0	557.9	554.4	535.0	515.7	495.6	476.2	472.1	468.6	464.4	460.3
35°	481.7	479.7	476.9	472.1	467.2	462.4	457.5	452.0	446.4	440.9	435.4
37.5°	459.6	449.9	440.2	438.1	436.1	434.0	431.9	429.8	427.8	425.0	422.9
40°	454.7	445.1	435.4	431.9	428.4	424.3	420.8	421.5	422.9	423.6	424.3
42.5°	449.2	439.5	429.1	426.4	423.6	420.8	418.1	418.8	420.1	420.8	421.5
45°	442.3	434.0	425.7	420.8	416.7	411.8	407.0	411.1	415.3	418.8	422.9
47.5°	428.4	419.4	411.1	408.4	405.6	402.1	399.4	403.5	407.7	411.1	415.3
50°	413.9	407.0	399.4	398.7	398.0	396.6	395.9	398.7	401.5	404.2	407.0
52.5°	402.8	397.3	391.1	391.1	390.4	390.4	389.7	392.5	395.2	397.3	400.1
55°	390.4	385.5	380.7	381.4	382.8	383.5	384.1	386.9	390.4	393.1	395.9
57.5°	374.5	371.0	366.8	369.6	371.7	374.5	376.5	378.6	381.4	383.5	385.5
60°	359.2	355.8	351.6	354.4	357.8	360.6	363.4	365.5	367.5	369.6	371.7
62.5°	340.5	335.0	330.2	334.3	337.8	341.9	345.4	346.8	348.8	350.2	351.6
65°	320.5	315.6	310.8	313.5	316.3	318.4	321.2	323.2	325.3	327.4	329.5
67.5°	297.6	294.9	291.4	293.5	295.6	297.6	299.7	300.4	300.4	301.1	301.1
70°	270.6	268.6	265.8	267.2	269.2	270.6	272.0	272.0	272.0	271.3	271.3
72.5°	242.3	240.9	239.5	240.2	241.6	242.3	242.9	242.3	241.6	240.9	240.2
75°	210.4	209.7	209.0	209.7	211.1	211.8	212.5	211.8	210.4	209.7	208.3
77.5°	178.6	178.6	178.6	178.6	179.3	179.3	179.3	177.9	176.5	175.1	173.7
80°	143.3	144.0	144.7	144.7	144.7	144.7	144.7	143.3	141.9	139.8	138.4
82.5°	110.7	110.7	110.7	110.7	111.4	111.4	111.4	108.0	105.2	101.7	98.3
85°	69.2	69.9	69.9	70.6	71.3	71.3	72.0	67.1	63.0	58.1	53.3
87.5°	18.7	18.7	18.7	18.7	18.7	18.0	18.0	13.8	9.0	4.8	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064  
 CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P368064

CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1
2.5°	1490.9	1495.1	1498.5	1502.7	1503.4	1504.1	1504.1	1504.8	1490.2	1475.7	1460.5
5°	1508.2	1517.9	1528.3	1538.0	1535.9	1533.8	1531.7	1529.7	1525.5	1522.1	1517.9
7.5°	1215.4	1208.5	1200.9	1193.3	1199.5	1205.7	1212.0	1218.2	1221.0	1223.7	1225.8
10°	1056.2	1038.9	1021.6	1004.3	994.6	984.2	974.6	964.2	962.8	962.1	960.7
12.5°	919.2	900.5	882.5	863.8	858.3	852.0	846.5	840.3	845.8	851.4	856.2
15°	758.6	751.7	744.1	736.5	742.7	748.9	755.1	761.4	766.9	771.8	777.3
17.5°	646.5	643.7	640.2	636.8	642.3	648.6	654.1	659.6	672.1	684.5	697.0
20°	573.1	571.0	568.3	565.5	563.4	560.6	558.6	555.8	573.8	591.1	609.1
22.5°	529.5	525.3	521.2	517.0	517.7	518.4	518.4	519.1	533.7	548.9	563.4
25°	474.8	473.4	472.1	470.7	474.8	479.0	482.4	486.6	499.7	512.9	525.3
27.5°	447.1	447.8	448.5	449.2	454.7	461.0	466.5	472.1	481.0	490.0	499.0
30°	431.9	436.1	439.5	443.0	445.1	447.1	449.2	451.3	460.3	468.6	477.6
32.5°	454.7	449.2	443.0	437.4	440.2	443.7	446.4	449.2	457.5	465.8	474.1
35°	433.3	430.5	428.4	425.7	429.1	432.6	435.4	438.8	446.4	453.4	461.0
37.5°	422.2	421.5	420.8	420.1	422.2	424.3	425.7	427.8	434.7	441.6	447.8
40°	421.5	418.1	415.3	411.8	413.9	416.0	417.4	419.4	427.8	436.1	444.4
42.5°	417.4	413.2	408.4	404.2	406.3	409.1	411.1	413.2	422.2	430.5	439.5
45°	416.7	410.4	403.5	397.3	400.1	402.8	405.6	408.4	415.3	422.2	428.4
47.5°	409.1	402.8	396.6	390.4	391.8	393.1	393.8	395.2	401.5	407.0	413.2
50°	402.8	398.0	393.8	389.0	386.9	385.5	383.5	381.4	386.2	391.1	395.9
52.5°	395.2	390.4	384.8	380.0	377.2	374.5	371.7	368.9	373.1	376.5	380.7
55°	390.4	384.1	378.6	372.4	368.9	365.5	362.0	358.5	361.3	363.4	366.2
57.5°	380.0	374.5	368.2	362.7	358.5	354.4	349.5	345.4	346.8	348.2	349.5
60°	366.2	359.9	354.4	348.2	343.3	338.5	332.9	328.1	328.8	330.2	330.9
62.5°	346.1	340.5	334.3	328.8	323.2	318.4	312.9	307.3	308.7	309.4	310.8
65°	323.9	317.7	312.2	305.9	301.1	296.2	290.7	285.9	287.2	288.6	289.3
67.5°	296.9	292.1	287.9	283.1	278.9	274.1	269.9	265.1	265.8	266.5	267.2
70°	267.9	263.7	260.3	256.1	252.6	249.2	245.7	242.3	242.3	242.9	242.9
72.5°	236.7	233.3	229.8	226.3	222.9	220.1	216.6	213.2	214.6	216.0	216.6
75°	204.9	202.1	198.6	195.2	192.4	189.7	186.2	183.4	184.8	186.2	186.9
77.5°	171.7	169.6	166.8	164.7	162.0	159.2	155.7	153.0	154.4	155.7	156.4
80°	137.0	135.7	133.6	132.2	129.4	126.7	123.9	121.1	121.8	121.8	122.5
82.5°	99.0	99.7	99.7	100.4	98.3	95.5	93.4	90.7	90.7	90.7	90.0
85°	55.4	58.1	60.2	62.3	60.2	58.1	56.1	54.0	53.3	53.3	52.6
87.5°	2.1	3.5	5.5	6.9	6.2	5.5	4.2	3.5	4.2	4.8	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064  
 CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064

CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1
2.5°	1445.9	1457.7	1469.5	1481.2	1493.0	1511.0	1529.0	1547.7	1566.4	1556.0	1544.9
5°	1513.7	1520.7	1528.3	1535.2	1542.1	1562.2	1581.6	1605.8	1629.3	1626.6	1623.1
7.5°	1228.6	1238.3	1248.0	1257.0	1266.6	1297.1	1327.6	1353.2	1378.8	1375.3	1371.2
10°	959.3	979.4	1000.2	1020.2	1040.3	1065.2	1089.5	1110.9	1132.4	1168.4	1203.7
12.5°	861.7	892.9	924.0	955.2	986.3	1004.3	1021.6	1049.3	1077.0	1096.4	1116.5
15°	782.1	811.2	840.3	869.3	898.4	899.8	901.2	930.3	959.3	975.9	991.9
17.5°	709.5	725.4	741.3	756.5	772.4	766.9	761.4	775.2	788.4	795.3	802.9
20°	626.4	637.5	648.6	659.6	670.7	678.3	685.2	693.5	701.2	694.2	686.6
22.5°	578.0	594.6	611.9	628.5	645.1	649.9	654.1	649.2	644.4	642.3	640.2
25°	538.5	558.6	579.3	599.4	619.5	629.2	638.9	643.0	646.5	638.9	631.2
27.5°	508.0	532.3	555.8	580.0	603.6	620.9	638.2	643.0	647.2	641.6	635.4
30°	485.9	512.2	538.5	564.8	591.1	617.4	643.0	665.9	688.0	685.9	683.9
32.5°	482.4	500.4	518.4	536.4	554.4	571.0	586.9	588.3	589.0	583.5	577.3
35°	467.9	479.7	491.4	503.2	515.0	525.3	535.0	533.7	532.3	526.7	521.2
37.5°	454.7	466.5	479.0	490.7	502.5	520.5	537.8	534.3	530.2	524.7	519.1
40°	452.7	465.8	479.0	491.4	504.6	521.2	537.8	534.3	530.9	524.0	517.0
42.5°	447.8	461.0	473.4	486.6	499.0	519.1	538.5	532.3	525.3	519.8	514.3
45°	435.4	447.1	458.9	470.7	482.4	503.9	525.3	517.7	510.1	508.0	505.3
47.5°	418.8	430.5	442.3	454.1	465.8	487.3	508.0	501.8	494.9	494.2	492.8
50°	400.8	411.8	423.6	434.7	445.7	467.2	488.0	482.4	476.9	477.6	477.6
52.5°	384.1	394.5	404.2	414.6	424.3	445.7	466.5	462.4	457.5	458.9	459.6
55°	368.2	376.5	384.8	393.1	401.5	422.2	443.0	436.8	430.5	432.6	434.7
57.5°	350.9	357.8	364.8	371.0	377.9	398.7	418.8	411.8	404.2	407.7	410.4
60°	331.5	337.8	344.0	349.5	355.8	374.5	392.5	386.2	379.3	384.1	388.3
62.5°	311.5	316.3	321.2	326.0	330.9	348.2	365.5	360.6	355.8	361.3	366.2
65°	290.7	294.2	298.3	301.8	305.2	321.9	337.8	334.3	330.9	335.7	340.5
67.5°	267.9	270.6	274.1	276.9	279.6	294.9	310.1	306.6	302.5	306.6	310.1
70°	242.9	245.7	247.8	250.6	252.6	266.5	280.3	275.5	269.9	274.1	277.6
72.5°	218.0	219.4	221.5	222.9	224.3	234.6	245.0	240.9	236.7	240.9	244.3
75°	188.3	189.7	191.0	192.4	193.8	202.8	211.1	206.3	200.7	204.9	209.0
77.5°	157.8	158.5	159.9	160.6	161.3	167.5	173.0	168.2	162.7	167.5	172.3
80°	122.5	123.2	123.9	123.9	124.6	126.7	128.7	125.3	121.1	127.4	133.6
82.5°	90.0	89.3	89.3	88.6	87.9	87.9	87.2	85.1	82.4	87.9	93.4
85°	51.9	51.2	49.8	49.1	47.8	45.7	43.6	42.9	42.2	47.1	51.9
87.5°	5.5	4.8	3.5	2.8	1.4	0.7	0.0	0.0	0.0	2.8	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064  
 CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064

CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1
2.5°	1534.5	1523.4	1513.1	1502.7	1492.3	1481.9	1501.3	1520.7	1540.1	1559.4	1576.7
5°	1620.3	1616.9	1607.9	1599.6	1590.6	1581.6	1586.4	1592.0	1596.8	1601.7	1612.0
7.5°	1367.7	1363.6	1382.9	1401.6	1421.0	1439.7	1444.5	1448.7	1453.5	1457.7	1454.9
10°	1239.7	1275.0	1284.0	1292.3	1301.3	1309.6	1323.4	1337.2	1350.4	1364.2	1371.9
12.5°	1135.8	1155.2	1187.1	1219.6	1251.4	1283.3	1304.0	1324.8	1345.6	1366.3	1409.2
15°	1008.5	1024.4	1048.6	1072.8	1097.1	1121.3	1151.1	1181.5	1211.3	1241.0	1288.1
17.5°	809.8	816.7	834.7	852.7	870.0	888.0	928.2	967.6	1007.8	1047.2	1101.2
20°	679.7	672.1	672.1	672.8	672.8	672.8	712.9	752.4	792.5	832.0	903.3
22.5°	637.5	635.4	627.8	619.5	611.9	603.6	624.3	645.8	666.5	687.3	745.5
25°	622.9	615.3	605.6	595.9	586.3	576.6	589.7	602.9	616.0	629.2	674.9
27.5°	629.9	623.6	628.5	632.6	637.5	641.6	645.8	649.9	654.1	658.2	674.2
30°	681.8	679.7	687.3	694.2	701.8	708.8	699.1	690.1	680.4	670.7	676.2
32.5°	571.7	565.5	562.7	560.0	557.2	554.4	553.7	553.0	551.6	551.0	563.4
35°	515.7	510.1	506.0	501.8	497.0	492.8	494.9	496.3	498.4	499.7	513.6
37.5°	513.6	508.0	503.2	498.4	492.8	488.0	490.0	492.8	494.9	497.0	507.4
40°	510.1	503.2	500.4	497.7	494.9	492.1	493.5	494.9	495.6	497.0	504.6
42.5°	508.0	502.5	501.1	499.7	498.4	497.0	498.4	499.7	500.4	501.8	510.8
45°	503.2	500.4	501.8	503.2	504.6	506.0	506.0	506.0	506.0	506.0	515.7
47.5°	492.1	490.7	494.9	499.0	503.2	507.4	514.3	521.2	527.4	534.3	536.4
50°	478.3	478.3	485.2	492.1	498.4	505.3	521.9	537.8	554.4	570.3	560.0
52.5°	461.0	461.7	472.1	481.7	492.1	501.8	517.0	532.3	546.8	562.0	546.8
55°	436.1	438.1	451.3	463.7	476.9	489.4	501.1	512.9	524.7	536.4	520.5
57.5°	413.9	416.7	430.5	443.7	457.5	470.7	477.6	485.2	492.1	499.0	488.7
60°	393.1	397.3	415.3	433.3	450.6	468.6	463.1	457.5	451.3	445.7	445.1
62.5°	371.7	376.5	393.1	409.8	425.7	442.3	434.0	425.7	416.7	408.4	411.8
65°	344.7	349.5	357.2	364.8	371.7	379.3	378.6	378.6	377.9	377.2	384.1
67.5°	314.2	317.7	322.5	326.7	331.5	335.7	338.5	341.9	344.7	347.5	355.8
70°	281.7	285.2	290.0	294.2	299.0	303.2	306.6	310.1	312.9	316.3	324.6
72.5°	248.5	251.9	256.8	261.6	265.8	270.6	273.4	276.2	278.2	281.0	287.9
75°	213.2	217.3	222.2	226.3	231.2	235.3	237.4	239.5	241.6	243.6	249.9
77.5°	177.2	182.0	186.9	191.7	196.6	201.4	202.1	202.8	203.5	204.2	209.7
80°	139.1	145.4	150.2	155.0	159.9	164.7	164.7	164.7	164.7	164.7	167.5
82.5°	99.0	104.5	110.1	114.9	120.4	125.3	125.3	124.6	124.6	123.9	123.9
85°	56.8	61.6	65.1	69.2	72.7	76.1	76.1	76.1	75.4	75.4	74.1
87.5°	9.0	11.8	13.2	15.2	16.6	18.0	17.3	17.3	16.6	15.9	13.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064  
 CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064

CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1
2.5°	1594.0	1611.3	1628.6	1625.9	1623.1	1620.3	1617.6	1628.0	1637.6	1648.0	1657.7
5°	1621.7	1632.1	1641.8	1649.4	1657.0	1664.6	1672.3	1707.6	1742.2	1777.5	1812.1
7.5°	1452.1	1448.7	1445.9	1478.4	1511.7	1544.2	1576.7	1621.7	1666.7	1711.7	1756.7
10°	1379.5	1387.1	1394.7	1407.8	1421.7	1434.8	1448.0	1492.3	1536.6	1580.9	1625.2
12.5°	1451.5	1494.4	1536.6	1547.0	1558.0	1568.4	1578.8	1587.8	1596.8	1605.1	1614.1
15°	1335.2	1382.2	1429.3	1456.3	1483.3	1509.6	1536.6	1604.4	1671.6	1739.4	1806.5
17.5°	1154.5	1208.5	1261.8	1328.3	1394.7	1461.1	1527.6	1589.9	1652.2	1713.8	1776.1
20°	974.6	1045.2	1116.5	1189.1	1261.1	1333.8	1405.8	1466.7	1527.6	1587.8	1648.7
22.5°	802.9	861.0	918.5	1007.1	1095.0	1183.6	1271.5	1385.0	1497.8	1611.3	1724.2
25°	719.8	765.5	810.5	901.9	993.2	1083.9	1175.3	1322.7	1469.5	1616.9	1763.6
27.5°	690.8	706.7	722.6	805.7	888.0	971.1	1053.5	1212.7	1371.9	1530.4	1689.6
30°	681.8	687.3	692.8	757.9	823.0	888.0	953.1	1110.2	1268.0	1425.2	1582.3
32.5°	575.2	587.6	599.4	663.1	726.1	789.8	852.7	1011.2	1169.1	1327.6	1485.4
35°	527.4	541.3	555.1	617.4	679.7	741.3	803.6	970.4	1137.9	1304.7	1471.5
37.5°	517.7	528.1	538.5	609.1	679.7	750.3	820.9	989.8	1158.7	1327.6	1496.4
40°	512.9	520.5	528.1	596.6	665.9	734.4	802.9	980.1	1156.6	1333.8	1510.3
42.5°	519.1	528.1	536.4	598.7	660.3	722.6	784.2	967.6	1150.4	1333.8	1516.5
45°	524.7	534.3	543.3	601.5	659.6	717.8	775.9	971.8	1167.0	1362.9	1558.0
47.5°	537.8	539.9	541.3	591.8	641.6	692.2	742.0	941.3	1140.7	1339.3	1538.7
50°	548.9	538.5	527.4	580.0	631.9	684.5	736.5	925.4	1114.4	1302.6	1491.6
52.5°	531.6	515.7	500.4	557.2	613.9	670.0	726.8	915.7	1105.4	1294.3	1483.3
55°	505.3	489.4	473.4	530.9	588.3	645.8	703.2	891.5	1080.5	1268.7	1457.0
57.5°	479.0	468.6	458.2	505.3	553.0	600.1	647.2	851.4	1054.8	1259.0	1462.5
60°	444.4	443.0	442.3	479.0	516.3	553.0	589.7	789.8	989.1	1189.1	1388.5
62.5°	414.6	418.1	420.8	450.6	480.4	509.4	539.2	732.3	926.1	1119.2	1312.3
65°	391.8	398.7	405.6	439.5	473.4	506.7	540.6	702.5	864.5	1026.5	1188.4
67.5°	364.1	372.4	380.7	425.0	469.3	513.6	557.9	691.5	825.1	958.6	1092.2
70°	332.2	340.5	348.2	404.9	461.0	517.7	573.8	692.2	811.2	929.6	1047.9
72.5°	294.9	301.8	308.7	369.6	430.5	491.4	552.3	652.7	753.1	852.7	953.1
75°	256.8	263.0	269.2	321.9	374.5	427.1	479.7	557.2	634.0	711.5	788.4
77.5°	214.6	220.1	225.0	260.3	295.6	330.9	366.2	425.7	484.5	544.0	602.9
80°	170.3	173.0	175.8	196.6	216.6	237.4	257.5	296.9	336.4	375.1	414.6
82.5°	124.6	124.6	124.6	137.7	151.6	164.7	177.9	198.0	217.3	237.4	256.8
85°	72.7	70.6	69.2	78.2	87.2	96.2	105.2	113.5	121.8	130.1	138.4
87.5°	11.8	9.0	6.9	12.5	18.0	23.5	29.1	31.8	35.3	38.1	40.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064  
 CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P368064

CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1
2.5°	1634.2	1611.3	1587.8	1564.3	1598.9	1633.5	1668.1	1702.7	1794.8	1849.4	1852.9
5°	1841.1	1870.2	1899.3	1928.4	1957.4	1986.5	2014.9	2043.9	2193.4	2285.5	2302.8
7.5°	1804.5	1852.9	1900.7	1948.4	2030.8	2113.2	2195.5	2277.9	2404.6	2495.9	2556.1
10°	1684.7	1744.2	1803.8	1863.3	1960.9	2059.2	2156.8	2254.4	2388.6	2509.1	2566.5
12.5°	1708.9	1803.8	1897.9	1992.7	2077.2	2162.3	2246.7	2331.2	2423.9	2469.6	2574.1
15°	1872.3	1938.0	2003.8	2069.6	2196.9	2323.6	2450.9	2577.6	2630.2	2734.7	2828.8
17.5°	1897.2	2017.6	2138.8	2259.2	2414.9	2570.7	2726.4	2882.1	2979.7	3114.7	3228.2
20°	1819.7	1990.0	2160.9	2331.2	2531.9	2733.3	2934.1	3134.8	3258.7	3372.2	3548.0
22.5°	1912.4	2100.7	2288.3	2476.5	2743.0	3008.8	3275.3	3541.1	3799.9	4053.3	4172.3
25°	2014.9	2266.8	2518.1	2769.3	3102.3	3434.5	3767.4	4099.6	4432.6	4670.0	4807.0
27.5°	1942.9	2195.5	2448.9	2701.5	3113.3	3525.9	3937.7	4349.5	4706.0	4991.8	5109.5
30°	1892.4	2202.4	2512.5	2822.6	3305.7	3788.9	4272.0	4755.1	5084.6	5403.7	5576.7
32.5°	1883.4	2281.4	2678.6	3076.6	3639.4	4201.4	4764.1	5326.2	5544.9	5828.0	6061.2
35°	1908.3	2345.7	2782.5	3219.2	3864.3	4509.4	5153.8	5798.9	6109.7	6390.0	6594.2
37.5°	1984.4	2472.4	2959.7	3447.6	4224.9	5002.9	5780.2	6557.5	7078.7	7591.6	7682.9
40°	2027.3	2545.1	3062.1	3579.1	4483.1	5387.1	6291.0	7195.0	7794.4	8357.1	8395.2
42.5°	2077.9	2639.2	3199.8	3761.2	4763.4	5766.4	6768.6	7770.9	8512.8	9117.8	9135.8
45°	2136.0	2713.3	3291.2	3868.5	4915.0	5960.9	7007.4	8053.3	8950.3	9685.4	9506.1
47.5°	2158.8	2779.7	3399.9	4020.1	5135.8	6250.9	7366.6	8481.7	9286.7	9955.3	9783.6
50°	2167.8	2844.8	3521.0	4197.2	5353.1	6509.7	7665.6	8821.5	9640.4	10292.4	10029.4
52.5°	2223.9	2964.5	3705.1	4445.7	5650.1	6854.4	8058.8	9263.1	10068.8	10695.2	10368.5
55°	2299.3	3141.7	3983.4	4825.7	6072.3	7318.2	8564.8	9810.6	10619.1	11201.9	10797.0
57.5°	2369.3	3276.7	4183.4	5090.1	6381.7	7674.0	8965.5	10257.1	11075.9	11652.5	11260.0
60°	2335.3	3282.2	4229.1	5176.0	6445.4	7714.1	8983.5	10252.2	11181.8	11873.3	11672.5
62.5°	2232.9	3153.5	4073.3	4993.9	6199.0	7403.3	8608.4	9812.7	10900.8	11787.4	11778.4
65°	2035.6	2882.8	3729.3	4576.5	5691.6	6807.4	7922.4	9037.5	10320.1	11397.1	11467.0
67.5°	1795.5	2498.7	3201.9	3905.2	4955.2	6005.2	7055.2	8105.2	9476.3	10664.8	10725.0
70°	1562.9	2078.5	2593.5	3108.5	4030.4	4952.4	5873.6	6795.6	8180.6	9382.9	9438.3
72.5°	1290.2	1627.3	1963.7	2300.7	3047.6	3794.4	4540.6	5287.4	6503.5	7428.2	7740.4
75°	988.4	1188.4	1388.5	1588.5	2192.8	2797.0	3400.6	4004.8	4813.3	5495.7	5847.3
77.5°	706.7	810.5	914.3	1018.2	1531.7	2045.3	2558.2	3071.8	3496.8	3883.7	4121.1
80°	463.7	512.2	561.3	609.8	1036.9	1463.9	1890.3	2317.3	2576.2	2783.9	2903.6
82.5°	281.0	305.2	328.8	353.0	699.1	1045.2	1390.5	1736.6	1884.7	1983.7	2090.3
85°	151.6	164.7	177.9	191.0	413.2	634.7	856.9	1078.4	1092.9	1104.7	1263.2
87.5°	44.3	48.5	51.9	55.4	91.4	128.0	164.0	200.0	124.6	77.5	159.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064  
 CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064

CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1
2.5°	1832.8	1823.8	1814.8	1805.1	1796.1	1758.1	1720.7	1682.6	1644.6	1681.3	1717.2
5°	2282.7	2310.4	2337.4	2365.1	2392.8	2394.9	2396.2	2398.3	2399.7	2406.6	2413.6
7.5°	2606.7	2655.8	2704.3	2753.4	2802.5	2840.6	2878.7	2917.4	2955.5	2920.9	2886.3
10°	2634.4	2738.2	2842.0	2945.8	3049.6	3068.3	3086.3	3105.0	3123.7	3148.6	3172.9
12.5°	2662.0	2788.7	2914.7	3041.3	3168.0	3223.4	3278.1	3333.4	3388.1	3415.1	3441.4
15°	2954.8	3029.6	3103.6	3178.4	3252.4	3290.5	3327.9	3366.0	3404.0	3426.9	3449.0
17.5°	3331.4	3359.0	3386.0	3413.7	3441.4	3467.0	3492.6	3518.2	3543.8	3548.0	3552.2
20°	3674.7	3680.2	3685.0	3690.6	3695.4	3641.4	3588.1	3534.2	3480.2	3489.9	3498.9
22.5°	4189.6	4159.2	4129.4	4099.0	4069.2	3967.4	3866.4	3764.6	3663.6	3620.0	3577.1
25°	4964.8	4887.3	4809.8	4732.3	4654.8	4492.8	4331.5	4169.6	4008.3	3913.5	3819.3
27.5°	5214.7	5045.8	4877.6	4708.7	4539.9	4417.3	4295.5	4173.0	4051.2	3901.0	3750.8
30°	5720.0	5453.5	5187.7	4921.2	4654.8	4536.4	4418.0	4299.0	4180.6	4027.0	3874.0
32.5°	6167.8	5891.0	5614.1	5336.5	5059.7	4835.4	4611.2	4386.9	4162.6	4058.8	3955.0
35°	6686.2	6338.1	5989.9	5641.8	5293.6	5101.2	4909.5	4717.1	4525.3	4368.2	4211.8
37.5°	7441.4	7071.1	6700.8	6329.8	5959.5	5699.2	5439.7	5179.4	4919.9	4833.3	4747.5
40°	8161.2	7723.8	7287.0	6849.6	6412.8	6213.5	6014.2	5814.1	5614.8	5468.7	5322.7
42.5°	8764.1	8331.5	7899.6	7467.0	7035.1	6889.7	6745.1	6599.7	6455.1	6334.6	6214.2
45°	8971.1	8618.1	8265.7	7912.7	7559.7	7508.5	7458.0	7406.8	7356.3	7267.0	7177.7
47.5°	9304.0	8944.1	8584.8	8224.9	7865.0	7883.7	7902.4	7921.7	7940.4	7945.3	7949.4
50°	9499.9	9157.9	8816.7	8474.8	8133.5	8224.2	8314.2	8404.9	8495.5	8701.1	8906.0
52.5°	9785.7	9450.0	9115.0	8779.3	8443.6	8597.3	8750.3	8903.9	9056.9	9344.8	9632.8
55°	10144.3	9823.1	9502.6	9181.5	8861.0	9010.5	9159.3	9308.8	9457.6	9778.1	10098.6
57.5°	10619.8	10275.8	9932.5	9588.5	9245.1	9382.9	9519.9	9657.7	9794.7	10099.3	10403.8
60°	11161.0	10787.3	10413.5	10039.1	9665.3	9703.4	9740.7	9778.8	9816.2	10146.3	10475.8
62.5°	11426.8	11080.7	10735.4	10389.3	10043.2	9937.3	9831.4	9724.8	9618.9	9914.5	10209.3
65°	11196.3	10958.2	10720.8	10482.7	10244.6	10057.7	9871.6	9684.7	9497.8	9682.6	9866.7
67.5°	10462.7	10327.7	10193.4	10058.4	9923.5	9609.9	9296.4	8982.1	8668.6	8681.0	8692.8
70°	9273.5	9237.5	9202.2	9166.2	9130.2	8658.9	8188.2	7716.9	7245.5	7173.5	7101.5
72.5°	7766.7	7790.2	7813.1	7836.6	7860.1	7353.5	6846.8	6340.2	5833.5	5713.8	5594.0
75°	6015.5	6145.7	6275.8	6406.6	6536.7	6052.2	5567.7	5082.5	4598.0	4450.6	4303.1
77.5°	4250.5	4493.5	4735.7	4978.7	5221.6	4783.5	4346.1	3907.9	3469.8	3374.3	3278.8
80°	2963.8	3082.9	3201.9	3321.0	3440.0	3219.9	2999.8	2779.7	2559.6	2585.9	2611.5
82.5°	2158.8	2186.5	2213.5	2241.2	2268.9	2178.9	2088.9	1998.3	1908.3	1976.8	2045.3
85°	1382.9	1481.9	1580.2	1679.2	1777.5	1677.8	1578.1	1477.8	1378.1	1423.8	1469.5
87.5°	309.4	489.4	669.3	850.0	1029.9	933.0	836.8	739.9	643.0	599.4	556.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064  
 CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064

CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1
2.5°	1753.9	1790.6	1779.5	1769.2	1758.1	1747.0	1767.1	1787.2	1807.9	1828.0	1821.1
5°	2421.2	2428.1	2362.3	2297.3	2231.5	2165.8	2206.6	2247.4	2288.3	2329.1	2314.6
7.5°	2851.7	2817.1	2779.0	2740.9	2702.2	2664.1	2655.8	2647.5	2638.5	2630.2	2619.1
10°	3197.8	3222.0	3197.1	3172.9	3147.9	3123.0	3064.9	3006.7	2947.9	2889.8	2865.5
12.5°	3468.4	3495.4	3501.6	3507.2	3513.4	3519.6	3454.6	3390.2	3325.1	3260.1	3201.2
15°	3471.9	3494.7	3514.8	3534.2	3554.2	3573.6	3533.5	3494.0	3453.9	3413.7	3395.0
17.5°	3557.0	3561.2	3544.5	3528.6	3512.0	3496.1	3480.2	3464.9	3449.0	3433.8	3404.0
20°	3508.5	3518.2	3516.2	3514.1	3511.3	3509.2	3510.6	3511.3	3512.7	3513.4	3496.8
22.5°	3533.5	3489.9	3498.9	3507.2	3516.2	3524.5	3549.4	3574.3	3599.9	3624.8	3691.3
25°	3724.5	3629.7	3615.1	3601.3	3586.8	3572.9	3638.0	3702.4	3767.4	3832.5	3940.5
27.5°	3599.9	3449.7	3416.5	3383.3	3350.0	3316.8	3415.8	3514.1	3613.1	3712.0	3822.1
30°	3720.3	3567.4	3494.0	3420.6	3346.6	3273.2	3368.0	3462.2	3557.0	3651.1	3773.0
32.5°	3851.2	3747.3	3698.2	3649.7	3600.6	3552.2	3559.8	3567.4	3575.0	3582.6	3754.3
35°	4054.7	3897.5	3849.1	3800.6	3752.2	3703.7	3784.7	3865.0	3946.0	4026.3	4171.6
37.5°	4661.0	4574.5	4487.3	4400.0	4312.1	4224.9	4272.7	4320.4	4368.2	4416.0	4553.0
40°	5176.6	5030.6	5016.1	5002.2	4987.7	4973.2	4977.3	4980.8	4984.9	4989.1	5106.0
42.5°	6093.1	5972.6	5898.6	5824.5	5750.4	5676.4	5671.5	5666.7	5661.2	5656.3	5744.2
45°	7087.7	6998.4	6943.0	6887.7	6831.6	6776.2	6688.3	6600.4	6511.8	6423.9	6500.7
47.5°	7954.3	7959.1	8059.5	8159.2	8259.5	8359.9	8209.7	8059.5	7909.3	7759.1	7660.1
50°	9111.6	9316.4	9340.7	9364.2	9388.4	9412.7	9157.9	8903.9	8649.2	8394.5	8290.7
52.5°	9921.4	10209.3	10171.9	10135.3	10097.9	10060.5	9913.1	9766.3	9618.9	9471.5	9245.1
55°	10419.7	10740.2	10711.8	10684.1	10655.8	10627.4	10520.1	10412.8	10305.5	10198.2	9949.8
57.5°	10708.4	11012.9	11021.2	11029.5	11037.8	11046.1	11017.8	10989.4	10961.0	10932.6	10609.4
60°	10806.0	11136.1	11139.6	11142.4	11145.8	11148.6	11103.6	11058.6	11012.9	10967.9	10756.8
62.5°	10504.9	10799.7	10812.9	10825.3	10838.5	10851.6	10820.5	10789.4	10758.2	10727.1	10570.6
65°	10051.5	10236.3	10239.8	10242.5	10246.0	10249.5	10170.6	10092.3	10013.4	9934.5	9897.2
67.5°	8705.3	8717.7	8791.1	8864.5	8937.8	9011.2	9017.4	9023.7	9030.6	9036.8	8982.8
70°	7029.6	6957.6	7037.2	7116.8	7196.4	7276.0	7309.9	7343.8	7378.4	7412.3	7437.2
72.5°	5473.6	5353.8	5412.7	5471.5	5531.0	5589.9	5539.3	5488.8	5438.3	5387.8	5547.6
75°	4155.7	4008.3	4000.7	3993.7	3986.1	3979.2	3953.6	3928.0	3901.7	3876.1	4025.6
77.5°	3182.5	3087.0	3091.9	3096.0	3100.9	3105.0	3078.7	3053.1	3026.8	3000.5	3058.0
80°	2637.8	2663.4	2664.1	2664.8	2665.5	2666.2	2641.3	2617.0	2592.1	2567.2	2525.7
82.5°	2114.5	2183.1	2182.4	2182.4	2181.7	2181.0	2179.6	2178.2	2176.1	2174.8	2106.9
85°	1515.1	1560.8	1513.7	1466.7	1419.6	1372.5	1407.2	1441.8	1477.1	1511.7	1483.3
87.5°	512.9	470.0	413.9	358.5	302.5	246.4	306.6	366.8	427.8	488.0	522.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064  
 CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064

CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1	1504.1
2.5°	1814.8	1807.9	1801.7	1758.1	1713.8	1670.2	1625.9	1706.2	1787.2	1867.4	1947.7
5°	2300.7	2286.2	2272.4	2268.9	2265.4	2261.3	2257.8	2298.7	2339.5	2379.6	2420.5
7.5°	2608.0	2597.0	2585.9	2556.8	2528.5	2499.4	2470.3	2495.2	2519.5	2544.4	2568.6
10°	2842.0	2817.8	2793.5	2730.6	2668.3	2605.3	2542.3	2523.6	2504.9	2486.2	2467.5
12.5°	3142.4	3082.9	3024.0	2952.7	2880.8	2809.5	2737.5	2727.8	2718.1	2709.1	2699.4
15°	3377.0	3358.3	3339.7	3282.9	3226.1	3169.4	3112.6	3036.5	2959.7	2883.5	2807.4
17.5°	3375.0	3345.2	3316.1	3392.3	3467.7	3543.8	3619.3	3538.3	3456.6	3375.7	3294.7
20°	3480.2	3462.9	3446.3	3586.8	3726.6	3867.1	4006.9	3962.6	3917.6	3873.3	3828.3
22.5°	3757.0	3823.5	3889.2	4009.7	4129.4	4249.8	4369.6	4420.1	4470.6	4521.2	4571.7
25°	4047.7	4155.7	4263.7	4443.0	4621.5	4800.8	4980.1	5016.1	5052.1	5088.0	5124.0
27.5°	3931.5	4041.5	4151.6	4287.2	4422.2	4557.9	4692.8	4850.6	5009.1	5167.0	5324.8
30°	3894.1	4015.9	4137.0	4323.2	4508.7	4694.9	4881.1	5098.4	5315.8	5532.4	5749.8
32.5°	3925.2	4096.9	4268.5	4520.5	4771.7	5023.7	5275.6	5504.0	5733.1	5961.6	6190.0
35°	4316.3	4461.6	4606.3	4888.0	5169.7	5451.4	5733.1	6001.0	6268.9	6536.0	6803.9
37.5°	4689.4	4826.4	4963.5	5251.4	5538.6	5826.6	6114.5	6537.4	6961.0	7383.9	7806.8
40°	5222.3	5339.3	5455.6	5702.0	5948.4	6194.8	6441.2	6951.3	7461.5	7971.6	8481.7
42.5°	5831.4	5919.3	6006.5	6261.9	6517.4	6772.8	7028.2	7583.3	8139.1	8694.2	9249.3
45°	6576.9	6653.7	6730.5	6906.3	7082.2	7258.7	7434.5	8006.9	8579.3	9151.7	9724.1
47.5°	7561.1	7462.2	7363.2	7449.7	7536.2	7622.7	7709.3	8275.4	8841.6	9407.1	9973.3
50°	8186.8	8083.0	7979.2	7986.8	7993.7	8001.3	8009.0	8537.1	9065.2	9592.6	10120.7
52.5°	9018.8	8791.8	8565.4	8563.4	8561.3	8558.5	8556.5	9016.7	9477.7	9938.0	10398.3
55°	9701.3	9452.8	9204.3	9155.9	9107.4	9058.3	9009.8	9465.3	9920.0	10375.4	10830.2
57.5°	10286.2	9962.2	9639.0	9562.8	9486.7	9410.6	9334.4	9825.2	10316.6	10807.3	11298.1
60°	10546.4	10335.3	10124.9	10031.4	9938.0	9844.6	9751.1	10169.2	10587.2	11004.6	11422.7
62.5°	10414.9	10258.5	10102.7	10124.2	10145.6	10167.1	10188.6	10427.4	10666.8	10905.6	11144.4
65°	9860.5	9823.1	9786.4	9959.5	10132.5	10305.5	10478.6	10482.0	10485.5	10489.0	10492.4
67.5°	8928.8	8874.8	8820.9	9180.8	9540.0	9899.9	10259.9	10088.9	9917.9	9747.7	9576.7
70°	7461.5	7486.4	7510.6	8000.6	8490.0	8980.1	9470.1	9222.3	8973.8	8726.0	8477.5
72.5°	5707.5	5868.1	6028.0	6536.0	7044.1	7552.1	8060.2	7777.1	7493.3	7210.2	6926.4
75°	4175.1	4324.6	4474.1	4975.9	5477.7	5980.2	6482.1	6145.7	5809.3	5473.6	5137.2
77.5°	3115.4	3173.5	3231.0	3648.4	4065.0	4482.4	4899.1	4561.3	4223.5	3886.5	3548.7
80°	2484.8	2443.3	2402.5	2633.7	2864.8	3096.0	3327.2	3087.7	2847.5	2608.0	2368.6
82.5°	2039.8	1972.0	1904.8	1990.6	2076.5	2163.0	2248.8	2057.1	1865.4	1673.6	1481.9
85°	1454.9	1426.5	1398.2	1423.1	1447.3	1472.2	1497.1	1310.3	1123.4	937.2	750.3
87.5°	556.5	591.1	625.7	665.2	703.9	743.4	782.1	612.6	443.0	274.1	104.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P368064  
 CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P368064  
 CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	1504.1	1504.1
2.5°	1981.0	2014.2
5°	2419.8	2419.1
7.5°	2557.5	2545.8
10°	2437.1	2406.6
12.5°	2609.4	2518.8
15°	2717.4	2626.7
17.5°	3158.3	3021.3
20°	3665.7	3502.3
22.5°	4323.2	4074.7
25°	4827.1	4529.5
27.5°	5148.3	4971.1
30°	5547.0	5344.1
32.5°	6040.5	5890.3
35°	6666.9	6529.1
37.5°	7763.9	7720.3
40°	8429.8	8377.2
42.5°	9251.4	9252.8
45°	9755.3	9786.4
47.5°	10052.2	10130.4
50°	10288.9	10456.4
52.5°	10627.4	10856.5
55°	11134.7	11438.6
57.5°	11557.0	11815.8
60°	11557.0	11690.5
62.5°	11141.0	11136.8
65°	10428.0	10363.0
67.5°	9495.0	9413.3
70°	8350.2	8222.1
72.5°	6767.9	6608.7
75°	4919.2	4700.4
77.5°	3444.9	3340.4
80°	2419.1	2469.6
82.5°	1553.9	1625.9
85°	739.2	728.1
87.5°	87.2	69.9
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P368064  
CATALOG NUMBER: PMM-SA3D-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)