

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P367822

Luminaire Tested: **PMM-SA3B-730-U-SLR**

Issue Date: 12/2/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P367822  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1910-543-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/2/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: PMM-SA3B-730-U-SLR  
Description: MESA POST TOP DECORATIVE LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR RIGHT OPTICS.  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11468 lumens  
Efficiency: N/A  
Efficacy: 91.0 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B2 - U0 - G3


Input Watts (W): 126  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P367822  
 CATALOG NUMBER: PMM-SA3B-730-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4.9 fc  
 Type IV - Short - N/A

REPORT NUMBER: P367822  
CATALOG NUMBER: PMM-SA3B-730-U-SLR

### Luminous Intensity Polar Plot



— Vertical Plane Through 270-Deg Lateral      - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P367822

CATALOG NUMBER: PMM-SA3B-730-U-SLR

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2221.1	0.0	2221.1
	% Fixture	19.4	0.0	19.4
<b>Street Side</b>	Lumens	9246.9	0.0	9246.9
	% Fixture	80.6	0.0	80.6
<b>Total</b>	Lumens	11468.0	0.0	11468.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	138.7	1.2
10°-20°	402.9	3.5
20°-30°	711.3	6.2
30°-40°	1107.9	9.7
40°-50°	1824.0	15.9
50°-60°	2603.4	22.7
60°-70°	2760.6	24.1
70°-80°	1524.7	13.3
80°-90°	394.5	3.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11468.0	100.0
0°-180°	11468.0	100.0

**Coefficient of Utilization**



REPORT NUMBER: P367822


CATALOG NUMBER: PMM-SA3B-730-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	877.5	7.7			
FM (30°-60°)	4445.7	38.8			
FH (60°-80°)	3588.4	31.3			G2/5000
FVH (80°-90°)	335.3	2.9			G3/500
BL (0°-30°)	375.5	3.3	B1/500		
BM (30°-60°)	1089.5	9.5	B2/2500		
BH (60°-80°)	696.9	6.1	B2/1000		G2/1000
BVH (80°-90°)	59.2	0.5			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G3**

Type IV Short





REPORT NUMBER: P367822

CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6
2.5°	1619.8	1629.8	1639.3	1620.4	1601.4	1582.0	1563.0	1534.7	1505.7	1477.3	1448.4
5°	1945.5	1908.7	1871.4	1856.4	1841.9	1826.9	1811.9	1797.9	1784.0	1769.6	1755.6
7.5°	2047.3	1995.0	1942.1	1919.8	1897.6	1874.8	1852.5	1802.4	1752.3	1701.6	1651.5
10°	1935.4	1880.9	1825.8	1804.1	1781.8	1760.1	1737.8	1676.6	1615.9	1554.7	1493.5
12.5°	2025.6	1969.9	1913.7	1844.7	1775.7	1706.1	1637.1	1603.1	1569.2	1534.7	1500.7
15°	2112.4	2037.3	1961.6	1892.6	1823.5	1754.0	1684.9	1617.0	1549.1	1481.2	1413.3
17.5°	2429.7	2304.5	2179.2	2054.6	1929.3	1804.6	1679.4	1600.9	1521.8	1443.4	1364.3
20°	2816.6	2642.4	2467.6	2278.3	2088.5	1899.2	1709.4	1610.4	1511.8	1412.7	1313.7
22.5°	3276.9	3057.1	2837.2	2598.4	2359.6	2120.2	1881.4	1737.8	1594.2	1450.0	1306.4
25°	3642.6	3431.1	3219.6	2916.8	2614.0	2311.2	2008.4	1845.3	1682.2	1518.5	1355.4
27.5°	3997.8	3661.0	3323.7	2976.9	2630.7	2283.9	1937.1	1786.3	1635.4	1484.6	1333.7
30°	4297.8	4030.6	3763.4	3310.9	2858.3	2405.2	1952.7	1767.3	1582.0	1396.6	1211.2
32.5°	4737.0	4355.7	3973.8	3501.8	3029.8	2557.8	2085.7	1848.6	1611.5	1374.3	1137.2
35°	5250.8	4854.4	4458.1	3874.2	3290.8	2706.9	2123.0	1872.0	1620.4	1369.3	1117.7
37.5°	6208.7	5510.2	4811.0	4173.7	3536.3	2898.4	2261.1	1969.4	1677.7	1385.5	1093.8
40°	6737.0	6091.3	5445.6	4651.3	3856.9	3062.1	2267.7	1969.4	1670.5	1372.1	1073.2
42.5°	7441.1	6624.6	5807.4	4948.5	4090.2	3231.3	2372.4	2041.7	1711.1	1379.9	1049.3
45°	7870.3	6960.2	6049.5	5131.6	4213.8	3295.9	2378.0	2042.3	1706.7	1371.0	1035.3
47.5°	8147.0	7273.0	6398.6	5410.5	4422.5	3433.9	2445.9	2089.6	1732.8	1376.6	1019.8
50°	8409.1	7543.6	6677.4	5651.5	4626.2	3600.3	2574.5	2185.4	1796.3	1406.6	1017.5
52.5°	8730.9	7933.8	7136.1	6035.6	4934.6	3834.1	2733.1	2309.5	1885.9	1462.3	1038.7
55°	9199.0	8413.6	7627.6	6446.4	5264.7	4083.5	2901.8	2431.4	1961.6	1491.2	1020.9
57.5°	9502.4	8705.8	7909.3	6704.7	5500.1	4295.0	3090.5	2569.4	2048.4	1526.9	1005.8
60°	9401.6	8580.0	7757.9	6609.5	5461.2	4312.8	3164.5	2601.7	2039.5	1476.8	914.0
62.5°	8956.3	8082.9	7209.6	6180.9	5152.8	4124.1	3095.5	2523.2	1951.6	1379.3	807.1
65°	8334.0	7431.1	6527.7	5599.8	4671.9	3743.9	2816.0	2296.7	1776.8	1257.4	737.5
67.5°	7570.3	6629.0	5687.2	4865.6	4044.0	3221.8	2400.2	1966.0	1532.4	1098.2	664.1
70°	6612.3	5687.2	4762.0	4051.2	3340.4	2629.6	1918.7	1592.0	1265.8	939.0	612.3
72.5°	5314.8	4516.6	3718.3	3158.9	2599.5	2040.1	1480.7	1253.5	1027.0	799.9	572.8
75°	3780.1	3310.9	2841.6	2406.3	1971.1	1535.2	1099.9	953.0	806.0	659.1	512.1
77.5°	2686.3	2409.7	2133.0	1791.8	1450.6	1109.4	768.2	681.9	596.2	509.9	423.6
80°	1986.1	1755.1	1524.1	1266.9	1009.7	752.6	495.4	453.1	411.4	369.1	326.7
82.5°	1307.5	1203.5	1098.8	895.1	691.3	487.6	283.9	268.3	252.7	237.1	221.5
85°	585.6	618.4	650.7	526.0	400.8	276.1	150.8	143.6	136.4	129.1	121.9
87.5°	56.2	82.9	109.7	94.1	77.9	62.3	46.2	45.6	45.6	45.1	44.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822  
 CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P367822

CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6
2.5°	1456.2	1464.0	1471.8	1479.5	1471.2	1462.8	1453.9	1445.6	1435.0	1424.4	1413.3
5°	1732.3	1708.3	1684.9	1661.0	1625.4	1589.8	1553.6	1518.0	1513.5	1508.5	1504.0
7.5°	1607.6	1564.2	1520.2	1476.2	1420.5	1365.4	1309.8	1254.1	1237.4	1220.7	1204.0
10°	1464.0	1433.9	1404.4	1374.3	1339.8	1305.3	1270.2	1235.7	1190.1	1143.9	1098.2
12.5°	1451.7	1402.7	1353.2	1304.2	1283.1	1261.9	1240.7	1219.6	1179.5	1139.4	1098.8
15°	1373.8	1333.7	1294.2	1254.1	1223.5	1192.9	1162.3	1131.6	1099.4	1066.5	1034.2
17.5°	1318.7	1273.0	1227.4	1181.7	1146.7	1111.6	1076.0	1040.9	1001.9	962.4	923.5
20°	1261.3	1209.6	1157.3	1104.9	1060.4	1016.4	971.9	927.4	884.5	842.2	799.3
22.5°	1238.0	1169.5	1101.0	1032.6	985.8	938.5	891.7	844.4	804.9	765.4	725.9
25°	1273.6	1192.3	1110.5	1028.7	965.8	902.3	839.4	776.0	743.1	710.3	676.9
27.5°	1231.8	1129.4	1027.6	925.1	857.8	789.9	722.5	654.6	649.6	644.6	639.0
30°	1103.8	996.4	889.0	781.5	719.7	657.4	595.6	533.3	521.6	509.3	497.6
32.5°	1027.6	917.9	808.2	698.6	643.5	587.8	532.7	477.0	463.7	450.3	437.0
35°	998.6	879.5	760.4	641.2	593.9	546.6	499.3	452.0	442.5	433.6	424.2
37.5°	975.2	857.2	738.7	620.1	574.5	528.8	482.6	437.0	429.7	422.5	415.3
40°	953.0	833.3	713.1	592.8	552.2	512.1	471.5	430.8	426.4	421.9	416.9
42.5°	932.9	816.6	699.7	583.4	547.2	511.6	475.4	439.2	434.7	430.3	425.8
45°	921.8	808.2	694.7	581.1	555.0	528.8	502.1	475.9	465.3	454.8	443.6
47.5°	913.4	807.1	700.8	594.5	567.2	539.9	512.7	485.4	475.9	466.5	456.4
50°	915.1	813.2	710.8	608.4	575.6	542.2	509.3	475.9	474.8	473.7	472.6
52.5°	930.1	822.2	713.6	605.1	569.4	533.8	497.6	462.0	469.2	475.9	483.2
55°	908.4	796.0	683.0	570.6	536.6	503.2	469.2	435.3	444.8	453.7	463.1
57.5°	883.9	762.0	640.1	518.2	492.6	467.0	440.9	415.3	425.3	435.8	445.9
60°	802.7	691.3	580.0	468.7	451.4	434.2	416.9	399.7	404.1	408.6	413.0
62.5°	713.6	619.5	526.0	432.0	418.6	404.7	391.3	377.4	377.4	378.0	378.0
65°	656.8	576.1	495.4	414.7	399.7	384.6	369.1	354.0	351.8	349.6	347.3
67.5°	600.1	536.6	472.6	408.6	386.9	365.7	344.0	322.3	319.5	317.3	314.5
70°	555.5	498.7	442.0	385.2	360.7	336.8	312.3	287.8	285.6	283.9	281.7
72.5°	519.3	466.5	413.0	359.6	334.0	307.8	282.2	256.1	254.4	252.7	250.5
75°	464.8	418.0	370.7	323.4	298.4	273.9	248.8	223.8	221.5	219.9	217.6
77.5°	384.6	345.1	306.2	266.6	247.1	228.2	208.7	189.3	188.1	187.0	185.4
80°	296.1	265.5	234.3	203.7	190.9	177.6	164.8	151.4	150.8	150.3	149.2
82.5°	203.2	184.8	166.4	148.1	138.6	128.6	119.1	109.1	109.7	110.2	110.8
85°	115.8	109.1	103.0	96.3	88.5	81.3	73.5	65.7	67.4	69.0	70.1
87.5°	42.3	40.1	37.9	35.6	31.7	28.4	24.5	20.6	21.7	23.4	24.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822  
 CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822  
 CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6
2.5°	1402.7	1386.0	1369.3	1352.6	1335.9	1301.4	1267.5	1233.0	1198.4	1219.6	1241.3
5°	1499.0	1470.6	1441.7	1413.3	1384.4	1368.2	1352.1	1335.9	1319.8	1328.1	1337.0
7.5°	1187.3	1170.6	1153.4	1136.7	1119.4	1112.2	1105.5	1098.2	1091.0	1111.6	1132.2
10°	1052.0	1028.7	1005.3	981.4	958.0	944.1	930.1	916.2	902.3	907.9	913.4
12.5°	1058.7	1024.2	989.7	955.2	920.7	900.1	879.5	858.9	838.3	843.3	848.3
15°	1001.4	965.8	930.1	894.5	858.9	835.0	810.5	786.5	762.0	753.7	744.8
17.5°	883.9	845.0	806.0	767.0	728.1	711.9	695.8	679.7	663.5	654.6	645.7
20°	756.5	720.3	684.1	647.9	611.7	600.6	589.5	577.8	566.7	561.1	555.0
22.5°	686.3	664.1	641.2	619.0	596.2	583.4	571.1	558.3	545.5	539.4	532.7
25°	644.0	648.5	653.5	657.9	662.4	656.8	650.7	645.1	639.0	641.2	642.9
27.5°	634.0	643.5	653.5	663.0	672.4	677.4	682.4	687.4	692.5	694.1	695.8
30°	485.4	490.4	494.9	499.9	504.3	518.2	532.1	545.5	559.4	581.1	603.4
32.5°	423.6	421.9	420.3	418.0	416.4	419.7	423.0	425.8	429.2	437.0	445.3
35°	414.7	410.8	406.3	402.4	398.0	399.7	401.3	403.0	404.7	410.8	416.9
37.5°	408.0	406.3	405.2	403.6	401.9	405.8	409.1	413.0	416.4	421.4	426.4
40°	412.5	411.9	411.4	410.2	409.7	411.9	414.1	416.4	418.6	425.3	432.0
42.5°	421.4	421.4	420.8	420.8	420.3	422.5	424.2	426.4	428.1	432.0	435.8
45°	433.1	432.0	431.4	430.3	429.2	428.6	428.6	428.1	427.5	429.7	432.5
47.5°	447.0	443.1	438.6	434.7	430.3	429.2	427.5	426.4	424.7	425.8	426.9
50°	471.5	460.9	450.9	440.3	429.7	426.9	424.2	421.4	418.6	418.0	418.0
52.5°	489.8	474.3	458.7	443.1	427.5	422.5	417.5	412.5	407.5	406.3	405.8
55°	472.0	460.3	449.2	437.5	425.8	418.6	410.8	403.6	395.8	394.1	392.4
57.5°	455.9	448.7	441.4	434.2	426.9	419.7	411.9	404.7	396.9	393.0	389.1
60°	417.5	417.5	418.0	418.0	418.0	410.2	402.4	394.7	386.9	383.0	379.6
62.5°	378.0	384.1	389.6	395.8	401.3	390.8	379.6	369.1	357.9	355.1	352.9
65°	345.1	346.8	349.0	350.7	352.4	344.0	335.7	327.3	319.0	317.3	315.1
67.5°	311.7	311.2	310.6	309.5	308.9	303.9	298.4	293.3	287.8	285.6	283.3
70°	279.4	278.9	278.3	277.2	276.6	272.2	267.7	263.3	258.8	257.2	255.5
72.5°	248.8	248.3	247.1	246.6	245.5	241.6	238.2	234.3	230.4	228.2	226.0
75°	215.4	214.3	213.2	212.1	211.0	207.6	204.3	200.4	197.0	194.8	192.6
77.5°	184.2	182.6	180.9	178.7	177.0	174.2	170.9	168.1	164.8	162.0	159.8
80°	148.6	147.5	146.4	144.7	143.6	140.8	138.0	134.7	131.9	128.6	125.8
82.5°	111.3	110.8	109.7	109.1	108.0	105.2	102.4	99.6	96.9	93.5	90.2
85°	71.8	71.2	70.7	70.1	69.6	67.4	65.7	63.5	61.2	57.9	55.1
87.5°	25.6	24.5	23.9	22.8	21.7	21.2	20.0	19.5	18.4	16.7	15.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822  
 CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822

CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6
2.5°	1262.5	1283.6	1284.2	1284.2	1294.2	1303.6	1284.2	1264.7	1244.6	1225.2	1205.7
5°	1345.4	1353.7	1351.5	1348.7	1336.5	1324.2	1311.4	1298.6	1285.8	1273.0	1273.6
7.5°	1152.8	1173.4	1190.1	1206.2	1190.6	1175.1	1166.7	1158.4	1150.0	1141.7	1140.6
10°	918.5	924.0	930.7	936.8	927.4	917.3	934.0	950.7	966.9	983.6	965.2
12.5°	853.3	858.3	846.6	834.4	830.5	826.6	822.7	818.3	814.4	809.9	807.7
15°	736.4	727.5	718.6	709.2	706.9	704.1	701.4	698.0	695.2	691.9	681.9
17.5°	636.8	627.9	612.9	597.3	591.1	584.5	582.8	581.1	578.9	577.2	567.8
20°	549.4	543.3	539.4	534.9	528.8	522.7	516.6	510.4	503.8	497.6	488.7
22.5°	526.6	519.9	514.9	509.3	508.2	507.1	496.0	484.3	473.1	461.5	456.4
25°	645.1	646.8	616.2	585.0	582.2	579.5	559.4	538.8	518.8	498.2	480.9
27.5°	696.9	698.6	697.5	696.4	687.4	678.0	644.0	609.5	575.6	541.1	516.6
30°	625.1	646.8	655.2	663.5	657.4	650.7	615.1	580.0	544.4	508.8	492.6
32.5°	453.1	460.9	474.8	488.2	495.4	502.1	491.0	479.8	468.7	457.6	454.8
35°	422.5	428.6	431.4	434.2	429.7	425.3	416.9	408.6	399.7	391.3	389.6
37.5°	430.8	435.8	441.4	447.0	434.7	421.9	412.5	403.6	394.1	384.6	376.8
40°	438.6	445.3	448.7	452.0	439.7	427.5	415.8	404.7	393.0	381.3	373.5
42.5°	439.7	443.6	449.8	455.9	438.6	420.8	410.2	399.1	388.5	377.4	369.6
45°	434.7	437.0	442.5	448.1	428.1	407.5	398.0	388.0	378.5	368.5	361.8
47.5°	427.5	428.6	433.1	437.0	415.8	394.1	385.2	376.3	366.8	357.9	351.2
50°	417.5	416.9	420.3	423.0	401.3	379.6	370.7	362.4	353.5	344.6	339.0
52.5°	404.7	403.6	406.9	409.7	386.9	364.0	356.2	349.0	341.2	333.4	329.0
55°	390.2	388.5	391.3	394.1	371.8	349.0	342.3	335.1	328.4	321.2	317.3
57.5°	384.6	380.7	382.4	384.1	359.0	334.0	327.3	320.6	313.9	307.3	304.5
60°	375.7	371.8	373.5	374.6	347.9	320.6	314.5	307.8	301.7	295.0	292.2
62.5°	350.1	347.3	349.6	351.8	327.9	303.4	297.8	292.8	287.2	281.7	277.8
65°	313.4	311.2	315.6	320.1	299.5	278.9	275.5	272.2	268.3	265.0	261.1
67.5°	281.1	278.9	283.3	287.8	272.8	257.7	254.4	251.0	247.7	244.4	242.1
70°	253.8	252.2	256.1	260.0	247.1	234.3	231.0	228.2	224.9	221.5	219.9
72.5°	223.2	221.0	226.0	230.4	219.9	208.7	206.0	202.6	199.8	196.5	195.4
75°	190.4	188.1	192.6	196.5	189.3	181.5	178.7	175.9	173.1	170.3	169.8
77.5°	157.0	154.2	158.6	162.5	158.1	153.1	150.8	148.1	145.8	143.1	143.1
80°	122.5	119.1	122.5	125.2	123.6	121.9	120.2	118.0	116.3	114.1	114.7
82.5°	86.8	83.5	85.2	86.8	87.9	89.1	89.1	89.1	89.1	89.1	89.1
85°	51.8	48.4	49.0	49.5	51.2	52.9	53.4	54.0	54.6	55.1	55.7
87.5°	13.4	11.7	10.6	8.9	10.6	11.7	12.8	13.4	14.5	15.0	15.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822  
 CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822

CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6
2.5°	1186.2	1166.2	1146.7	1158.9	1170.6	1182.9	1194.5	1195.1	1195.1	1195.7	1195.7
5°	1274.7	1275.3	1275.8	1264.1	1253.0	1241.3	1229.6	1223.5	1217.4	1210.7	1204.6
7.5°	1138.9	1137.8	1136.1	1125.0	1113.8	1102.7	1091.6	1064.8	1037.6	1010.9	983.6
10°	946.3	927.9	909.0	904.5	900.6	896.2	891.7	884.5	877.8	870.6	863.3
12.5°	805.5	803.2	801.0	789.3	777.6	765.4	753.7	753.7	753.7	753.7	753.7
15°	671.3	661.3	650.7	645.1	639.0	633.5	627.3	624.5	621.8	619.0	616.2
17.5°	557.8	548.3	538.3	537.2	536.0	534.9	533.8	531.0	528.2	525.5	522.7
20°	479.8	470.9	462.0	465.3	468.7	471.5	474.8	472.0	469.2	465.9	463.1
22.5°	450.9	445.9	440.3	437.5	434.7	431.4	428.6	428.6	429.2	429.2	429.2
25°	464.2	447.0	429.7	421.4	413.0	404.1	395.8	392.4	389.6	386.3	383.0
27.5°	492.1	467.0	442.5	428.1	413.6	399.1	384.6	378.5	371.8	365.7	359.0
30°	475.9	459.8	443.1	426.4	409.7	393.0	376.3	368.5	360.7	352.4	344.6
32.5°	452.0	448.7	445.9	430.3	414.7	398.6	383.0	379.6	376.8	373.5	370.2
35°	387.4	385.8	383.5	379.6	375.7	371.8	367.9	363.5	359.0	354.6	350.1
37.5°	369.6	361.8	354.0	352.4	350.7	349.0	347.3	345.7	344.0	341.8	340.1
40°	365.7	357.9	350.1	347.3	344.6	341.2	338.4	339.0	340.1	340.7	341.2
42.5°	361.3	353.5	345.1	342.9	340.7	338.4	336.2	336.8	337.9	338.4	339.0
45°	355.7	349.0	342.3	338.4	335.1	331.2	327.3	330.6	334.0	336.8	340.1
47.5°	344.6	337.3	330.6	328.4	326.2	323.4	321.2	324.5	327.9	330.6	334.0
50°	332.9	327.3	321.2	320.6	320.1	319.0	318.4	320.6	322.9	325.1	327.3
52.5°	324.0	319.5	314.5	314.5	313.9	313.9	313.4	315.6	317.8	319.5	321.7
55°	313.9	310.0	306.2	306.7	307.8	308.4	308.9	311.2	313.9	316.2	318.4
57.5°	301.1	298.4	295.0	297.2	298.9	301.1	302.8	304.5	306.7	308.4	310.0
60°	288.9	286.1	282.8	285.0	287.8	290.0	292.2	293.9	295.6	297.2	298.9
62.5°	273.9	269.4	265.5	268.9	271.6	275.0	277.8	278.9	280.5	281.7	282.8
65°	257.7	253.8	249.9	252.2	254.4	256.1	258.3	260.0	261.6	263.3	265.0
67.5°	239.4	237.1	234.3	236.0	237.7	239.4	241.0	241.6	241.6	242.1	242.1
70°	217.6	216.0	213.7	214.9	216.5	217.6	218.8	218.8	218.8	218.2	218.2
72.5°	194.8	193.7	192.6	193.2	194.3	194.8	195.4	194.8	194.3	193.7	193.2
75°	169.2	168.7	168.1	168.7	169.8	170.3	170.9	170.3	169.2	168.7	167.5
77.5°	143.6	143.6	143.6	143.6	144.2	144.2	144.2	143.1	141.9	140.8	139.7
80°	115.2	115.8	116.3	116.3	116.3	116.3	116.3	115.2	114.1	112.4	111.3
82.5°	89.1	89.1	89.1	89.1	89.6	89.6	89.6	86.8	84.6	81.8	79.0
85°	55.7	56.2	56.2	56.8	57.3	57.3	57.9	54.0	50.7	46.8	42.9
87.5°	15.0	15.0	15.0	15.0	15.0	14.5	14.5	11.1	7.2	3.9	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822  
 CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P367822

CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6
2.5°	1199.0	1202.3	1205.1	1208.5	1209.0	1209.6	1209.6	1210.1	1198.4	1186.8	1174.5
5°	1212.9	1220.7	1229.1	1236.9	1235.2	1233.5	1231.8	1230.2	1226.8	1224.0	1220.7
7.5°	977.5	971.9	965.8	959.6	964.7	969.7	974.7	979.7	981.9	984.1	985.8
10°	849.4	835.5	821.6	807.7	799.9	791.5	783.7	775.4	774.3	773.7	772.6
12.5°	739.2	724.2	709.7	694.7	690.2	685.2	680.8	675.8	680.2	684.7	688.6
15°	610.1	604.5	598.4	592.3	597.3	602.3	607.3	612.3	616.8	620.7	625.1
17.5°	519.9	517.7	514.9	512.1	516.6	521.6	526.0	530.5	540.5	550.5	560.5
20°	460.9	459.2	457.0	454.8	453.1	450.9	449.2	447.0	461.5	475.4	489.8
22.5°	425.8	422.5	419.1	415.8	416.4	416.9	416.9	417.5	429.2	441.4	453.1
25°	381.9	380.7	379.6	378.5	381.9	385.2	388.0	391.3	401.9	412.5	422.5
27.5°	359.6	360.1	360.7	361.3	365.7	370.7	375.2	379.6	386.9	394.1	401.3
30°	347.3	350.7	353.5	356.2	357.9	359.6	361.3	362.9	370.2	376.8	384.1
32.5°	365.7	361.3	356.2	351.8	354.0	356.8	359.0	361.3	367.9	374.6	381.3
35°	348.5	346.2	344.6	342.3	345.1	347.9	350.1	352.9	359.0	364.6	370.7
37.5°	339.5	339.0	338.4	337.9	339.5	341.2	342.3	344.0	349.6	355.1	360.1
40°	339.0	336.2	334.0	331.2	332.9	334.5	335.7	337.3	344.0	350.7	357.4
42.5°	335.7	332.3	328.4	325.1	326.7	329.0	330.6	332.3	339.5	346.2	353.5
45°	335.1	330.1	324.5	319.5	321.7	324.0	326.2	328.4	334.0	339.5	344.6
47.5°	329.0	324.0	319.0	313.9	315.1	316.2	316.7	317.8	322.9	327.3	332.3
50°	324.0	320.1	316.7	312.8	311.2	310.0	308.4	306.7	310.6	314.5	318.4
52.5°	317.8	313.9	309.5	305.6	303.4	301.1	298.9	296.7	300.0	302.8	306.2
55°	313.9	308.9	304.5	299.5	296.7	293.9	291.1	288.3	290.6	292.2	294.5
57.5°	305.6	301.1	296.1	291.7	288.3	285.0	281.1	277.8	278.9	280.0	281.1
60°	294.5	289.5	285.0	280.0	276.1	272.2	267.7	263.8	264.4	265.5	266.1
62.5°	278.3	273.9	268.9	264.4	260.0	256.1	251.6	247.1	248.3	248.8	249.9
65°	260.5	255.5	251.0	246.0	242.1	238.2	233.8	229.9	231.0	232.1	232.7
67.5°	238.8	234.9	231.6	227.7	224.3	220.4	217.1	213.2	213.7	214.3	214.9
70°	215.4	212.1	209.3	206.0	203.2	200.4	197.6	194.8	194.8	195.4	195.4
72.5°	190.4	187.6	184.8	182.0	179.2	177.0	174.2	171.4	172.6	173.7	174.2
75°	164.8	162.5	159.8	157.0	154.7	152.5	149.7	147.5	148.6	149.7	150.3
77.5°	138.0	136.4	134.1	132.5	130.3	128.0	125.2	123.0	124.1	125.2	125.8
80°	110.2	109.1	107.4	106.3	104.1	101.9	99.6	97.4	98.0	98.0	98.5
82.5°	79.6	80.2	80.2	80.7	79.0	76.8	75.1	72.9	72.9	72.9	72.4
85°	44.5	46.8	48.4	50.1	48.4	46.8	45.1	43.4	42.9	42.9	42.3
87.5°	1.7	2.8	4.5	5.6	5.0	4.5	3.3	2.8	3.3	3.9	3.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822  
 CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822  
 CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6
2.5°	1162.8	1172.3	1181.7	1191.2	1200.7	1215.1	1229.6	1244.6	1259.7	1251.3	1242.4
5°	1217.4	1222.9	1229.1	1234.6	1240.2	1256.3	1271.9	1291.4	1310.3	1308.1	1305.3
7.5°	988.0	995.8	1003.6	1010.9	1018.6	1043.1	1067.6	1088.2	1108.8	1106.0	1102.7
10°	771.5	787.6	804.3	820.5	836.6	856.7	876.1	893.4	910.7	939.6	968.0
12.5°	693.0	718.1	743.1	768.2	793.2	807.7	821.6	843.9	866.1	881.7	897.9
15°	629.0	652.4	675.8	699.1	722.5	723.6	724.7	748.1	771.5	784.9	797.7
17.5°	570.6	583.4	596.2	608.4	621.2	616.8	612.3	623.4	634.0	639.6	645.7
20°	503.8	512.7	521.6	530.5	539.4	545.5	551.1	557.8	563.9	558.3	552.2
22.5°	464.8	478.2	492.1	505.4	518.8	522.7	526.0	522.1	518.2	516.6	514.9
25°	433.1	449.2	465.9	482.0	498.2	506.0	513.8	517.1	519.9	513.8	507.7
27.5°	408.6	428.1	447.0	466.5	485.4	499.3	513.2	517.1	520.5	516.0	511.0
30°	390.8	411.9	433.1	454.2	475.4	496.5	517.1	535.5	553.3	551.6	550.0
32.5°	388.0	402.4	416.9	431.4	445.9	459.2	472.0	473.1	473.7	469.2	464.2
35°	376.3	385.8	395.2	404.7	414.1	422.5	430.3	429.2	428.1	423.6	419.1
37.5°	365.7	375.2	385.2	394.7	404.1	418.6	432.5	429.7	426.4	421.9	417.5
40°	364.0	374.6	385.2	395.2	405.8	419.1	432.5	429.7	426.9	421.4	415.8
42.5°	360.1	370.7	380.7	391.3	401.3	417.5	433.1	428.1	422.5	418.0	413.6
45°	350.1	359.6	369.1	378.5	388.0	405.2	422.5	416.4	410.2	408.6	406.3
47.5°	336.8	346.2	355.7	365.2	374.6	391.9	408.6	403.6	398.0	397.4	396.3
50°	322.3	331.2	340.7	349.6	358.5	375.7	392.4	388.0	383.5	384.1	384.1
52.5°	308.9	317.3	325.1	333.4	341.2	358.5	375.2	371.8	367.9	369.1	369.6
55°	296.1	302.8	309.5	316.2	322.9	339.5	356.2	351.2	346.2	347.9	349.6
57.5°	282.2	287.8	293.3	298.4	303.9	320.6	336.8	331.2	325.1	327.9	330.1
60°	266.6	271.6	276.6	281.1	286.1	301.1	315.6	310.6	305.0	308.9	312.3
62.5°	250.5	254.4	258.3	262.2	266.1	280.0	293.9	290.0	286.1	290.6	294.5
65°	233.8	236.6	239.9	242.7	245.5	258.8	271.6	268.9	266.1	270.0	273.9
67.5°	215.4	217.6	220.4	222.7	224.9	237.1	249.4	246.6	243.3	246.6	249.4
70°	195.4	197.6	199.3	201.5	203.2	214.3	225.4	221.5	217.1	220.4	223.2
72.5°	175.3	176.5	178.1	179.2	180.4	188.7	197.0	193.7	190.4	193.7	196.5
75°	151.4	152.5	153.6	154.7	155.9	163.1	169.8	165.9	161.4	164.8	168.1
77.5°	126.9	127.5	128.6	129.1	129.7	134.7	139.2	135.3	130.8	134.7	138.6
80°	98.5	99.1	99.6	99.6	100.2	101.9	103.5	100.8	97.4	102.4	107.4
82.5°	72.4	71.8	71.8	71.2	70.7	70.7	70.1	68.5	66.2	70.7	75.1
85°	41.7	41.2	40.1	39.5	38.4	36.7	35.1	34.5	34.0	37.9	41.7
87.5°	4.5	3.9	2.8	2.2	1.1	0.6	0.0	0.0	0.0	2.2	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822  
 CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822

CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6
2.5°	1234.1	1225.2	1216.8	1208.5	1200.1	1191.8	1207.3	1222.9	1238.5	1254.1	1268.0
5°	1303.1	1300.3	1293.1	1286.4	1279.2	1271.9	1275.8	1280.3	1284.2	1288.1	1296.4
7.5°	1099.9	1096.6	1112.2	1127.2	1142.8	1157.8	1161.7	1165.0	1168.9	1172.3	1170.1
10°	996.9	1025.3	1032.6	1039.2	1046.5	1053.2	1064.3	1075.4	1086.0	1097.1	1103.3
12.5°	913.4	929.0	954.6	980.8	1006.4	1032.0	1048.7	1065.4	1082.1	1098.8	1133.3
15°	811.0	823.8	843.3	862.8	882.3	901.8	925.7	950.2	974.1	998.1	1035.9
17.5°	651.3	656.8	671.3	685.8	699.7	714.2	746.5	778.2	810.5	842.2	885.6
20°	546.6	540.5	540.5	541.1	541.1	541.1	573.3	605.1	637.4	669.1	726.4
22.5°	512.7	511.0	504.9	498.2	492.1	485.4	502.1	519.3	536.0	552.7	599.5
25°	501.0	494.9	487.1	479.3	471.5	463.7	474.3	484.8	495.4	506.0	542.7
27.5°	506.5	501.5	505.4	508.8	512.7	516.0	519.3	522.7	526.0	529.4	542.2
30°	548.3	546.6	552.7	558.3	564.4	570.0	562.2	555.0	547.2	539.4	543.8
32.5°	459.8	454.8	452.5	450.3	448.1	445.9	445.3	444.8	443.6	443.1	453.1
35°	414.7	410.2	406.9	403.6	399.7	396.3	398.0	399.1	400.8	401.9	413.0
37.5°	413.0	408.6	404.7	400.8	396.3	392.4	394.1	396.3	398.0	399.7	408.0
40°	410.2	404.7	402.4	400.2	398.0	395.8	396.9	398.0	398.6	399.7	405.8
42.5°	408.6	404.1	403.0	401.9	400.8	399.7	400.8	401.9	402.4	403.6	410.8
45°	404.7	402.4	403.6	404.7	405.8	406.9	406.9	406.9	406.9	406.9	414.7
47.5°	395.8	394.7	398.0	401.3	404.7	408.0	413.6	419.1	424.2	429.7	431.4
50°	384.6	384.6	390.2	395.8	400.8	406.3	419.7	432.5	445.9	458.7	450.3
52.5°	370.7	371.3	379.6	387.4	395.8	403.6	415.8	428.1	439.7	452.0	439.7
55°	350.7	352.4	362.9	372.9	383.5	393.5	403.0	412.5	421.9	431.4	418.6
57.5°	332.9	335.1	346.2	356.8	367.9	378.5	384.1	390.2	395.8	401.3	393.0
60°	316.2	319.5	334.0	348.5	362.4	376.8	372.4	367.9	362.9	358.5	357.9
62.5°	298.9	302.8	316.2	329.5	342.3	355.7	349.0	342.3	335.1	328.4	331.2
65°	277.2	281.1	287.2	293.3	298.9	305.0	304.5	304.5	303.9	303.4	308.9
67.5°	252.7	255.5	259.4	262.7	266.6	270.0	272.2	275.0	277.2	279.4	286.1
70°	226.6	229.3	233.2	236.6	240.5	243.8	246.6	249.4	251.6	254.4	261.1
72.5°	199.8	202.6	206.5	210.4	213.7	217.6	219.9	222.1	223.8	226.0	231.6
75°	171.4	174.8	178.7	182.0	185.9	189.3	190.9	192.6	194.3	195.9	200.9
77.5°	142.5	146.4	150.3	154.2	158.1	162.0	162.5	163.1	163.7	164.2	168.7
80°	111.9	116.9	120.8	124.7	128.6	132.5	132.5	132.5	132.5	132.5	134.7
82.5°	79.6	84.1	88.5	92.4	96.9	100.8	100.8	100.2	100.2	99.6	99.6
85°	45.6	49.5	52.3	55.7	58.4	61.2	61.2	61.2	60.7	60.7	59.6
87.5°	7.2	9.5	10.6	12.2	13.4	14.5	13.9	13.9	13.4	12.8	11.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822  
 CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822

CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6
2.5°	1281.9	1295.9	1309.8	1307.5	1305.3	1303.1	1300.9	1309.2	1317.0	1325.4	1333.1
5°	1304.2	1312.6	1320.3	1326.5	1332.6	1338.7	1344.8	1373.2	1401.1	1429.4	1457.3
7.5°	1167.8	1165.0	1162.8	1189.0	1215.7	1241.9	1268.0	1304.2	1340.4	1376.6	1412.7
10°	1109.4	1115.5	1121.6	1132.2	1143.3	1153.9	1164.5	1200.1	1235.7	1271.4	1307.0
12.5°	1167.3	1201.8	1235.7	1244.1	1253.0	1261.3	1269.7	1276.9	1284.2	1290.8	1298.1
15°	1073.8	1111.6	1149.5	1171.2	1192.9	1214.0	1235.7	1290.3	1344.3	1398.8	1452.8
17.5°	928.5	971.9	1014.8	1068.2	1121.6	1175.1	1228.5	1278.6	1328.7	1378.2	1428.3
20°	783.7	840.5	897.9	956.3	1014.2	1072.6	1130.5	1179.5	1228.5	1276.9	1325.9
22.5°	645.7	692.5	738.7	809.9	880.6	951.9	1022.5	1113.8	1204.6	1295.9	1386.6
25°	578.9	615.6	651.8	725.3	798.8	871.7	945.2	1063.7	1181.7	1300.3	1418.3
27.5°	555.5	568.3	581.1	647.9	714.2	781.0	847.2	975.2	1103.3	1230.7	1358.8
30°	548.3	552.7	557.2	609.5	661.8	714.2	766.5	892.8	1019.8	1146.1	1272.5
32.5°	462.6	472.6	482.0	533.3	583.9	635.1	685.8	813.2	940.2	1067.6	1194.5
35°	424.2	435.3	446.4	496.5	546.6	596.2	646.3	780.4	915.1	1049.3	1183.4
37.5°	416.4	424.7	433.1	489.8	546.6	603.4	660.2	796.0	931.8	1067.6	1203.5
40°	412.5	418.6	424.7	479.8	535.5	590.6	645.7	788.2	930.1	1072.6	1214.6
42.5°	417.5	424.7	431.4	481.5	531.0	581.1	630.7	778.2	925.1	1072.6	1219.6
45°	421.9	429.7	437.0	483.7	530.5	577.2	624.0	781.5	938.5	1096.0	1253.0
47.5°	432.5	434.2	435.3	475.9	516.0	556.6	596.7	757.0	917.3	1077.1	1237.4
50°	441.4	433.1	424.2	466.5	508.2	550.5	592.3	744.2	896.2	1047.6	1199.6
52.5°	427.5	414.7	402.4	448.1	493.7	538.8	584.5	736.4	889.0	1040.9	1192.9
55°	406.3	393.5	380.7	426.9	473.1	519.3	565.5	717.0	868.9	1020.3	1171.7
57.5°	385.2	376.8	368.5	406.3	444.8	482.6	520.5	684.7	848.3	1012.5	1176.2
60°	357.4	356.2	355.7	385.2	415.3	444.8	474.3	635.1	795.4	956.3	1116.6
62.5°	333.4	336.2	338.4	362.4	386.3	409.7	433.6	588.9	744.8	900.1	1055.4
65°	315.1	320.6	326.2	353.5	380.7	407.5	434.7	565.0	695.2	825.5	955.7
67.5°	292.8	299.5	306.2	341.8	377.4	413.0	448.7	556.1	663.5	770.9	878.4
70°	267.2	273.9	280.0	325.6	370.7	416.4	461.5	556.6	652.4	747.6	842.8
72.5°	237.1	242.7	248.3	297.2	346.2	395.2	444.2	524.9	605.6	685.8	766.5
75°	206.5	211.5	216.5	258.8	301.1	343.4	385.8	448.1	509.9	572.2	634.0
77.5°	172.6	177.0	180.9	209.3	237.7	266.1	294.5	342.3	389.6	437.5	484.8
80°	136.9	139.2	141.4	158.1	174.2	190.9	207.1	238.8	270.5	301.7	333.4
82.5°	100.2	100.2	100.2	110.8	121.9	132.5	143.1	159.2	174.8	190.9	206.5
85°	58.4	56.8	55.7	62.9	70.1	77.4	84.6	91.3	98.0	104.6	111.3
87.5°	9.5	7.2	5.6	10.0	14.5	18.9	23.4	25.6	28.4	30.6	32.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822  
 CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P367822

CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6
2.5°	1314.2	1295.9	1276.9	1258.0	1285.8	1313.7	1341.5	1369.3	1443.4	1487.3	1490.1
5°	1480.7	1504.0	1527.4	1550.8	1574.2	1597.6	1620.4	1643.8	1764.0	1838.0	1851.9
7.5°	1451.2	1490.1	1528.5	1566.9	1633.2	1699.4	1765.7	1831.9	1933.8	2007.2	2055.7
10°	1354.9	1402.7	1450.6	1498.5	1577.0	1656.0	1734.5	1813.0	1921.0	2017.8	2064.0
12.5°	1374.3	1450.6	1526.3	1602.6	1670.5	1738.9	1806.8	1874.8	1949.3	1986.1	2070.1
15°	1505.7	1558.6	1611.5	1664.3	1766.8	1868.6	1971.1	2072.9	2115.2	2199.3	2275.0
17.5°	1525.7	1622.6	1720.0	1816.9	1942.1	2067.4	2192.6	2317.8	2396.3	2504.9	2596.2
20°	1463.4	1600.3	1737.8	1874.8	2036.2	2198.2	2359.6	2521.0	2620.7	2711.9	2853.3
22.5°	1538.0	1689.4	1840.2	1991.7	2206.0	2419.7	2634.0	2847.8	3055.9	3259.7	3355.4
25°	1620.4	1823.0	2025.1	2227.1	2494.9	2762.0	3029.8	3297.0	3564.7	3755.6	3865.9
27.5°	1562.5	1765.7	1969.4	2172.6	2503.8	2835.5	3166.7	3497.9	3784.6	4014.5	4109.1
30°	1521.8	1771.2	2020.6	2270.0	2658.5	3047.0	3435.6	3824.1	4089.1	4345.7	4484.8
32.5°	1514.6	1834.7	2154.2	2474.3	2926.8	3378.8	3831.3	4283.3	4459.2	4686.9	4874.5
35°	1534.7	1886.4	2237.7	2588.9	3107.7	3626.5	4144.7	4663.5	4913.4	5138.9	5303.1
37.5°	1595.9	1988.3	2380.2	2772.6	3397.7	4023.4	4648.5	5273.6	5692.7	6105.2	6178.7
40°	1630.4	2046.8	2462.6	2878.4	3605.3	4332.3	5059.3	5786.3	6268.3	6720.9	6751.5
42.5°	1671.0	2122.5	2573.3	3024.8	3830.8	4637.4	5443.4	6249.4	6846.1	7332.6	7347.1
45°	1717.8	2182.0	2646.8	3111.1	3952.7	4793.8	5635.4	6476.5	7197.9	7789.0	7644.9
47.5°	1736.2	2235.5	2734.2	3233.0	4130.3	5027.0	5924.3	6821.0	7468.4	8006.1	7868.1
50°	1743.4	2287.8	2831.6	3375.5	4305.0	5235.2	6164.8	7094.4	7752.9	8277.2	8065.7
52.5°	1788.5	2384.1	2979.7	3575.3	4543.8	5512.4	6480.9	7449.5	8097.4	8601.2	8338.4
55°	1849.2	2526.6	3203.5	3880.9	4883.4	5885.3	6887.8	7889.8	8539.9	9008.6	8683.0
57.5°	1905.4	2635.1	3364.3	4093.5	5132.2	6171.4	7210.1	8248.8	8907.3	9371.0	9055.4
60°	1878.1	2639.6	3401.1	4162.5	5183.4	6203.7	7224.6	8244.9	8992.5	9548.6	9387.1
62.5°	1795.7	2536.0	3275.8	4016.1	4985.3	5953.8	6922.9	7891.5	8766.5	9479.6	9472.3
65°	1637.1	2318.4	2999.2	3680.5	4577.2	5474.5	6371.3	7268.0	8299.5	9165.6	9221.8
67.5°	1443.9	2009.5	2575.0	3140.6	3985.0	4829.4	5673.8	6518.2	7620.9	8576.7	8625.1
70°	1256.9	1671.6	2085.7	2499.9	3241.3	3982.7	4723.6	5465.1	6578.9	7545.8	7590.3
72.5°	1037.6	1308.7	1579.2	1850.3	2450.9	3051.5	3651.5	4252.2	5230.2	5973.8	6224.9
75°	794.9	955.7	1116.6	1277.5	1763.4	2249.4	2734.8	3220.7	3870.9	4419.7	4702.5
77.5°	568.3	651.8	735.3	818.8	1231.8	1644.9	2057.3	2470.4	2812.1	3123.3	3314.2
80°	372.9	411.9	451.4	490.4	833.8	1177.3	1520.2	1863.6	2071.8	2238.8	2335.1
82.5°	226.0	245.5	264.4	283.9	562.2	840.5	1118.3	1396.6	1515.7	1595.3	1681.0
85°	121.9	132.5	143.1	153.6	332.3	510.4	689.1	867.2	878.9	888.4	1015.9
87.5°	35.6	39.0	41.7	44.5	73.5	103.0	131.9	160.9	100.2	62.3	128.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822  
 CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822

CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6
2.5°	1474.0	1466.7	1459.5	1451.7	1444.5	1413.9	1383.8	1353.2	1322.6	1352.1	1381.0
5°	1835.8	1858.1	1879.8	1902.0	1924.3	1926.0	1927.1	1928.8	1929.9	1935.4	1941.0
7.5°	2096.3	2135.8	2174.8	2214.3	2253.8	2284.4	2315.1	2346.2	2376.8	2349.0	2321.2
10°	2118.6	2202.1	2285.6	2369.1	2452.5	2467.6	2482.1	2497.1	2512.1	2532.1	2551.6
12.5°	2140.8	2242.7	2344.0	2445.9	2547.7	2592.3	2636.2	2680.8	2724.7	2746.5	2767.6
15°	2376.3	2436.4	2496.0	2556.1	2615.6	2646.3	2676.3	2706.9	2737.5	2755.9	2773.7
17.5°	2679.1	2701.4	2723.1	2745.3	2767.6	2788.2	2808.8	2829.4	2850.0	2853.3	2856.7
20°	2955.2	2959.6	2963.5	2968.0	2971.9	2928.5	2885.6	2842.2	2798.8	2806.6	2813.8
22.5°	3369.3	3344.8	3320.9	3296.4	3272.5	3190.7	3109.4	3027.6	2946.3	2911.2	2876.7
25°	3992.8	3930.4	3868.1	3805.7	3743.4	3613.1	3483.4	3353.2	3223.5	3147.2	3071.5
27.5°	4193.7	4057.9	3922.6	3786.8	3651.0	3552.5	3454.5	3356.0	3258.0	3137.2	3016.4
30°	4600.1	4385.8	4172.0	3957.7	3743.4	3648.2	3553.0	3457.3	3362.1	3238.5	3115.5
32.5°	4960.2	4737.5	4514.9	4291.7	4069.0	3888.7	3708.3	3528.0	3347.6	3264.1	3180.6
35°	5377.1	5097.1	4817.1	4537.2	4257.2	4102.4	3948.2	3793.5	3639.3	3512.9	3387.1
37.5°	5984.4	5686.6	5388.8	5090.5	4792.7	4583.4	4374.6	4165.3	3956.6	3887.0	3818.0
40°	6563.3	6211.5	5860.3	5508.5	5157.3	4996.9	4836.6	4675.8	4515.5	4398.0	4280.5
42.5°	7048.2	6700.3	6352.9	6005.0	5657.7	5540.8	5424.4	5307.5	5191.2	5094.4	4997.5
45°	7214.6	6930.7	6647.4	6363.5	6079.6	6038.4	5997.8	5956.6	5916.0	5844.1	5772.3
47.5°	7482.3	7192.9	6904.0	6614.5	6325.1	6340.1	6355.1	6370.7	6385.8	6389.7	6393.0
50°	7639.9	7364.9	7090.5	6815.5	6541.1	6614.0	6686.3	6759.3	6832.2	6997.5	7162.3
52.5°	7869.8	7599.8	7330.4	7060.4	6790.4	6914.0	7037.0	7160.6	7283.6	7515.2	7746.7
55°	8158.1	7899.8	7642.1	7383.8	7126.1	7246.3	7366.0	7486.2	7605.9	7863.6	8121.4
57.5°	8540.5	8263.9	7987.8	7711.1	7435.0	7545.8	7656.0	7766.8	7877.0	8121.9	8366.8
60°	8975.8	8675.2	8374.6	8073.5	7772.9	7803.5	7833.6	7864.2	7894.2	8159.8	8424.7
62.5°	9189.5	8911.2	8633.5	8355.1	8076.8	7991.7	7906.5	7820.8	7735.6	7973.3	8210.4
65°	9004.2	8812.7	8621.8	8430.3	8238.8	8088.5	7938.8	7788.5	7638.2	7786.8	7934.9
67.5°	8414.1	8305.6	8197.6	8089.1	7980.5	7728.4	7476.2	7223.5	6971.3	6981.4	6990.8
70°	7457.8	7428.9	7400.5	7371.6	7342.6	6963.5	6585.0	6206.0	5826.9	5769.0	5711.1
72.5°	6246.0	6265.0	6283.3	6302.3	6321.2	5913.7	5506.3	5098.8	4691.3	4595.0	4498.8
75°	4837.7	4942.4	5047.0	5152.2	5256.9	4867.2	4477.6	4087.4	3697.7	3579.2	3460.6
77.5°	3418.3	3613.7	3808.5	4003.9	4199.3	3846.9	3495.1	3142.8	2790.4	2713.6	2636.8
80°	2383.5	2479.3	2575.0	2670.8	2766.5	2589.5	2412.5	2235.5	2058.4	2079.6	2100.2
82.5°	1736.2	1758.4	1780.1	1802.4	1824.7	1752.3	1679.9	1607.0	1534.7	1589.8	1644.9
85°	1112.2	1191.8	1270.8	1350.4	1429.4	1349.3	1269.1	1188.4	1108.3	1145.0	1181.7
87.5°	248.8	393.5	538.3	683.6	828.3	750.3	673.0	595.0	517.1	482.0	447.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822  
 CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822

CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6
2.5°	1410.5	1440.0	1431.1	1422.8	1413.9	1405.0	1421.1	1437.2	1453.9	1470.1	1464.5
5°	1947.1	1952.7	1899.8	1847.5	1794.6	1741.7	1774.6	1807.4	1840.2	1873.1	1861.4
7.5°	2293.3	2265.5	2234.9	2204.3	2173.1	2142.5	2135.8	2129.1	2121.9	2115.2	2106.3
10°	2571.7	2591.2	2571.1	2551.6	2531.6	2511.6	2464.8	2418.0	2370.7	2324.0	2304.5
12.5°	2789.3	2811.0	2816.0	2820.5	2825.5	2830.5	2778.2	2726.4	2674.1	2621.8	2574.5
15°	2792.1	2810.5	2826.6	2842.2	2858.3	2873.9	2841.6	2809.9	2777.6	2745.3	2730.3
17.5°	2860.6	2863.9	2850.5	2837.7	2824.4	2811.6	2798.8	2786.5	2773.7	2761.5	2737.5
20°	2821.6	2829.4	2827.7	2826.1	2823.8	2822.2	2823.3	2823.8	2824.9	2825.5	2812.1
22.5°	2841.6	2806.6	2813.8	2820.5	2827.7	2834.4	2854.4	2874.5	2895.1	2915.1	2968.6
25°	2995.3	2919.0	2907.3	2896.2	2884.5	2873.4	2925.7	2977.5	3029.8	3082.1	3168.9
27.5°	2895.1	2774.3	2747.6	2720.8	2694.1	2667.4	2747.0	2826.1	2905.7	2985.3	3073.8
30°	2991.9	2868.9	2809.9	2750.9	2691.3	2632.3	2708.6	2784.3	2860.6	2936.3	3034.2
32.5°	3097.1	3013.6	2974.1	2935.2	2895.6	2856.7	2862.8	2868.9	2875.0	2881.2	3019.2
35°	3260.8	3134.4	3095.5	3056.5	3017.5	2978.6	3043.7	3108.3	3173.4	3238.0	3354.9
37.5°	3748.4	3678.8	3608.7	3538.5	3467.9	3397.7	3436.1	3474.5	3512.9	3551.4	3661.6
40°	4163.1	4045.6	4034.0	4022.8	4011.1	3999.4	4002.8	4005.6	4008.9	4012.2	4106.3
42.5°	4900.1	4803.2	4743.7	4684.1	4624.6	4565.0	4561.1	4557.2	4552.7	4548.8	4619.5
45°	5700.0	5628.2	5583.6	5539.1	5494.0	5449.5	5378.8	5308.1	5236.9	5166.2	5227.9
47.5°	6396.9	6400.8	6481.5	6561.7	6642.4	6723.1	6602.3	6481.5	6360.7	6239.9	6160.3
50°	7327.6	7492.4	7511.8	7530.8	7550.2	7569.7	7364.9	7160.6	6955.8	6750.9	6667.4
52.5°	7978.9	8210.4	8180.4	8150.9	8120.8	8090.7	7972.2	7854.2	7735.6	7617.0	7435.0
55°	8379.6	8637.4	8614.5	8592.3	8569.4	8546.6	8460.3	8374.1	8287.8	8201.5	8001.7
57.5°	8611.8	8856.7	8863.4	8870.0	8876.7	8883.4	8860.6	8837.7	8814.9	8792.1	8532.2
60°	8690.2	8955.8	8958.5	8960.8	8963.5	8965.8	8929.6	8893.4	8856.7	8820.5	8650.7
62.5°	8448.1	8685.2	8695.8	8705.8	8716.4	8727.0	8701.9	8676.9	8651.8	8626.8	8501.0
65°	8083.5	8232.1	8234.9	8237.1	8239.9	8242.7	8179.2	8116.3	8052.9	7989.4	7959.4
67.5°	7000.8	7010.9	7069.9	7128.9	7187.9	7246.9	7251.9	7256.9	7262.5	7267.5	7224.1
70°	5653.2	5595.3	5659.3	5723.4	5787.4	5851.4	5878.7	5905.9	5933.8	5961.0	5981.1
72.5°	4401.9	4305.6	4352.9	4400.2	4448.1	4495.4	4454.8	4414.1	4373.5	4332.9	4461.5
75°	3342.1	3223.5	3217.4	3211.8	3205.7	3200.1	3179.5	3158.9	3137.8	3117.2	3237.4
77.5°	2559.4	2482.6	2486.5	2489.8	2493.7	2497.1	2475.9	2455.3	2434.2	2413.0	2459.2
80°	2121.3	2141.9	2142.5	2143.1	2143.6	2144.2	2124.1	2104.6	2084.6	2064.6	2031.2
82.5°	1700.5	1755.6	1755.1	1755.1	1754.5	1754.0	1752.9	1751.7	1750.1	1749.0	1694.4
85°	1218.5	1255.2	1217.4	1179.5	1141.7	1103.8	1131.6	1159.5	1187.9	1215.7	1192.9
87.5°	412.5	378.0	332.9	288.3	243.3	198.2	246.6	295.0	344.0	392.4	420.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822  
 CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822

CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6	1209.6
2.5°	1459.5	1453.9	1448.9	1413.9	1378.2	1343.2	1307.5	1372.1	1437.2	1501.8	1566.4
5°	1850.3	1838.6	1827.4	1824.7	1821.9	1818.5	1815.8	1848.6	1881.4	1913.7	1946.6
7.5°	2097.4	2088.5	2079.6	2056.2	2033.4	2010.0	1986.6	2006.7	2026.2	2046.2	2065.7
10°	2285.6	2266.1	2246.6	2195.9	2145.8	2095.2	2044.5	2029.5	2014.5	1999.4	1984.4
12.5°	2527.1	2479.3	2432.0	2374.6	2316.7	2259.4	2201.5	2193.7	2185.9	2178.7	2170.9
15°	2715.8	2700.8	2685.8	2640.1	2594.5	2548.8	2503.2	2442.0	2380.2	2319.0	2257.7
17.5°	2714.2	2690.2	2666.9	2728.1	2788.8	2850.0	2910.7	2845.5	2779.9	2714.7	2649.6
20°	2798.8	2784.9	2771.5	2884.5	2996.9	3109.9	3222.4	3186.8	3150.6	3114.9	3078.8
22.5°	3021.4	3074.9	3127.8	3224.6	3320.9	3417.8	3514.1	3554.7	3595.3	3636.0	3676.6
25°	3255.2	3342.1	3428.9	3573.1	3716.7	3860.8	4005.0	4034.0	4062.9	4091.8	4120.8
27.5°	3161.7	3250.2	3338.7	3447.8	3556.4	3665.5	3774.0	3900.9	4028.4	4155.3	4282.2
30°	3131.6	3229.6	3327.0	3476.8	3625.9	3775.7	3925.4	4100.2	4275.0	4449.2	4624.0
32.5°	3156.7	3294.7	3432.8	3635.4	3837.5	4040.1	4242.7	4426.4	4610.6	4794.3	4978.0
35°	3471.2	3588.1	3704.4	3931.0	4157.5	4384.1	4610.6	4826.1	5041.5	5256.3	5471.8
37.5°	3771.2	3881.4	3991.7	4223.2	4454.2	4685.8	4917.3	5257.4	5598.1	5938.2	6278.3
40°	4199.8	4293.9	4387.4	4585.6	4783.7	4981.9	5180.1	5590.3	6000.6	6410.8	6821.0
42.5°	4689.7	4760.4	4830.5	5035.9	5241.3	5446.7	5652.1	6098.5	6545.5	6991.9	7438.4
45°	5289.2	5351.0	5412.8	5554.1	5695.5	5837.5	5978.9	6439.2	6899.5	7359.9	7820.2
47.5°	6080.7	6001.1	5921.5	5991.1	6060.7	6130.3	6199.8	6655.2	7110.5	7565.3	8020.6
50°	6583.9	6500.4	6416.9	6423.0	6428.6	6434.7	6440.9	6865.6	7290.3	7714.5	8139.2
52.5°	7253.0	7070.4	6888.4	6886.7	6885.1	6882.8	6881.2	7251.3	7622.0	7992.2	8362.4
55°	7801.8	7602.0	7402.2	7363.2	7324.2	7284.7	7245.8	7612.0	7977.7	8344.0	8709.7
57.5°	8272.2	8011.7	7751.7	7690.5	7629.3	7568.1	7506.8	7901.5	8296.7	8691.4	9086.0
60°	8481.5	8311.7	8142.5	8067.4	7992.2	7917.1	7841.9	8178.1	8514.3	8850.0	9186.2
62.5°	8375.7	8249.9	8124.7	8141.9	8159.2	8176.5	8193.7	8385.8	8578.4	8770.4	8962.4
65°	7929.9	7899.8	7870.3	8009.5	8148.6	8287.8	8426.9	8429.7	8432.5	8435.3	8438.1
67.5°	7180.6	7137.2	7093.8	7383.3	7672.1	7961.6	8251.0	8113.6	7976.1	7839.1	7701.6
70°	6000.6	6020.6	6040.1	6434.2	6827.7	7221.8	7615.9	7416.6	7216.8	7017.5	6817.7
72.5°	4590.0	4719.2	4847.8	5256.3	5664.9	6073.5	6482.1	6254.4	6026.2	5798.5	5570.3
75°	3357.6	3477.9	3598.1	4001.7	4405.2	4809.4	5212.9	4942.4	4671.9	4401.9	4131.4
77.5°	2505.4	2552.2	2598.4	2934.0	3269.1	3604.8	3939.9	3668.2	3396.6	3125.5	2853.9
80°	1998.3	1964.9	1932.1	2118.0	2303.9	2489.8	2675.8	2483.2	2290.0	2097.4	1904.8
82.5°	1640.4	1585.9	1531.9	1600.9	1669.9	1739.5	1808.5	1654.3	1500.1	1346.0	1191.8
85°	1170.1	1147.2	1124.4	1144.4	1163.9	1184.0	1204.0	1053.7	903.4	753.7	603.4
87.5°	447.5	475.4	503.2	534.9	566.1	597.8	629.0	492.6	356.2	220.4	84.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P367822  
 CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P367822  
CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	1209.6	1209.6
2.5°	1593.1	1619.8
5°	1946.0	1945.5
7.5°	2056.8	2047.3
10°	1959.9	1935.4
12.5°	2098.5	2025.6
15°	2185.4	2112.4
17.5°	2539.9	2429.7
20°	2948.0	2816.6
22.5°	3476.8	3276.9
25°	3882.0	3642.6
27.5°	4140.3	3997.8
30°	4460.9	4297.8
32.5°	4857.8	4737.0
35°	5361.5	5250.8
37.5°	6243.8	6208.7
40°	6779.3	6737.0
42.5°	7440.0	7441.1
45°	7845.3	7870.3
47.5°	8084.1	8147.0
50°	8274.4	8409.1
52.5°	8546.6	8730.9
55°	8954.6	9199.0
57.5°	9294.2	9502.4
60°	9294.2	9401.6
62.5°	8959.7	8956.3
65°	8386.3	8334.0
67.5°	7636.0	7570.3
70°	6715.3	6612.3
72.5°	5442.8	5314.8
75°	3956.0	3780.1
77.5°	2770.4	2686.3
80°	1945.5	1986.1
82.5°	1249.7	1307.5
85°	594.5	585.6
87.5°	70.1	56.2
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P367822  
CATALOG NUMBER: PMM-SA3B-730-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)