

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P366854

Luminaire Tested: **PMM-SA1B-830-U-SLR**

Issue Date: 12/2/2019

Test Information

Test Method: LM-79-08
Report Number: P366854
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1910-543-24)
Test Lab: INNOVATION CENTER
Issue Date: 12/2/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: PMM-SA1B-830-U-SLR
Description: MESA POST TOP DECORATIVE LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR RIGHT OPTICS.
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3447 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.5 fc
 Type IV - Short - N/A

REPORT NUMBER: P366854
CATALOG NUMBER: PMM-SA1B-830-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P366854

CATALOG NUMBER: PMM-SA1B-830-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	667.6	0.0	667.6
	% Fixture	19.4	0.0	19.4
Street Side	Lumens	2779.4	0.0	2779.4
	% Fixture	80.6	0.0	80.6
Total	Lumens	3447.0	0.0	3447.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.7	1.2
10°-20°	121.1	3.5
20°-30°	213.8	6.2
30°-40°	333.0	9.7
40°-50°	548.2	15.9
50°-60°	782.5	22.7
60°-70°	829.8	24.1
70°-80°	458.3	13.3
80°-90°	118.6	3.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3447.0	100.0
0°-180°	3447.0	100.0

Coefficient of Utilization



REPORT NUMBER: P366854


CATALOG NUMBER: PMM-SA1B-830-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	263.8	7.7			
FM (30°-60°)	1336.3	38.8			
FH (60°-80°)	1078.6	31.3			G1/1800
FVH (80°-90°)	100.8	2.9			G2/225
BL (0°-30°)	112.9	3.3	B1/500		
BM (30°-60°)	327.5	9.5	B1/1000		
BH (60°-80°)	209.5	6.1	B1/500		G1/500
BVH (80°-90°)	17.8	0.5			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P366854

CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6
2.5°	486.9	489.9	492.7	487.0	481.4	475.5	469.8	461.3	452.6	444.0	435.3
5°	584.8	573.7	562.5	558.0	553.6	549.1	544.6	540.4	536.2	531.9	527.7
7.5°	615.4	599.6	583.8	577.1	570.4	563.5	556.8	541.8	526.7	511.5	496.4
10°	581.7	565.3	548.8	542.3	535.6	529.0	522.3	503.9	485.7	467.3	448.9
12.5°	608.8	592.1	575.2	554.5	533.7	512.8	492.1	481.9	471.7	461.3	451.1
15°	634.9	612.4	589.6	568.9	548.1	527.2	506.5	486.0	465.6	445.2	424.8
17.5°	730.3	692.7	655.0	617.5	579.9	542.4	504.8	481.2	457.4	433.8	410.1
20°	846.6	794.2	741.7	684.8	627.8	570.9	513.8	484.0	454.4	424.6	394.9
22.5°	985.0	918.9	852.8	781.0	709.2	637.3	565.5	522.3	479.2	435.8	392.7
25°	1094.9	1031.3	967.7	876.7	785.7	694.7	603.7	554.6	505.6	456.4	407.4
27.5°	1201.6	1100.4	999.0	894.8	790.7	686.5	582.2	536.9	491.6	446.2	400.9
30°	1291.8	1211.5	1131.2	995.2	859.1	723.0	586.9	531.2	475.5	419.8	364.1
32.5°	1423.8	1309.2	1194.4	1052.6	910.7	768.8	626.9	555.6	484.4	413.1	341.8
35°	1578.3	1459.1	1340.0	1164.5	989.1	813.6	638.1	562.7	487.0	411.6	336.0
37.5°	1866.2	1656.2	1446.1	1254.5	1062.9	871.2	679.6	591.9	504.3	416.4	328.8
40°	2025.0	1830.9	1636.8	1398.1	1159.3	920.4	681.6	591.9	502.1	412.4	322.6
42.5°	2236.6	1991.2	1745.6	1487.4	1229.4	971.2	713.1	613.7	514.3	414.8	315.4
45°	2365.6	2092.1	1818.3	1542.4	1266.6	990.7	714.8	613.9	513.0	412.1	311.2
47.5°	2448.8	2186.1	1923.2	1626.3	1329.3	1032.1	735.2	628.1	520.8	413.8	306.5
50°	2527.6	2267.4	2007.1	1698.7	1390.5	1082.2	773.8	656.9	539.9	422.8	305.8
52.5°	2624.3	2384.7	2144.9	1814.2	1483.2	1152.4	821.5	694.2	566.9	439.5	312.2
55°	2765.0	2528.9	2292.7	1937.6	1582.4	1227.4	872.2	730.8	589.6	448.2	306.8
57.5°	2856.2	2616.8	2377.3	2015.3	1653.2	1291.0	928.9	772.3	615.7	458.9	302.3
60°	2825.9	2578.9	2331.8	1986.7	1641.5	1296.3	951.2	782.0	613.0	443.9	274.7
62.5°	2692.0	2429.5	2167.0	1857.8	1548.8	1239.6	930.4	758.4	586.6	414.6	242.6
65°	2505.0	2233.6	1962.1	1683.2	1404.2	1125.3	846.4	690.3	534.1	378.0	221.7
67.5°	2275.4	1992.5	1709.4	1462.5	1215.5	968.4	721.4	590.9	460.6	330.1	199.6
70°	1987.5	1709.4	1431.4	1217.7	1004.0	790.4	576.7	478.5	380.5	282.3	184.0
72.5°	1597.5	1357.6	1117.6	949.5	781.3	613.2	445.0	376.8	308.7	240.4	172.2
75°	1136.2	995.2	854.1	723.3	592.5	461.4	330.6	286.4	242.3	198.1	153.9
77.5°	807.4	724.3	641.1	538.6	436.0	333.5	230.9	205.0	179.2	153.3	127.3
80°	597.0	527.5	458.1	380.8	303.5	226.2	148.9	136.2	123.6	110.9	98.2
82.5°	393.0	361.7	330.3	269.0	207.8	146.6	85.3	80.6	76.0	71.3	66.6
85°	176.0	185.9	195.6	158.1	120.5	83.0	45.3	43.2	41.0	38.8	36.6
87.5°	16.9	24.9	33.0	28.3	23.4	18.7	13.9	13.7	13.7	13.6	13.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854

CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6
2.5°	437.7	440.0	442.4	444.7	442.2	439.7	437.0	434.5	431.3	428.2	424.8
5°	520.7	513.5	506.5	499.3	488.6	477.8	467.0	456.3	454.9	453.4	452.1
7.5°	483.2	470.1	456.9	443.7	427.0	410.4	393.7	377.0	371.9	366.9	361.9
10°	440.0	431.0	422.1	413.1	402.7	392.3	381.8	371.4	357.7	343.8	330.1
12.5°	436.3	421.6	406.7	392.0	385.7	379.3	372.9	366.6	354.5	342.5	330.3
15°	412.9	400.9	389.0	377.0	367.8	358.5	349.3	340.1	330.4	320.6	310.9
17.5°	396.4	382.6	368.9	355.2	344.7	334.1	323.4	312.9	301.2	289.3	277.6
20°	379.1	363.6	347.8	332.1	318.7	305.5	292.1	278.7	265.9	253.1	240.3
22.5°	372.1	351.5	330.9	310.4	296.3	282.1	268.0	253.8	241.9	230.1	218.2
25°	382.8	358.4	333.8	309.2	290.3	271.2	252.3	233.2	223.4	213.5	203.5
27.5°	370.3	339.5	308.9	278.1	257.8	237.4	217.2	196.8	195.3	193.7	192.1
30°	331.8	299.5	267.2	234.9	216.3	197.6	179.0	160.3	156.8	153.1	149.6
32.5°	308.9	275.9	242.9	210.0	193.4	176.7	160.1	143.4	139.4	135.4	131.3
35°	300.2	264.4	228.5	192.7	178.5	164.3	150.1	135.9	133.0	130.3	127.5
37.5°	293.1	257.7	222.0	186.4	172.7	158.9	145.1	131.3	129.2	127.0	124.8
40°	286.4	250.5	214.3	178.2	166.0	153.9	141.7	129.5	128.2	126.8	125.3
42.5°	280.4	245.4	210.3	175.3	164.5	153.8	142.9	132.0	130.7	129.3	128.0
45°	277.1	242.9	208.8	174.7	166.8	158.9	150.9	143.1	139.9	136.7	133.3
47.5°	274.6	242.6	210.6	178.7	170.5	162.3	154.1	145.9	143.1	140.2	137.2
50°	275.1	244.4	213.7	182.9	173.0	163.0	153.1	143.1	142.7	142.4	142.0
52.5°	279.6	247.1	214.5	181.9	171.2	160.5	149.6	138.9	141.0	143.1	145.2
55°	273.1	239.3	205.3	171.5	161.3	151.2	141.0	130.8	133.7	136.4	139.2
57.5°	265.7	229.0	192.4	155.8	148.1	140.4	132.5	124.8	127.8	131.0	134.0
60°	241.3	207.8	174.3	140.9	135.7	130.5	125.3	120.1	121.5	122.8	124.1
62.5°	214.5	186.2	158.1	129.8	125.8	121.6	117.6	113.4	113.4	113.6	113.6
65°	197.4	173.2	148.9	124.6	120.1	115.6	110.9	106.4	105.7	105.1	104.4
67.5°	180.4	161.3	142.0	122.8	116.3	109.9	103.4	96.9	96.0	95.4	94.5
70°	167.0	149.9	132.8	115.8	108.4	101.2	93.9	86.5	85.8	85.3	84.7
72.5°	156.1	140.2	124.1	108.1	100.4	92.5	84.8	77.0	76.5	76.0	75.3
75°	139.7	125.7	111.4	97.2	89.7	82.3	74.8	67.3	66.6	66.1	65.4
77.5°	115.6	103.7	92.0	80.1	74.3	68.6	62.7	56.9	56.6	56.2	55.7
80°	89.0	79.8	70.4	61.2	57.4	53.4	49.5	45.5	45.3	45.2	44.8
82.5°	61.1	55.5	50.0	44.5	41.7	38.6	35.8	32.8	33.0	33.1	33.3
85°	34.8	32.8	31.0	28.9	26.6	24.4	22.1	19.7	20.2	20.7	21.1
87.5°	12.7	12.0	11.4	10.7	9.5	8.5	7.4	6.2	6.5	7.0	7.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6
2.5°	421.6	416.6	411.6	406.6	401.5	391.2	381.0	370.6	360.2	366.6	373.1
5°	450.6	442.0	433.3	424.8	416.1	411.3	406.4	401.5	396.7	399.2	401.9
7.5°	356.9	351.9	346.7	341.7	336.5	334.3	332.3	330.1	327.9	334.1	340.3
10°	316.2	309.2	302.2	295.0	287.9	283.8	279.6	275.4	271.2	272.9	274.6
12.5°	318.2	307.9	297.5	287.1	276.7	270.5	264.4	258.2	252.0	253.5	255.0
15°	301.0	290.3	279.6	268.9	258.2	251.0	243.6	236.4	229.0	226.5	223.9
17.5°	265.7	254.0	242.3	230.6	218.8	214.0	209.1	204.3	199.4	196.8	194.1
20°	227.4	216.5	205.6	194.8	183.9	180.5	177.2	173.7	170.3	168.7	166.8
22.5°	206.3	199.6	192.7	186.1	179.2	175.3	171.7	167.8	164.0	162.1	160.1
25°	193.6	194.9	196.4	197.8	199.1	197.4	195.6	193.9	192.1	192.7	193.2
27.5°	190.6	193.4	196.4	199.3	202.1	203.6	205.1	206.6	208.1	208.6	209.1
30°	145.9	147.4	148.7	150.2	151.6	155.8	160.0	164.0	168.1	174.7	181.4
32.5°	127.3	126.8	126.3	125.7	125.1	126.2	127.2	128.0	129.0	131.3	133.8
35°	124.6	123.5	122.1	121.0	119.6	120.1	120.6	121.1	121.6	123.5	125.3
37.5°	122.6	122.1	121.8	121.3	120.8	122.0	123.0	124.1	125.1	126.7	128.2
40°	124.0	123.8	123.6	123.3	123.1	123.8	124.5	125.1	125.8	127.8	129.8
42.5°	126.7	126.7	126.5	126.5	126.3	127.0	127.5	128.2	128.7	129.8	131.0
45°	130.2	129.8	129.7	129.3	129.0	128.8	128.8	128.7	128.5	129.2	130.0
47.5°	134.4	133.2	131.8	130.7	129.3	129.0	128.5	128.2	127.7	128.0	128.3
50°	141.7	138.5	135.5	132.3	129.2	128.3	127.5	126.7	125.8	125.7	125.7
52.5°	147.2	142.5	137.9	133.2	128.5	127.0	125.5	124.0	122.5	122.1	122.0
55°	141.9	138.4	135.0	131.5	128.0	125.8	123.5	121.3	119.0	118.5	118.0
57.5°	137.0	134.9	132.7	130.5	128.3	126.2	123.8	121.6	119.3	118.1	117.0
60°	125.5	125.5	125.7	125.7	125.7	123.3	121.0	118.6	116.3	115.1	114.1
62.5°	113.6	115.4	117.1	119.0	120.6	117.5	114.1	110.9	107.6	106.7	106.1
65°	103.7	104.2	104.9	105.4	105.9	103.4	100.9	98.4	95.9	95.4	94.7
67.5°	93.7	93.5	93.4	93.0	92.9	91.4	89.7	88.2	86.5	85.8	85.2
70°	84.0	83.8	83.7	83.3	83.2	81.8	80.5	79.1	77.8	77.3	76.8
72.5°	74.8	74.6	74.3	74.1	73.8	72.6	71.6	70.4	69.3	68.6	67.9
75°	64.7	64.4	64.1	63.7	63.4	62.4	61.4	60.2	59.2	58.6	57.9
77.5°	55.4	54.9	54.4	53.7	53.2	52.4	51.4	50.5	49.5	48.7	48.0
80°	44.7	44.3	44.0	43.5	43.2	42.3	41.5	40.5	39.7	38.6	37.8
82.5°	33.5	33.3	33.0	32.8	32.5	31.6	30.8	29.9	29.1	28.1	27.1
85°	21.6	21.4	21.2	21.1	20.9	20.2	19.7	19.1	18.4	17.4	16.6
87.5°	7.7	7.4	7.2	6.9	6.5	6.4	6.0	5.9	5.5	5.0	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854

CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6
2.5°	379.5	385.8	386.0	386.0	389.0	391.8	386.0	380.1	374.1	368.3	362.4
5°	404.4	406.9	406.2	405.4	401.7	398.0	394.2	390.3	386.5	382.6	382.8
7.5°	346.5	352.7	357.7	362.6	357.9	353.2	350.7	348.2	345.7	343.2	342.8
10°	276.1	277.7	279.7	281.6	278.7	275.7	280.7	285.8	290.6	295.6	290.1
12.5°	256.5	258.0	254.5	250.8	249.6	248.5	247.3	245.9	244.8	243.4	242.8
15°	221.4	218.7	216.0	213.2	212.5	211.6	210.8	209.8	209.0	208.0	205.0
17.5°	191.4	188.7	184.2	179.5	177.7	175.7	175.2	174.7	174.0	173.5	170.7
20°	165.1	163.3	162.1	160.8	158.9	157.1	155.3	153.4	151.4	149.6	146.9
22.5°	158.3	156.3	154.8	153.1	152.8	152.4	149.1	145.6	142.2	138.7	137.2
25°	193.9	194.4	185.2	175.8	175.0	174.2	168.1	162.0	155.9	149.7	144.6
27.5°	209.5	210.0	209.6	209.3	206.6	203.8	193.6	183.2	173.0	162.6	155.3
30°	187.9	194.4	196.9	199.4	197.6	195.6	184.9	174.3	163.6	152.9	148.1
32.5°	136.2	138.5	142.7	146.7	148.9	150.9	147.6	144.2	140.9	137.5	136.7
35°	127.0	128.8	129.7	130.5	129.2	127.8	125.3	122.8	120.1	117.6	117.1
37.5°	129.5	131.0	132.7	134.4	130.7	126.8	124.0	121.3	118.5	115.6	113.3
40°	131.8	133.8	134.9	135.9	132.2	128.5	125.0	121.6	118.1	114.6	112.3
42.5°	132.2	133.3	135.2	137.0	131.8	126.5	123.3	120.0	116.8	113.4	111.1
45°	130.7	131.3	133.0	134.7	128.7	122.5	119.6	116.6	113.8	110.8	108.8
47.5°	128.5	128.8	130.2	131.3	125.0	118.5	115.8	113.1	110.3	107.6	105.6
50°	125.5	125.3	126.3	127.2	120.6	114.1	111.4	108.9	106.2	103.6	101.9
52.5°	121.6	121.3	122.3	123.1	116.3	109.4	107.1	104.9	102.6	100.2	98.9
55°	117.3	116.8	117.6	118.5	111.8	104.9	102.9	100.7	98.7	96.5	95.4
57.5°	115.6	114.4	114.9	115.4	107.9	100.4	98.4	96.4	94.4	92.4	91.5
60°	112.9	111.8	112.3	112.6	104.6	96.4	94.5	92.5	90.7	88.7	87.8
62.5°	105.2	104.4	105.1	105.7	98.5	91.2	89.5	88.0	86.3	84.7	83.5
65°	94.2	93.5	94.9	96.2	90.0	83.8	82.8	81.8	80.6	79.6	78.5
67.5°	84.5	83.8	85.2	86.5	82.0	77.5	76.5	75.5	74.5	73.4	72.8
70°	76.3	75.8	77.0	78.1	74.3	70.4	69.4	68.6	67.6	66.6	66.1
72.5°	67.1	66.4	67.9	69.3	66.1	62.7	61.9	60.9	60.1	59.1	58.7
75°	57.2	56.6	57.9	59.1	56.9	54.5	53.7	52.9	52.0	51.2	51.0
77.5°	47.2	46.3	47.7	48.9	47.5	46.0	45.3	44.5	43.8	43.0	43.0
80°	36.8	35.8	36.8	37.6	37.1	36.6	36.1	35.5	35.0	34.3	34.5
82.5°	26.1	25.1	25.6	26.1	26.4	26.8	26.8	26.8	26.8	26.8	26.8
85°	15.6	14.6	14.7	14.9	15.4	15.9	16.1	16.2	16.4	16.6	16.7
87.5°	4.0	3.5	3.2	2.7	3.2	3.5	3.8	4.0	4.4	4.5	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854

CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6
2.5°	356.5	350.5	344.7	348.3	351.9	355.5	359.1	359.2	359.2	359.4	359.4
5°	383.1	383.3	383.5	380.0	376.6	373.1	369.6	367.8	365.9	363.9	362.1
7.5°	342.3	342.0	341.5	338.1	334.8	331.4	328.1	320.1	311.9	303.8	295.6
10°	284.4	278.9	273.2	271.9	270.7	269.4	268.0	265.9	263.9	261.7	259.5
12.5°	242.1	241.4	240.8	237.2	233.7	230.1	226.5	226.5	226.5	226.5	226.5
15°	201.8	198.8	195.6	193.9	192.1	190.4	188.6	187.7	186.9	186.1	185.2
17.5°	167.6	164.8	161.8	161.5	161.1	160.8	160.5	159.6	158.8	157.9	157.1
20°	144.2	141.5	138.9	139.9	140.9	141.7	142.7	141.9	141.0	140.0	139.2
22.5°	135.5	134.0	132.3	131.5	130.7	129.7	128.8	128.8	129.0	129.0	129.0
25°	139.5	134.4	129.2	126.7	124.1	121.5	119.0	118.0	117.1	116.1	115.1
27.5°	147.9	140.4	133.0	128.7	124.3	120.0	115.6	113.8	111.8	109.9	107.9
30°	143.1	138.2	133.2	128.2	123.1	118.1	113.1	110.8	108.4	105.9	103.6
32.5°	135.9	134.9	134.0	129.3	124.6	119.8	115.1	114.1	113.3	112.3	111.3
35°	116.4	115.9	115.3	114.1	112.9	111.8	110.6	109.3	107.9	106.6	105.2
37.5°	111.1	108.8	106.4	105.9	105.4	104.9	104.4	103.9	103.4	102.7	102.2
40°	109.9	107.6	105.2	104.4	103.6	102.6	101.7	101.9	102.2	102.4	102.6
42.5°	108.6	106.2	103.7	103.1	102.4	101.7	101.1	101.2	101.6	101.7	101.9
45°	106.9	104.9	102.9	101.7	100.7	99.6	98.4	99.4	100.4	101.2	102.2
47.5°	103.6	101.4	99.4	98.7	98.0	97.2	96.5	97.5	98.5	99.4	100.4
50°	100.1	98.4	96.5	96.4	96.2	95.9	95.7	96.4	97.0	97.7	98.4
52.5°	97.4	96.0	94.5	94.5	94.4	94.4	94.2	94.9	95.5	96.0	96.7
55°	94.4	93.2	92.0	92.2	92.5	92.7	92.9	93.5	94.4	95.0	95.7
57.5°	90.5	89.7	88.7	89.3	89.8	90.5	91.0	91.5	92.2	92.7	93.2
60°	86.8	86.0	85.0	85.7	86.5	87.2	87.8	88.3	88.8	89.3	89.8
62.5°	82.3	81.0	79.8	80.8	81.6	82.7	83.5	83.8	84.3	84.7	85.0
65°	77.5	76.3	75.1	75.8	76.5	77.0	77.6	78.1	78.6	79.1	79.6
67.5°	71.9	71.3	70.4	70.9	71.4	71.9	72.4	72.6	72.6	72.8	72.8
70°	65.4	64.9	64.2	64.6	65.1	65.4	65.8	65.8	65.8	65.6	65.6
72.5°	58.6	58.2	57.9	58.1	58.4	58.6	58.7	58.6	58.4	58.2	58.1
75°	50.9	50.7	50.5	50.7	51.0	51.2	51.4	51.2	50.9	50.7	50.4
77.5°	43.2	43.2	43.2	43.2	43.3	43.3	43.3	43.0	42.7	42.3	42.0
80°	34.6	34.8	35.0	35.0	35.0	35.0	35.0	34.6	34.3	33.8	33.5
82.5°	26.8	26.8	26.8	26.8	26.9	26.9	26.9	26.1	25.4	24.6	23.8
85°	16.7	16.9	16.9	17.1	17.2	17.2	17.4	16.2	15.2	14.1	12.9
87.5°	4.5	4.5	4.5	4.5	4.5	4.4	4.4	3.3	2.2	1.2	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6
2.5°	360.4	361.4	362.2	363.2	363.4	363.6	363.6	363.7	360.2	356.7	353.0
5°	364.6	366.9	369.4	371.8	371.3	370.8	370.3	369.8	368.8	367.9	366.9
7.5°	293.8	292.1	290.3	288.4	290.0	291.5	293.0	294.5	295.1	295.8	296.3
10°	255.3	251.1	247.0	242.8	240.4	237.9	235.6	233.1	232.7	232.6	232.2
12.5°	222.2	217.7	213.3	208.8	207.5	206.0	204.6	203.1	204.5	205.8	207.0
15°	183.4	181.7	179.9	178.0	179.5	181.0	182.5	184.0	185.4	186.6	187.9
17.5°	156.3	155.6	154.8	153.9	155.3	156.8	158.1	159.4	162.5	165.5	168.5
20°	138.5	138.0	137.4	136.7	136.2	135.5	135.0	134.4	138.7	142.9	147.2
22.5°	128.0	127.0	126.0	125.0	125.1	125.3	125.3	125.5	129.0	132.7	136.2
25°	114.8	114.4	114.1	113.8	114.8	115.8	116.6	117.6	120.8	124.0	127.0
27.5°	108.1	108.3	108.4	108.6	109.9	111.4	112.8	114.1	116.3	118.5	120.6
30°	104.4	105.4	106.2	107.1	107.6	108.1	108.6	109.1	111.3	113.3	115.4
32.5°	109.9	108.6	107.1	105.7	106.4	107.2	107.9	108.6	110.6	112.6	114.6
35°	104.7	104.1	103.6	102.9	103.7	104.6	105.2	106.1	107.9	109.6	111.4
37.5°	102.1	101.9	101.7	101.6	102.1	102.6	102.9	103.4	105.1	106.7	108.3
40°	101.9	101.1	100.4	99.6	100.1	100.6	100.9	101.4	103.4	105.4	107.4
42.5°	100.9	99.9	98.7	97.7	98.2	98.9	99.4	99.9	102.1	104.1	106.2
45°	100.7	99.2	97.5	96.0	96.7	97.4	98.0	98.7	100.4	102.1	103.6
47.5°	98.9	97.4	95.9	94.4	94.7	95.0	95.2	95.5	97.0	98.4	99.9
50°	97.4	96.2	95.2	94.0	93.5	93.2	92.7	92.2	93.4	94.5	95.7
52.5°	95.5	94.4	93.0	91.9	91.2	90.5	89.8	89.2	90.2	91.0	92.0
55°	94.4	92.9	91.5	90.0	89.2	88.3	87.5	86.7	87.3	87.8	88.5
57.5°	91.9	90.5	89.0	87.7	86.7	85.7	84.5	83.5	83.8	84.2	84.5
60°	88.5	87.0	85.7	84.2	83.0	81.8	80.5	79.3	79.5	79.8	80.0
62.5°	83.7	82.3	80.8	79.5	78.1	77.0	75.6	74.3	74.6	74.8	75.1
65°	78.3	76.8	75.5	74.0	72.8	71.6	70.3	69.1	69.4	69.8	69.9
67.5°	71.8	70.6	69.6	68.4	67.4	66.3	65.3	64.1	64.2	64.4	64.6
70°	64.7	63.7	62.9	61.9	61.1	60.2	59.4	58.6	58.6	58.7	58.7
72.5°	57.2	56.4	55.5	54.7	53.9	53.2	52.4	51.5	51.9	52.2	52.4
75°	49.5	48.9	48.0	47.2	46.5	45.8	45.0	44.3	44.7	45.0	45.2
77.5°	41.5	41.0	40.3	39.8	39.2	38.5	37.6	37.0	37.3	37.6	37.8
80°	33.1	32.8	32.3	32.0	31.3	30.6	29.9	29.3	29.4	29.4	29.6
82.5°	23.9	24.1	24.1	24.3	23.8	23.1	22.6	21.9	21.9	21.9	21.8
85°	13.4	14.1	14.6	15.1	14.6	14.1	13.6	13.1	12.9	12.9	12.7
87.5°	0.5	0.8	1.3	1.7	1.5	1.3	1.0	0.8	1.0	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6
2.5°	349.5	352.4	355.2	358.0	360.9	365.2	369.6	374.1	378.6	376.1	373.4
5°	365.9	367.6	369.4	371.1	372.8	377.6	382.3	388.2	393.9	393.2	392.3
7.5°	297.0	299.3	301.7	303.8	306.2	313.5	320.9	327.1	333.3	332.4	331.4
10°	231.9	236.7	241.8	246.6	251.5	257.5	263.3	268.5	273.7	282.4	291.0
12.5°	208.3	215.8	223.4	230.9	238.4	242.8	247.0	253.6	260.3	265.0	269.9
15°	189.1	196.1	203.1	210.1	217.2	217.5	217.8	224.9	231.9	235.9	239.8
17.5°	171.5	175.3	179.2	182.9	186.7	185.4	184.0	187.4	190.6	192.2	194.1
20°	151.4	154.1	156.8	159.4	162.1	164.0	165.6	167.6	169.5	167.8	166.0
22.5°	139.7	143.7	147.9	151.9	155.9	157.1	158.1	156.9	155.8	155.3	154.8
25°	130.2	135.0	140.0	144.9	149.7	152.1	154.4	155.4	156.3	154.4	152.6
27.5°	122.8	128.7	134.4	140.2	145.9	150.1	154.3	155.4	156.4	155.1	153.6
30°	117.5	123.8	130.2	136.5	142.9	149.2	155.4	161.0	166.3	165.8	165.3
32.5°	116.6	121.0	125.3	129.7	134.0	138.0	141.9	142.2	142.4	141.0	139.5
35°	113.1	115.9	118.8	121.6	124.5	127.0	129.3	129.0	128.7	127.3	126.0
37.5°	109.9	112.8	115.8	118.6	121.5	125.8	130.0	129.2	128.2	126.8	125.5
40°	109.4	112.6	115.8	118.8	122.0	126.0	130.0	129.2	128.3	126.7	125.0
42.5°	108.3	111.4	114.4	117.6	120.6	125.5	130.2	128.7	127.0	125.7	124.3
45°	105.2	108.1	110.9	113.8	116.6	121.8	127.0	125.1	123.3	122.8	122.1
47.5°	101.2	104.1	106.9	109.8	112.6	117.8	122.8	121.3	119.6	119.5	119.1
50°	96.9	99.6	102.4	105.1	107.7	112.9	118.0	116.6	115.3	115.4	115.4
52.5°	92.9	95.4	97.7	100.2	102.6	107.7	112.8	111.8	110.6	110.9	111.1
55°	89.0	91.0	93.0	95.0	97.0	102.1	107.1	105.6	104.1	104.6	105.1
57.5°	84.8	86.5	88.2	89.7	91.4	96.4	101.2	99.6	97.7	98.5	99.2
60°	80.1	81.6	83.2	84.5	86.0	90.5	94.9	93.4	91.7	92.9	93.9
62.5°	75.3	76.5	77.6	78.8	80.0	84.2	88.3	87.2	86.0	87.3	88.5
65°	70.3	71.1	72.1	72.9	73.8	77.8	81.6	80.8	80.0	81.1	82.3
67.5°	64.7	65.4	66.3	66.9	67.6	71.3	75.0	74.1	73.1	74.1	75.0
70°	58.7	59.4	59.9	60.6	61.1	64.4	67.8	66.6	65.3	66.3	67.1
72.5°	52.7	53.0	53.5	53.9	54.2	56.7	59.2	58.2	57.2	58.2	59.1
75°	45.5	45.8	46.2	46.5	46.8	49.0	51.0	49.9	48.5	49.5	50.5
77.5°	38.1	38.3	38.6	38.8	39.0	40.5	41.8	40.7	39.3	40.5	41.7
80°	29.6	29.8	29.9	29.9	30.1	30.6	31.1	30.3	29.3	30.8	32.3
82.5°	21.8	21.6	21.6	21.4	21.2	21.2	21.1	20.6	19.9	21.2	22.6
85°	12.5	12.4	12.0	11.9	11.5	11.0	10.5	10.4	10.2	11.4	12.5
87.5°	1.3	1.2	0.8	0.7	0.3	0.2	0.0	0.0	0.0	0.7	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854

CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6
2.5°	370.9	368.3	365.7	363.2	360.7	358.2	362.9	367.6	372.3	377.0	381.1
5°	391.7	390.8	388.7	386.7	384.5	382.3	383.5	384.8	386.0	387.2	389.7
7.5°	330.6	329.6	334.3	338.8	343.5	348.0	349.2	350.2	351.4	352.4	351.7
10°	299.7	308.2	310.4	312.4	314.5	316.6	319.9	323.2	326.4	329.8	331.6
12.5°	274.6	279.2	286.9	294.8	302.5	310.2	315.2	320.2	325.3	330.3	340.6
15°	243.8	247.6	253.5	259.3	265.2	271.0	278.2	285.6	292.8	300.0	311.4
17.5°	195.8	197.4	201.8	206.1	210.3	214.7	224.4	233.9	243.6	253.1	266.2
20°	164.3	162.5	162.5	162.6	162.6	162.6	172.3	181.9	191.6	201.1	218.3
22.5°	154.1	153.6	151.8	149.7	147.9	145.9	150.9	156.1	161.1	166.1	180.2
25°	150.6	148.7	146.4	144.1	141.7	139.4	142.5	145.7	148.9	152.1	163.1
27.5°	152.3	150.7	151.9	152.9	154.1	155.1	156.1	157.1	158.1	159.1	163.0
30°	164.8	164.3	166.1	167.8	169.7	171.3	169.0	166.8	164.5	162.1	163.5
32.5°	138.2	136.7	136.0	135.4	134.7	134.0	133.8	133.7	133.3	133.2	136.2
35°	124.6	123.3	122.3	121.3	120.1	119.1	119.6	120.0	120.5	120.8	124.1
37.5°	124.1	122.8	121.6	120.5	119.1	118.0	118.5	119.1	119.6	120.1	122.6
40°	123.3	121.6	121.0	120.3	119.6	119.0	119.3	119.6	119.8	120.1	122.0
42.5°	122.8	121.5	121.1	120.8	120.5	120.1	120.5	120.8	121.0	121.3	123.5
45°	121.6	121.0	121.3	121.6	122.0	122.3	122.3	122.3	122.3	122.3	124.6
47.5°	119.0	118.6	119.6	120.6	121.6	122.6	124.3	126.0	127.5	129.2	129.7
50°	115.6	115.6	117.3	119.0	120.5	122.1	126.2	130.0	134.0	137.9	135.4
52.5°	111.4	111.6	114.1	116.4	119.0	121.3	125.0	128.7	132.2	135.9	132.2
55°	105.4	105.9	109.1	112.1	115.3	118.3	121.1	124.0	126.8	129.7	125.8
57.5°	100.1	100.7	104.1	107.2	110.6	113.8	115.4	117.3	119.0	120.6	118.1
60°	95.0	96.0	100.4	104.7	108.9	113.3	111.9	110.6	109.1	107.7	107.6
62.5°	89.8	91.0	95.0	99.0	102.9	106.9	104.9	102.9	100.7	98.7	99.6
65°	83.3	84.5	86.3	88.2	89.8	91.7	91.5	91.5	91.4	91.2	92.9
67.5°	76.0	76.8	78.0	79.0	80.1	81.1	81.8	82.7	83.3	84.0	86.0
70°	68.1	68.9	70.1	71.1	72.3	73.3	74.1	75.0	75.6	76.5	78.5
72.5°	60.1	60.9	62.1	63.2	64.2	65.4	66.1	66.8	67.3	67.9	69.6
75°	51.5	52.5	53.7	54.7	55.9	56.9	57.4	57.9	58.4	58.9	60.4
77.5°	42.8	44.0	45.2	46.3	47.5	48.7	48.9	49.0	49.2	49.4	50.7
80°	33.6	35.1	36.3	37.5	38.6	39.8	39.8	39.8	39.8	39.8	40.5
82.5°	23.9	25.3	26.6	27.8	29.1	30.3	30.3	30.1	30.1	29.9	29.9
85°	13.7	14.9	15.7	16.7	17.6	18.4	18.4	18.4	18.2	18.2	17.9
87.5°	2.2	2.8	3.2	3.7	4.0	4.4	4.2	4.2	4.0	3.8	3.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6
2.5°	385.3	389.5	393.7	393.0	392.3	391.7	391.0	393.5	395.9	398.4	400.7
5°	392.0	394.5	396.9	398.7	400.5	402.4	404.2	412.8	421.1	429.7	438.0
7.5°	351.0	350.2	349.5	357.4	365.4	373.3	381.1	392.0	402.9	413.8	424.6
10°	333.5	335.3	337.1	340.3	343.7	346.8	350.0	360.7	371.4	382.1	392.8
12.5°	350.9	361.2	371.4	373.9	376.6	379.1	381.6	383.8	386.0	388.0	390.2
15°	322.7	334.1	345.5	352.0	358.5	364.9	371.4	387.8	404.1	420.5	436.7
17.5°	279.1	292.1	305.0	321.1	337.1	353.2	369.3	384.3	399.4	414.3	429.3
20°	235.6	252.6	269.9	287.4	304.8	322.4	339.8	354.5	369.3	383.8	398.5
22.5°	194.1	208.1	222.0	243.4	264.7	286.1	307.4	334.8	362.1	389.5	416.8
25°	174.0	185.0	195.9	218.0	240.1	262.0	284.1	319.7	355.2	390.8	426.3
27.5°	167.0	170.8	174.7	194.8	214.7	234.7	254.6	293.1	331.6	369.9	408.4
30°	164.8	166.1	167.5	183.2	198.9	214.7	230.4	268.4	306.5	344.5	382.5
32.5°	139.0	142.0	144.9	160.3	175.5	190.9	206.1	244.4	282.6	320.9	359.1
35°	127.5	130.8	134.2	149.2	164.3	179.2	194.2	234.6	275.1	315.4	355.7
37.5°	125.1	127.7	130.2	147.2	164.3	181.4	198.4	239.3	280.1	320.9	361.7
40°	124.0	125.8	127.7	144.2	161.0	177.5	194.1	236.9	279.6	322.4	365.1
42.5°	125.5	127.7	129.7	144.7	159.6	174.7	189.6	233.9	278.1	322.4	366.6
45°	126.8	129.2	131.3	145.4	159.4	173.5	187.6	234.9	282.1	329.4	376.6
47.5°	130.0	130.5	130.8	143.1	155.1	167.3	179.4	227.5	275.7	323.7	371.9
50°	132.7	130.2	127.5	140.2	152.8	165.5	178.0	223.7	269.4	314.9	360.6
52.5°	128.5	124.6	121.0	134.7	148.4	162.0	175.7	221.4	267.2	312.9	358.5
55°	122.1	118.3	114.4	128.3	142.2	156.1	170.0	215.5	261.2	306.7	352.2
57.5°	115.8	113.3	110.8	122.1	133.7	145.1	156.4	205.8	255.0	304.3	353.5
60°	107.4	107.1	106.9	115.8	124.8	133.7	142.5	190.9	239.1	287.4	335.6
62.5°	100.2	101.1	101.7	108.9	116.1	123.1	130.3	177.0	223.9	270.5	317.2
65°	94.7	96.4	98.0	106.2	114.4	122.5	130.7	169.8	209.0	248.1	287.3
67.5°	88.0	90.0	92.0	102.7	113.4	124.1	134.9	167.1	199.4	231.7	264.0
70°	80.3	82.3	84.2	97.9	111.4	125.1	138.7	167.3	196.1	224.7	253.3
72.5°	71.3	72.9	74.6	89.3	104.1	118.8	133.5	157.8	182.0	206.1	230.4
75°	62.1	63.6	65.1	77.8	90.5	103.2	115.9	134.7	153.3	172.0	190.6
77.5°	51.9	53.2	54.4	62.9	71.4	80.0	88.5	102.9	117.1	131.5	145.7
80°	41.2	41.8	42.5	47.5	52.4	57.4	62.2	71.8	81.3	90.7	100.2
82.5°	30.1	30.1	30.1	33.3	36.6	39.8	43.0	47.9	52.5	57.4	62.1
85°	17.6	17.1	16.7	18.9	21.1	23.3	25.4	27.4	29.4	31.5	33.5
87.5°	2.8	2.2	1.7	3.0	4.4	5.7	7.0	7.7	8.5	9.2	9.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854

CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6
2.5°	395.0	389.5	383.8	378.1	386.5	394.9	403.2	411.6	433.8	447.1	447.9
5°	445.0	452.1	459.1	466.1	473.2	480.2	487.0	494.1	530.2	552.5	556.6
7.5°	436.2	447.9	459.4	471.0	490.9	510.8	530.7	550.6	581.2	603.3	617.9
10°	407.2	421.6	436.0	450.4	474.0	497.8	521.3	544.9	577.4	606.5	620.4
12.5°	413.1	436.0	458.8	481.7	502.1	522.7	543.1	563.5	585.9	597.0	622.2
15°	452.6	468.5	484.4	500.3	531.0	561.7	592.5	623.1	635.8	661.0	683.8
17.5°	458.6	487.7	517.0	546.1	583.8	621.4	659.0	696.7	720.3	752.9	780.3
20°	439.9	481.0	522.3	563.5	612.0	660.7	709.2	757.8	787.7	815.1	857.6
22.5°	462.3	507.8	553.1	598.6	663.1	727.3	791.7	856.0	918.5	979.8	1008.6
25°	487.0	547.9	608.7	669.4	749.9	830.2	910.7	991.0	1071.5	1128.9	1162.0
27.5°	469.6	530.7	591.9	653.0	752.6	852.3	951.8	1051.4	1137.6	1206.7	1235.1
30°	457.4	532.4	607.3	682.3	799.1	915.9	1032.6	1149.4	1229.1	1306.2	1348.0
32.5°	455.3	551.5	647.5	743.7	879.7	1015.6	1151.6	1287.5	1340.3	1408.8	1465.1
35°	461.3	567.0	672.6	778.2	934.1	1090.0	1245.8	1401.7	1476.9	1544.6	1594.0
37.5°	479.7	597.6	715.4	833.4	1021.3	1209.3	1397.2	1585.1	1711.1	1835.1	1857.2
40°	490.1	615.2	740.2	865.2	1083.7	1302.2	1520.7	1739.2	1884.1	2020.1	2029.3
42.5°	502.3	638.0	773.5	909.2	1151.4	1393.9	1636.1	1878.4	2057.8	2204.0	2208.3
45°	516.3	655.9	795.6	935.1	1188.1	1440.9	1693.9	1946.7	2163.5	2341.2	2297.9
47.5°	521.8	671.9	821.8	971.7	1241.5	1511.0	1780.7	2050.2	2244.8	2406.4	2365.0
50°	524.0	687.7	851.1	1014.6	1294.0	1573.6	1853.0	2132.4	2330.3	2487.9	2424.3
52.5°	537.6	716.6	895.6	1074.6	1365.8	1656.9	1948.0	2239.1	2433.9	2585.3	2506.3
55°	555.8	759.4	962.9	1166.5	1467.8	1769.0	2070.3	2371.5	2566.9	2707.8	2609.9
57.5°	572.7	792.1	1011.2	1230.4	1542.6	1855.0	2167.2	2479.4	2677.3	2816.7	2721.8
60°	564.5	793.4	1022.3	1251.2	1558.0	1864.7	2171.5	2478.2	2702.9	2870.1	2821.5
62.5°	539.7	762.3	984.6	1207.2	1498.4	1789.6	2080.9	2372.0	2635.0	2849.3	2847.1
65°	492.1	696.9	901.5	1106.3	1375.8	1645.5	1915.1	2184.6	2494.6	2755.0	2771.9
67.5°	434.0	604.0	774.0	944.0	1197.8	1451.6	1705.4	1959.2	2290.7	2577.9	2592.5
70°	377.8	502.4	626.9	751.4	974.3	1197.1	1419.8	1642.7	1977.5	2268.1	2281.5
72.5°	311.9	393.4	474.7	556.1	736.7	917.2	1097.6	1278.1	1572.1	1795.6	1871.0
75°	238.9	287.3	335.6	384.0	530.0	676.1	822.0	968.1	1163.5	1328.5	1413.5
77.5°	170.8	195.9	221.0	246.1	370.3	494.4	618.4	742.5	845.3	938.8	996.2
80°	112.1	123.8	135.7	147.4	250.6	353.9	456.9	560.2	622.7	672.9	701.9
82.5°	67.9	73.8	79.5	85.3	169.0	252.6	336.1	419.8	455.6	479.5	505.3
85°	36.6	39.8	43.0	46.2	99.9	153.4	207.1	260.7	264.2	267.0	305.3
87.5°	10.7	11.7	12.5	13.4	22.1	31.0	39.7	48.4	30.1	18.7	38.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854

CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6
2.5°	443.0	440.9	438.7	436.3	434.2	425.0	415.9	406.7	397.5	406.4	415.1
5°	551.8	558.5	565.0	571.7	578.4	578.9	579.2	579.7	580.1	581.7	583.4
7.5°	630.1	642.0	653.7	665.6	677.4	686.6	695.8	705.2	714.4	706.1	697.7
10°	636.8	661.9	687.0	712.1	737.2	741.7	746.0	750.6	755.1	761.1	767.0
12.5°	643.5	674.1	704.6	735.2	765.8	779.2	792.4	805.8	819.0	825.5	831.9
15°	714.3	732.3	750.2	768.3	786.2	795.4	804.4	813.6	822.8	828.4	833.7
17.5°	805.3	812.0	818.5	825.2	831.9	838.1	844.3	850.4	856.6	857.6	858.6
20°	888.3	889.6	890.8	892.1	893.3	880.2	867.3	854.3	841.2	843.6	845.8
22.5°	1012.7	1005.4	998.2	990.8	983.6	959.0	934.6	910.0	885.6	875.0	864.7
25°	1200.1	1181.4	1162.7	1143.9	1125.2	1086.0	1047.0	1007.9	968.9	946.0	923.2
27.5°	1260.5	1219.7	1179.0	1138.2	1097.4	1067.8	1038.3	1008.7	979.3	943.0	906.7
30°	1382.7	1318.3	1254.0	1189.6	1125.2	1096.6	1068.0	1039.2	1010.6	973.4	936.4
32.5°	1490.9	1424.0	1357.1	1290.0	1223.0	1168.8	1114.6	1060.4	1006.2	981.1	956.0
35°	1616.2	1532.1	1447.9	1363.8	1279.6	1233.1	1186.7	1140.2	1093.9	1055.9	1018.1
37.5°	1798.8	1709.3	1619.7	1530.1	1440.6	1377.6	1314.9	1252.0	1189.3	1168.3	1147.6
40°	1972.8	1867.0	1761.5	1655.7	1550.1	1502.0	1453.8	1405.4	1357.2	1321.9	1286.6
42.5°	2118.5	2013.9	1909.5	1805.0	1700.6	1665.4	1630.5	1595.3	1560.4	1531.2	1502.1
45°	2168.5	2083.2	1998.0	1912.7	1827.4	1815.0	1802.8	1790.4	1778.2	1756.6	1735.0
47.5°	2249.0	2162.0	2075.2	1988.2	1901.2	1905.7	1910.2	1914.9	1919.4	1920.6	1921.6
50°	2296.4	2213.7	2131.2	2048.6	1966.1	1988.0	2009.7	2031.7	2053.6	2103.3	2152.8
52.5°	2365.5	2284.3	2203.3	2122.2	2041.0	2078.2	2115.2	2152.3	2189.3	2258.9	2328.5
55°	2452.1	2374.5	2297.0	2219.4	2141.9	2178.1	2214.0	2250.2	2286.1	2363.6	2441.1
57.5°	2567.1	2483.9	2400.9	2317.8	2234.8	2268.1	2301.2	2334.5	2367.6	2441.2	2514.9
60°	2697.9	2607.6	2517.2	2426.7	2336.3	2345.5	2354.6	2363.8	2372.8	2452.6	2532.3
62.5°	2762.2	2678.5	2595.0	2511.4	2427.7	2402.1	2376.5	2350.7	2325.1	2396.6	2467.8
65°	2706.4	2648.9	2591.5	2533.9	2476.4	2431.2	2386.2	2341.0	2295.9	2340.5	2385.0
67.5°	2529.1	2496.5	2464.0	2431.4	2398.7	2323.0	2247.2	2171.2	2095.4	2098.4	2101.3
70°	2241.6	2232.9	2224.4	2215.7	2207.0	2093.1	1979.3	1865.4	1751.4	1734.0	1716.6
72.5°	1877.4	1883.1	1888.6	1894.3	1900.0	1777.5	1655.0	1532.6	1410.1	1381.2	1352.2
75°	1454.1	1485.6	1517.0	1548.6	1580.1	1463.0	1345.9	1228.6	1111.5	1075.8	1040.2
77.5°	1027.5	1086.2	1144.7	1203.5	1262.2	1156.3	1050.6	944.6	838.7	815.6	792.6
80°	716.4	745.2	774.0	802.8	831.5	778.3	725.1	671.9	618.7	625.1	631.3
82.5°	521.8	528.5	535.1	541.8	548.4	526.7	504.9	483.0	461.3	477.8	494.4
85°	334.3	358.2	382.0	405.9	429.7	405.6	381.5	357.2	333.1	344.2	355.2
87.5°	74.8	118.3	161.8	205.5	249.0	225.5	202.3	178.9	155.4	144.9	134.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854

CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6
2.5°	424.0	432.8	430.2	427.6	425.0	422.3	427.1	432.0	437.0	441.9	440.2
5°	585.3	586.9	571.0	555.3	539.4	523.5	533.4	543.3	553.1	563.0	559.5
7.5°	689.3	681.0	671.8	662.6	653.2	644.0	642.0	640.0	637.8	635.8	633.1
10°	773.0	778.8	772.8	767.0	760.9	754.9	740.9	726.8	712.6	698.5	692.7
12.5°	838.4	844.9	846.4	847.8	849.3	850.8	835.1	819.5	803.8	788.0	773.8
15°	839.2	844.8	849.6	854.3	859.1	863.8	854.1	844.6	834.9	825.2	820.7
17.5°	859.8	860.8	856.8	853.0	848.9	845.1	841.2	837.6	833.7	830.0	822.8
20°	848.1	850.4	849.9	849.4	848.8	848.3	848.6	848.8	849.1	849.3	845.3
22.5°	854.1	843.6	845.8	847.8	849.9	852.0	858.0	864.0	870.2	876.2	892.3
25°	900.3	877.4	873.9	870.5	867.0	863.7	879.4	895.0	910.7	926.4	952.5
27.5°	870.2	833.9	825.9	817.8	809.8	801.8	825.7	849.4	873.4	897.3	923.9
30°	899.3	862.3	844.6	826.9	809.0	791.2	814.1	836.9	859.8	882.6	912.0
32.5°	930.9	905.8	893.9	882.2	870.4	858.6	860.5	862.3	864.2	866.0	907.5
35°	980.1	942.1	930.4	918.7	907.0	895.3	914.9	934.3	953.8	973.3	1008.4
37.5°	1126.7	1105.8	1084.7	1063.6	1042.4	1021.3	1032.8	1044.4	1055.9	1067.4	1100.6
40°	1251.3	1216.0	1212.5	1209.2	1205.6	1202.1	1203.1	1204.0	1205.0	1206.0	1234.3
42.5°	1472.8	1443.7	1425.8	1407.9	1390.0	1372.1	1371.0	1369.8	1368.4	1367.3	1388.5
45°	1713.3	1691.7	1678.3	1664.9	1651.4	1638.0	1616.7	1595.5	1574.1	1552.8	1571.4
47.5°	1922.7	1923.9	1948.2	1972.3	1996.5	2020.8	1984.5	1948.2	1911.9	1875.6	1851.6
50°	2202.5	2252.0	2257.9	2263.6	2269.4	2275.3	2213.7	2152.3	2090.7	2029.2	2004.1
52.5°	2398.2	2467.8	2458.8	2449.9	2440.9	2431.9	2396.2	2360.8	2325.1	2289.5	2234.8
55°	2518.7	2596.2	2589.3	2582.6	2575.8	2568.9	2543.0	2517.0	2491.1	2465.2	2405.1
57.5°	2588.5	2662.1	2664.1	2666.1	2668.1	2670.1	2663.3	2656.4	2649.6	2642.7	2564.6
60°	2612.1	2691.9	2692.7	2693.4	2694.2	2694.9	2684.0	2673.1	2662.1	2651.2	2600.2
62.5°	2539.3	2610.6	2613.7	2616.8	2619.9	2623.1	2615.6	2608.1	2600.5	2593.0	2555.2
65°	2429.7	2474.4	2475.2	2475.9	2476.7	2477.6	2458.5	2439.6	2420.5	2401.4	2392.4
67.5°	2104.3	2107.3	2125.0	2142.8	2160.5	2178.2	2179.7	2181.2	2182.9	2184.4	2171.4
70°	1699.2	1681.8	1701.1	1720.3	1739.5	1758.8	1767.0	1775.2	1783.5	1791.7	1797.8
72.5°	1323.1	1294.2	1308.4	1322.6	1337.0	1351.2	1339.0	1326.8	1314.6	1302.4	1341.0
75°	1004.5	968.9	967.1	965.4	963.5	961.9	955.7	949.5	943.1	936.9	973.1
77.5°	769.3	746.2	747.4	748.4	749.6	750.6	744.2	738.0	731.7	725.3	739.2
80°	637.6	643.8	644.0	644.2	644.3	644.5	638.5	632.6	626.6	620.6	610.5
82.5°	511.1	527.7	527.5	527.5	527.4	527.2	526.9	526.5	526.0	525.7	509.3
85°	366.2	377.3	365.9	354.5	343.2	331.8	340.1	348.5	357.0	365.4	358.5
87.5°	124.0	113.6	100.1	86.7	73.1	59.6	74.1	88.7	103.4	118.0	126.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854

CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6
2.5°	438.7	437.0	435.5	425.0	414.3	403.7	393.0	412.4	432.0	451.4	470.8
5°	556.1	552.6	549.3	548.4	547.6	546.6	545.8	555.6	565.5	575.2	585.1
7.5°	630.4	627.8	625.1	618.0	611.2	604.2	597.1	603.2	609.0	615.0	620.9
10°	687.0	681.1	675.3	660.0	645.0	629.8	614.5	610.0	605.5	601.0	596.5
12.5°	759.6	745.2	731.0	713.8	696.4	679.1	661.7	659.4	657.0	654.9	652.5
15°	816.3	811.8	807.3	793.6	779.8	766.1	752.4	734.0	715.4	697.0	678.6
17.5°	815.8	808.6	801.6	820.0	838.2	856.6	874.9	855.3	835.6	816.0	796.4
20°	841.2	837.1	833.0	867.0	900.8	934.8	968.6	957.9	947.0	936.3	925.4
22.5°	908.2	924.2	940.1	969.2	998.2	1027.3	1056.2	1068.5	1080.7	1092.9	1105.1
25°	978.4	1004.5	1030.6	1074.0	1117.1	1160.5	1203.8	1212.5	1221.2	1229.9	1238.6
27.5°	950.3	976.9	1003.5	1036.3	1069.0	1101.7	1134.4	1172.5	1210.8	1249.0	1287.1
30°	941.3	970.7	1000.0	1045.0	1089.9	1134.9	1179.9	1232.4	1285.0	1337.3	1389.9
32.5°	948.8	990.3	1031.8	1092.7	1153.4	1214.3	1275.3	1330.5	1385.8	1441.1	1496.3
35°	1043.4	1078.5	1113.5	1181.6	1249.7	1317.7	1385.8	1450.6	1515.3	1579.9	1644.7
37.5°	1133.5	1166.7	1199.8	1269.4	1338.8	1408.4	1478.0	1580.3	1682.7	1784.9	1887.1
40°	1262.4	1290.6	1318.8	1378.3	1437.9	1497.4	1557.0	1680.3	1803.6	1926.9	2050.2
42.5°	1409.6	1430.9	1451.9	1513.7	1575.4	1637.1	1698.9	1833.1	1967.4	2101.6	2235.8
45°	1589.8	1608.4	1626.9	1669.4	1711.9	1754.6	1797.1	1935.5	2073.8	2212.2	2350.6
47.5°	1827.7	1803.8	1779.9	1800.8	1821.7	1842.6	1863.5	2000.4	2137.2	2273.9	2410.8
50°	1979.0	1953.9	1928.8	1930.6	1932.3	1934.1	1936.0	2063.6	2191.3	2318.8	2446.4
52.5°	2180.1	2125.2	2070.5	2070.0	2069.5	2068.8	2068.3	2179.6	2291.0	2402.3	2513.5
55°	2345.0	2285.0	2224.9	2213.2	2201.5	2189.6	2177.9	2288.0	2397.9	2508.0	2617.9
57.5°	2486.4	2408.1	2330.0	2311.6	2293.2	2274.8	2256.4	2375.0	2493.8	2612.4	2731.0
60°	2549.3	2498.3	2447.4	2424.9	2402.3	2379.7	2357.1	2458.1	2559.2	2660.1	2761.1
62.5°	2517.5	2479.7	2442.1	2447.3	2452.5	2457.6	2462.8	2520.6	2578.4	2636.2	2693.9
65°	2383.5	2374.5	2365.6	2407.5	2449.3	2491.1	2532.9	2533.8	2534.6	2535.4	2536.3
67.5°	2158.3	2145.3	2132.2	2219.2	2306.1	2393.1	2480.1	2438.7	2397.4	2356.3	2314.9
70°	1803.6	1809.6	1815.5	1934.0	2052.2	2170.7	2289.2	2229.3	2169.2	2109.3	2049.2
72.5°	1379.7	1418.5	1457.1	1579.9	1702.7	1825.5	1948.3	1879.9	1811.3	1742.9	1674.3
75°	1009.2	1045.4	1081.5	1202.8	1324.1	1445.6	1566.9	1485.6	1404.2	1323.1	1241.8
77.5°	753.1	767.1	781.0	881.9	982.6	1083.5	1184.2	1102.6	1020.9	939.5	857.8
80°	600.6	590.6	580.7	636.6	692.5	748.4	804.3	746.4	688.3	630.4	572.5
82.5°	493.1	476.7	460.4	481.2	501.9	522.8	543.6	497.3	450.9	404.6	358.2
85°	351.7	344.8	338.0	344.0	349.8	355.9	361.9	316.7	271.5	226.5	181.4
87.5°	134.5	142.9	151.2	160.8	170.2	179.7	189.1	148.1	107.1	66.3	25.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P366854
 CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	363.6	363.6
2.5°	478.8	486.9
5°	584.9	584.8
7.5°	618.2	615.4
10°	589.1	581.7
12.5°	630.8	608.8
15°	656.9	634.9
17.5°	763.4	730.3
20°	886.1	846.6
22.5°	1045.0	985.0
25°	1166.8	1094.9
27.5°	1244.5	1201.6
30°	1340.8	1291.8
32.5°	1460.1	1423.8
35°	1611.5	1578.3
37.5°	1876.7	1866.2
40°	2037.7	2025.0
42.5°	2236.3	2236.6
45°	2358.1	2365.6
47.5°	2429.9	2448.8
50°	2487.1	2527.6
52.5°	2568.9	2624.3
55°	2691.5	2765.0
57.5°	2793.6	2856.2
60°	2793.6	2825.9
62.5°	2693.1	2692.0
65°	2520.7	2505.0
67.5°	2295.2	2275.4
70°	2018.5	1987.5
72.5°	1636.0	1597.5
75°	1189.1	1136.2
77.5°	832.7	807.4
80°	584.8	597.0
82.5°	375.6	393.0
85°	178.7	176.0
87.5°	21.1	16.9
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P366854
CATALOG NUMBER: PMM-SA1B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)