

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579686

Luminaire Tested: **HCC4W10D010MW-HM40525827-41MDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579686  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W10D010MW-HM40525827-41MDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 961.3 lumens  
Efficiency: N/A  
Efficacy: 97.1 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579686  
CATALOG NUMBER: HCC4W10D010MW-HM40525827-41MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P579686

CATALOG NUMBER: HCC4W10D010MW-HM40525827-41MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	86
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86	83	81	79
4	96	88	82	78	94	87	81	77	85	80	76		82	79	75		81	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76	72	69	67
6	86	76	70	66	84	76	70	65	74	69	65		73	68	64		71	67	64	62
7	81	71	65	61	80	71	65	61	69	64	60		68	63	60		67	63	60	58
8	77	67	61	56	76	66	60	56	65	60	56		64	59	56		63	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52		61	56	52		60	55	52	51
10	70	59	53	49	69	59	53	49	58	53	49		57	52	49		57	52	49	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	124468
5°	121848
10°	115153
15°	107546
20°	98367
25°	87851
30°	73763
35°	51889
40°	32010
45°	19153
50°	11283
55°	5634
60°	2886
65°	1897
70°	1190
75°	905
80°	497
85°	991



TEST NUMBER: P579686  
 CATALOG NUMBER: HCC4W10D010MW-HM40525827-41MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.9	9.6
10°-20°	235.4	24.5
20°-30°	293.6	30.5
30°-40°	216.3	22.5
40°-50°	88.9	9.3
50°-60°	26.0	2.7
60°-70°	6.7	0.7
70°-80°	2.1	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	621.0	64.6
0°-40°	837.2	87.1
0°-60°	952.1	99.0
0°-90°	961.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	961.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1009	
5°	984	92
15°	842	235
25°	646	294
35°	345	216
45°	110	89
55°	26	26
65°	6	7
75°	2	2
85°	1	0
90°	0	



TEST NUMBER: P579686  
CATALOG NUMBER: HCC4W10D010MW-HM40525827-41MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1009.1
2.5°	998.6
5°	984.1
7.5°	958.0
10°	919.4
12.5°	881.5
15°	842.2
17.5°	798.4
20°	749.4
22.5°	698.4
25°	645.5
27.5°	586.6
30°	517.9
32.5°	434.8
35°	344.6
37.5°	264.8
40°	198.8
42.5°	147.1
45°	109.8
47.5°	81.1
50°	58.8
52.5°	40.5
55°	26.2
57.5°	15.7
60°	11.7
62.5°	8.5
65°	6.5
67.5°	4.6
70°	3.3
72.5°	2.6
75°	1.9
77.5°	1.3
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)