

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579720

Luminaire Tested: **HCC4W10D010SL-HM40525835-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579720
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W10D010SL-HM40525835-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 952.3 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579720
CATALOG NUMBER: HCC4W10D010SL-HM40525835-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P579720
 CATALOG NUMBER: HCC4W10D010SL-HM40525835-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94976
5°	95067
10°	95239
15°	96641
20°	94233
25°	88409
30°	78207
35°	59463
40°	37468
45°	21526
50°	11398
55°	4731
60°	1258
65°	1051
70°	793
75°	715
80°	497
85°	991



TEST NUMBER: P579720
 CATALOG NUMBER: HCC4W10D010SL-HM40525835-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	7.7
10°-20°	211.9	22.3
20°-30°	295.7	31.1
30°-40°	243.3	25.6
40°-50°	100.3	10.5
50°-60°	22.6	2.4
60°-70°	3.6	0.4
70°-80°	1.4	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	580.7	61.0
0°-40°	824.0	86.5
0°-60°	946.8	99.4
0°-90°	952.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	952.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	770	
5°	768	73
15°	757	212
25°	650	296
35°	395	243
45°	123	100
55°	22	23
65°	4	4
75°	2	1
85°	1	0
90°	0	



TEST NUMBER: P579720
CATALOG NUMBER: HCC4W10D010SL-HM40525835-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	770.0
2.5°	766.3
5°	767.8
7.5°	764.8
10°	760.4
12.5°	758.2
15°	756.8
17.5°	743.6
20°	717.9
22.5°	685.5
25°	649.6
27.5°	606.3
30°	549.1
32.5°	478.5
35°	394.9
37.5°	310.4
40°	232.7
42.5°	169.6
45°	123.4
47.5°	88.1
50°	59.4
52.5°	37.4
55°	22.0
57.5°	11.0
60°	5.1
62.5°	4.4
65°	3.6
67.5°	3.0
70°	2.2
72.5°	1.5
75°	1.5
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)