

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579728

Luminaire Tested: **HCC4W10D010MB-HM40525835-41WDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W10D010MB-HM40525835-41WDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1246.0 lumens
Efficiency: N/A
Efficacy: 125.9 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579728
CATALOG NUMBER: HCC4W10D010MB-HM40525835-41WDC

Luminous Intensity Polar Plot





TEST NUMBER: P579728
 CATALOG NUMBER: HCC4W10D010MB-HM40525835-41WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92			92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85			85
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77			77
4	95	86	80	76	93	85	79	75	83	78	74	81	77	73	79	75	72	71			71
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65			65
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	65	61	60			60
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	57	53	73	63	57	53	62	57	53	61	56	52	60	56	52	51			51
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47			47
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100662
5°	102124
10°	105334
15°	112552
20°	119264
25°	117955
30°	105866
35°	82411
40°	55824
45°	34853
50°	15083
55°	5075
60°	1258
65°	876
70°	541
75°	334
80°	497
85°	0



TEST NUMBER: P579728
 CATALOG NUMBER: HCC4W10D010MB-HM40525835-41WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.2	6.4
10°-20°	250.2	20.1
20°-30°	392.0	31.5
30°-40°	338.4	27.2
40°-50°	155.6	12.5
50°-60°	26.4	2.1
60°-70°	3.0	0.2
70°-80°	1.1	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	721.5	57.9
0°-40°	1059.8	85.1
0°-60°	1241.9	99.7
0°-90°	1246.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1246.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	816	
5°	825	79
15°	881	250
25°	867	392
35°	547	338
45°	200	156
55°	24	26
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P579728
CATALOG NUMBER: HCC4W10D010MB-HM40525835-41WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	816.1
2.5°	816.1
5°	824.8
7.5°	832.9
10°	841.0
12.5°	857.9
15°	881.4
17.5°	901.3
20°	908.6
22.5°	897.5
25°	866.7
27.5°	816.7
30°	743.3
32.5°	650.8
35°	547.3
37.5°	442.9
40°	346.7
42.5°	265.2
45°	199.8
47.5°	140.3
50°	78.6
52.5°	43.4
55°	23.6
57.5°	11.7
60°	5.1
62.5°	3.6
65°	3.0
67.5°	2.2
70°	1.5
72.5°	1.5
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)