

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579730

Luminaire Tested: **HCC4W10D010MW-HM40525835-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579730
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W10D010MW-HM40525835-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1010.4 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579730
CATALOG NUMBER: HCC4W10D010MW-HM40525835-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P579730
 CATALOG NUMBER: HCC4W10D010MW-HM40525835-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			89	
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79	
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71	
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64	
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			58	
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			52	
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			48	
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			44	
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			41	
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			38	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88772
5°	88108
10°	85808
15°	83539
20°	79807
25°	74363
30°	65460
35°	51633
40°	37468
45°	27526
50°	22413
55°	18795
60°	17046
65°	15644
70°	14570
75°	13296
80°	11933
85°	10473



TEST NUMBER: P579730
 CATALOG NUMBER: HCC4W10D010MW-HM40525835-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.1	6.6
10°-20°	183.5	18.2
20°-30°	248.8	24.6
30°-40°	213.5	21.1
40°-50°	126.0	12.5
50°-60°	79.9	7.9
60°-70°	53.7	5.3
70°-80°	29.6	2.9
80°-90°	8.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	499.4	49.4
0°-40°	712.8	70.6
0°-60°	918.8	90.9
0°-90°	1010.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1010.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	720	
5°	712	67
15°	654	184
25°	546	249
35°	343	213
45°	158	126
55°	87	80
65°	54	54
75°	28	30
85°	7	8
90°	0	



TEST NUMBER: P579730
CATALOG NUMBER: HCC4W10D010MW-HM40525835-41NDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	719.7
2.5°	714.4
5°	711.6
7.5°	702.0
10°	685.1
12.5°	670.4
15°	654.2
17.5°	633.8
20°	608.0
22.5°	579.4
25°	546.4
27.5°	507.4
30°	459.6
32.5°	403.1
35°	342.9
37.5°	285.0
40°	232.7
42.5°	189.5
45°	157.8
47.5°	135.1
50°	116.8
52.5°	101.3
55°	87.4
57.5°	76.4
60°	69.1
62.5°	61.7
65°	53.6
67.5°	47.0
70°	40.4
72.5°	33.8
75°	27.9
77.5°	22.1
80°	16.8
82.5°	11.7
85°	7.4
87.5°	3.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)