

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592604

Luminaire Tested: **HCC4W10D010MW-HM40525850-41MDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592604
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W10D010MW-HM40525850-41MDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1109.2 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592604
CATALOG NUMBER: HCC4W10D010MW-HM40525850-41MDH

Luminous Intensity Polar Plot





TEST NUMBER: P592604

CATALOG NUMBER: HCC4W10D010MW-HM40525850-41MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86				86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79				79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67				67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62				62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58				58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54				54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51				51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	143587
5°	140594
10°	132851
15°	124083
20°	113476
25°	101338
30°	85115
35°	59869
40°	36921
45°	22119
50°	13029
55°	6494
60°	3330
65°	2189
70°	1370
75°	1096
80°	568
85°	1132



TEST NUMBER: P592604
 CATALOG NUMBER: HCC4W10D010MW-HM40525850-41MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.0	9.6
10°-20°	271.6	24.5
20°-30°	338.7	30.5
30°-40°	249.5	22.5
40°-50°	102.6	9.3
50°-60°	30.0	2.7
60°-70°	7.7	0.7
70°-80°	2.4	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	716.4	64.6
0°-40°	965.9	87.1
0°-60°	1098.5	99.0
0°-90°	1109.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1109.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1164	
5°	1136	106
15°	972	272
25°	745	339
35°	398	250
45°	127	103
55°	30	30
65°	8	8
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P592604

CATALOG NUMBER: HCC4W10D010MW-HM40525850-41MDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1164.1
2.5°	1152.0
5°	1135.5
7.5°	1105.2
10°	1060.7
12.5°	1017.0
15°	971.7
17.5°	921.2
20°	864.5
22.5°	805.7
25°	744.6
27.5°	676.8
30°	597.6
32.5°	501.7
35°	397.6
37.5°	305.6
40°	229.3
42.5°	169.8
45°	126.8
47.5°	93.5
50°	67.9
52.5°	46.8
55°	30.2
57.5°	18.1
60°	13.5
62.5°	9.8
65°	7.5
67.5°	5.2
70°	3.8
72.5°	3.1
75°	2.3
77.5°	1.5
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)