

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579774

Luminaire Tested: **HCC4W10D010SL-HM40525930-41WDBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579774  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W10D010SL-HM40525930-41WDBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 807.4 lumens  
Efficiency: N/A  
Efficacy: 81.6 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579774  
CATALOG NUMBER: HCC4W10D010SL-HM40525930-41WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P579774

CATALOG NUMBER: HCC4W10D010SL-HM40525930-41WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	80520
5°	80592
10°	80748
15°	81930
20°	79886
25°	74962
30°	66286
35°	50413
40°	31769
45°	18246
50°	9671
55°	4021
60°	1061
65°	905
70°	649
75°	620
80°	426
85°	849



TEST NUMBER: P579774  
 CATALOG NUMBER: HCC4W10D010SL-HM40525930-41WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	61.9	7.7
10°-20°	179.7	22.3
20°-30°	250.7	31.1
30°-40°	206.3	25.6
40°-50°	85.0	10.5
50°-60°	19.2	2.4
60°-70°	3.1	0.4
70°-80°	1.2	0.1
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	492.3	61.0
0°-40°	698.6	86.5
0°-60°	802.8	99.4
0°-90°	807.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	807.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	653	
5°	651	62
15°	642	180
25°	551	251
35°	335	206
45°	105	85
55°	19	19
65°	3	3
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P579774  
CATALOG NUMBER: HCC4W10D010SL-HM40525930-41WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	652.8
2.5°	649.7
5°	650.9
7.5°	648.4
10°	644.7
12.5°	642.9
15°	641.6
17.5°	630.5
20°	608.6
22.5°	581.3
25°	550.8
27.5°	514.0
30°	465.4
32.5°	405.7
35°	334.8
37.5°	263.2
40°	197.3
42.5°	143.7
45°	104.6
47.5°	74.7
50°	50.4
52.5°	31.8
55°	18.7
57.5°	9.3
60°	4.3
62.5°	3.8
65°	3.1
67.5°	2.5
70°	1.8
72.5°	1.3
75°	1.3
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)