

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579786

Luminaire Tested: **HCC4S10D010SL-HM40525930-41WDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579786  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S10D010SL-HM40525930-41WDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 927.5 lumens  
Efficiency: N/A  
Efficacy: 93.7 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579786  
CATALOG NUMBER: HCC4S10D010SL-HM40525930-41WDW

### Luminous Intensity Polar Plot





TEST NUMBER: P579786

CATALOG NUMBER: HCC4S10D010SL-HM40525930-41WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69								
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62								
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56								
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51								
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46								
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42								
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39								
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	74155	74155	74155
5°	73968	74042	74042
10°	73120	73195	73120
15°	72238	72238	72238
20°	69267	69424	69516
25°	64782	64877	65054
30°	58053	58239	58239
35°	47146	47522	47597
40°	35568	35762	35874
45°	27247	27142	27142
50°	22451	22336	22336
55°	19268	19139	19139
60°	17170	17046	17046
65°	16169	16169	16169
70°	15039	15039	15039
75°	13678	13916	13678
80°	12857	12360	12857
85°	10614	10614	10614



TEST NUMBER: P579786  
 CATALOG NUMBER: HCC4S10D010SL-HM40525930-41WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.6	6.1
10°-20°	158.5	17.1
20°-30°	217.8	23.5
30°-40°	195.9	21.1
40°-50°	123.7	13.3
50°-60°	80.8	8.7
60°-70°	54.7	5.9
70°-80°	30.8	3.3
80°-90°	8.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	433.0	46.7
0°-40°	628.8	67.8
0°-60°	833.4	89.8
0°-90°	927.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	927.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	601	601	601	601	601	
5°	597	597	598	598	598	57
15°	566	566	566	566	566	158
25°	476	477	477	478	478	217
35°	313	314	316	317	316	195
45°	156	156	156	156	156	124
55°	90	90	89	90	89	81
65°	55	55	55	55	55	55
75°	29	29	29	29	29	31
85°	8	8	8	8	8	9
90°	0	0	0	0	0	



TEST NUMBER: P579786

CATALOG NUMBER: HCC4S10D010SL-HM40525930-41WDW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	601.2	601.2	601.2	601.2	601.2
2.5°	598.0	598.0	598.0	598.0	598.0
5°	597.4	597.4	598.0	598.0	598.0
7.5°	593.1	593.7	593.7	593.7	593.7
10°	583.8	583.8	584.4	584.4	583.8
12.5°	575.0	575.0	575.0	575.6	575.0
15°	565.7	565.7	565.7	565.7	565.7
17.5°	549.5	550.1	550.1	550.1	550.1
20°	527.7	528.9	528.9	529.6	529.6
22.5°	502.9	503.5	504.1	504.7	504.1
25°	476.0	476.7	476.7	478.0	478.0
27.5°	445.0	445.6	446.8	446.8	446.8
30°	407.6	408.2	408.9	408.9	408.9
32.5°	363.5	363.5	364.7	365.3	364.7
35°	313.1	314.3	315.6	316.8	316.1
37.5°	265.2	266.4	267.0	267.0	267.7
40°	220.9	222.1	222.1	223.4	222.8
42.5°	186.1	185.5	185.5	186.7	186.1
45°	156.2	155.6	155.6	155.6	155.6
47.5°	134.4	133.8	133.8	133.8	133.8
50°	117.0	116.4	116.4	116.4	116.4
52.5°	102.6	102.1	102.1	102.1	101.4
55°	89.6	89.6	89.0	89.6	89.0
57.5°	77.8	77.8	77.8	77.8	77.8
60°	69.6	69.1	69.1	69.1	69.1
62.5°	62.2	62.2	62.2	62.2	62.2
65°	55.4	55.4	55.4	55.4	55.4
67.5°	48.6	47.9	48.6	48.6	47.9
70°	41.7	41.1	41.7	41.7	41.7
72.5°	34.8	34.8	34.8	35.5	34.8
75°	28.7	29.2	29.2	29.2	28.7
77.5°	23.0	23.7	23.0	23.0	23.0
80°	18.1	17.4	17.4	17.4	18.1
82.5°	12.4	12.4	12.4	12.4	12.4
85°	7.5	7.5	7.5	7.5	7.5
87.5°	3.1	3.1	3.1	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)