

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579785

Luminaire Tested: **HCC4W10D010MB-HM40525930-41PSMDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579785
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W10D010MB-HM40525930-41PSMDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 880.2 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579785
CATALOG NUMBER: HCC4W10D010MB-HM40525930-41PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P579785
 CATALOG NUMBER: HCC4W10D010MB-HM40525930-41PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89		
2	103	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78		
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70		
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63		
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44		
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40		
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76462
5°	75974
10°	74360
15°	72723
20°	69359
25°	64197
30°	55831
35°	42177
40°	30561
45°	23880
50°	20417
55°	17677
60°	16282
65°	14885
70°	13921
75°	12724
80°	11933
85°	11463



TEST NUMBER: P579785
 CATALOG NUMBER: HCC4W10D010MB-HM40525930-41PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.0	6.6
10°-20°	159.5	18.1
20°-30°	214.5	24.4
30°-40°	176.4	20.0
40°-50°	108.3	12.3
50°-60°	75.0	8.5
60°-70°	51.1	5.8
70°-80°	28.5	3.2
80°-90°	9.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	431.9	49.1
0°-40°	608.3	69.1
0°-60°	791.6	89.9
0°-90°	880.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	880.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	620	
5°	614	58
15°	570	160
25°	472	214
35°	280	176
45°	137	108
55°	82	75
65°	51	51
75°	27	28
85°	8	9
90°	0	



TEST NUMBER: P579785
CATALOG NUMBER: HCC4W10D010MB-HM40525930-41PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	619.9
2.5°	615.5
5°	613.6
7.5°	606.8
10°	593.7
12.5°	581.9
15°	569.5
17.5°	551.4
20°	528.4
22.5°	500.9
25°	471.7
27.5°	436.3
30°	392.0
32.5°	338.0
35°	280.1
37.5°	230.2
40°	189.8
42.5°	158.8
45°	136.9
47.5°	120.1
50°	106.4
52.5°	94.0
55°	82.2
57.5°	73.4
60°	66.0
62.5°	58.5
65°	51.0
67.5°	44.8
70°	38.6
72.5°	32.3
75°	26.7
77.5°	21.2
80°	16.8
82.5°	12.4
85°	8.1
87.5°	4.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)