

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579792

Luminaire Tested: **HCC4W10D010MW-HM40525935-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W10D010MW-HM40525935-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 850.6 lumens
Efficiency: N/A
Efficacy: 85.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579792
CATALOG NUMBER: HCC4W10D010MW-HM40525935-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P579792
 CATALOG NUMBER: HCC4W10D010MW-HM40525935-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80	76	73	72
5	90	81	74	70	88	80	74	70	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66	61	58	56
8	76	65	59	55	74	65	59	54	64	58	54		63	58	54		62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58	53	50	49
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55	50	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84825
5°	84889
10°	85069
15°	86310
20°	84152
25°	78963
30°	69846
35°	53109
40°	33459
45°	19223
50°	10189
55°	4236
60°	1135
65°	963
70°	685
75°	667
80°	497
85°	991



TEST NUMBER: P579792
 CATALOG NUMBER: HCC4W10D010MW-HM40525935-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.2	7.7
10°-20°	189.2	22.2
20°-30°	264.1	31.0
30°-40°	217.3	25.6
40°-50°	89.5	10.5
50°-60°	20.2	2.4
60°-70°	3.2	0.4
70°-80°	1.3	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	518.6	61.0
0°-40°	735.9	86.5
0°-60°	845.6	99.4
0°-90°	850.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	850.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	688	
5°	686	65
15°	676	189
25°	580	264
35°	353	217
45°	110	90
55°	20	20
65°	3	3
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P579792
CATALOG NUMBER: HCC4W10D010MW-HM40525935-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	687.7
2.5°	684.4
5°	685.6
7.5°	683.0
10°	679.2
12.5°	677.1
15°	675.9
17.5°	664.0
20°	641.1
22.5°	612.2
25°	580.2
27.5°	541.5
30°	490.4
32.5°	427.4
35°	352.7
37.5°	277.3
40°	207.8
42.5°	151.5
45°	110.2
47.5°	78.6
50°	53.1
52.5°	33.5
55°	19.7
57.5°	9.8
60°	4.6
62.5°	4.0
65°	3.3
67.5°	2.6
70°	1.9
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)