

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579801

Luminaire Tested: **HCC4W10D010MB-HM40525935-41MDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579801  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W10D010MB-HM40525935-41MDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 946.9 lumens  
Efficiency: N/A  
Efficacy: 95.6 lumens/watt  
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579801  
CATALOG NUMBER: HCC4W10D010MB-HM40525935-41MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P579801  
 CATALOG NUMBER: HCC4W10D010MB-HM40525935-41MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	80273
5°	79849
10°	78393
15°	76746
20°	73467
25°	68307
30°	60460
35°	47718
40°	35713
45°	27474
50°	22279
55°	18472
60°	16331
65°	15118
70°	13957
75°	12820
80°	11649
85°	9341



TEST NUMBER: P579801  
 CATALOG NUMBER: HCC4W10D010MB-HM40525935-41MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	61.0	6.4
10°-20°	168.5	17.8
20°-30°	228.8	24.2
30°-40°	198.2	20.9
40°-50°	124.5	13.1
50°-60°	78.3	8.3
60°-70°	51.4	5.4
70°-80°	28.3	3.0
80°-90°	7.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	458.3	48.4
0°-40°	656.6	69.3
0°-60°	859.3	90.8
0°-90°	946.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	946.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	651	
5°	645	61
15°	601	169
25°	502	229
35°	317	198
45°	158	124
55°	86	78
65°	52	51
75°	27	28
85°	7	8
90°	0	



TEST NUMBER: P579801  
CATALOG NUMBER: HCC4W10D010MB-HM40525935-41MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	650.8
2.5°	646.8
5°	644.9
7.5°	638.3
10°	625.9
12.5°	613.4
15°	601.0
17.5°	583.9
20°	559.7
22.5°	532.0
25°	501.9
27.5°	467.1
30°	424.5
32.5°	372.7
35°	316.9
37.5°	265.7
40°	221.8
42.5°	187.0
45°	157.5
47.5°	135.2
50°	116.1
52.5°	99.7
55°	85.9
57.5°	74.1
60°	66.2
62.5°	59.1
65°	51.8
67.5°	44.6
70°	38.7
72.5°	32.1
75°	26.9
77.5°	20.9
80°	16.4
82.5°	11.2
85°	6.6
87.5°	2.6
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)