

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579810

Luminaire Tested: **HCC4W10D010MB-HM40525940-41WDBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579810  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W10D010MB-HM40525940-41WDBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 881.3 lumens  
Efficiency: N/A  
Efficacy: 89.0 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579810  
CATALOG NUMBER: HCC4W10D010MB-HM40525940-41WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P579810  
 CATALOG NUMBER: HCC4W10D010MB-HM40525940-41WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	87884
5°	87972
10°	88137
15°	89426
20°	87197
25°	81808
30°	72367
35°	55021
40°	34667
45°	19903
50°	10554
55°	4387
60°	1184
65°	992
70°	721
75°	667
80°	497
85°	991



TEST NUMBER: P579810  
 CATALOG NUMBER: HCC4W10D010MB-HM40525940-41WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.6	7.7
10°-20°	196.1	22.3
20°-30°	273.7	31.1
30°-40°	225.2	25.6
40°-50°	92.8	10.5
50°-60°	20.9	2.4
60°-70°	3.4	0.4
70°-80°	1.3	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	537.3	61.0
0°-40°	762.5	86.5
0°-60°	876.2	99.4
0°-90°	881.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	881.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	712	
5°	710	68
15°	700	196
25°	601	274
35°	365	225
45°	114	93
55°	20	21
65°	3	3
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P579810  
CATALOG NUMBER: HCC4W10D010MB-HM40525940-41WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	712.5
2.5°	709.1
5°	710.5
7.5°	707.7
10°	703.7
12.5°	701.7
15°	700.3
17.5°	688.0
20°	664.3
22.5°	634.4
25°	601.1
27.5°	561.0
30°	508.1
32.5°	442.9
35°	365.4
37.5°	287.3
40°	215.3
42.5°	156.9
45°	114.1
47.5°	81.5
50°	55.0
52.5°	34.6
55°	20.4
57.5°	10.2
60°	4.8
62.5°	4.1
65°	3.4
67.5°	2.7
70°	2.0
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)