

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579812

Luminaire Tested: **HCC4S10D010BZ-HM40525940-41MDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579812
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S10D010BZ-HM40525940-41MDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 998.8 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579812
CATALOG NUMBER: HCC4S10D010BZ-HM40525940-41MDH

Luminous Intensity Polar Plot





TEST NUMBER: P579812
 CATALOG NUMBER: HCC4S10D010BZ-HM40525940-41MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86			86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79			79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67			67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62			62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58			58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54			54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51			51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47			47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	129303
5°	126603
10°	119637
15°	111735
20°	102200
25°	91253
30°	76626
35°	53907
40°	33250
45°	19903
50°	11725
55°	5849
60°	3010
65°	1985
70°	1226
75°	953
80°	497
85°	991



TEST NUMBER: P579812
 CATALOG NUMBER: HCC4S10D010BZ-HM40525940-41MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	9.6
10°-20°	244.6	24.5
20°-30°	305.0	30.5
30°-40°	224.7	22.5
40°-50°	92.4	9.2
50°-60°	27.0	2.7
60°-70°	7.0	0.7
70°-80°	2.1	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	645.1	64.6
0°-40°	869.8	87.1
0°-60°	989.2	99.0
0°-90°	998.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	998.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1048	
5°	1022	95
15°	875	245
25°	670	305
35°	358	225
45°	114	92
55°	27	27
65°	7	7
75°	2	2
85°	1	0
90°	0	



TEST NUMBER: P579812
CATALOG NUMBER: HCC4S10D010BZ-HM40525940-41MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1048.3
2.5°	1037.4
5°	1022.5
7.5°	995.3
10°	955.2
12.5°	915.9
15°	875.0
17.5°	829.5
20°	778.6
22.5°	725.6
25°	670.5
27.5°	609.4
30°	538.0
32.5°	451.8
35°	358.0
37.5°	275.2
40°	206.5
42.5°	152.8
45°	114.1
47.5°	84.2
50°	61.1
52.5°	42.1
55°	27.2
57.5°	16.3
60°	12.2
62.5°	8.9
65°	6.8
67.5°	4.8
70°	3.4
72.5°	2.7
75°	2.0
77.5°	1.4
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)