

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579830

Luminaire Tested: **HCC4W15D010SL-HM40525827-41MDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579830  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W15D010SL-HM40525827-41MDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1307.1 lumens  
Efficiency: N/A  
Efficacy: 93.4 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579830  
CATALOG NUMBER: HCC4W15D010SL-HM40525827-41MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P579830  
 CATALOG NUMBER: HCC4W15D010SL-HM40525827-41MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	169218
5°	165679
10°	156573
15°	146238
20°	133756
25°	119425
30°	100283
35°	70560
40°	43523
45°	26061
50°	15351
55°	7656
60°	3947
65°	2598
70°	1587
75°	1239
80°	639
85°	1274



TEST NUMBER: P579830  
 CATALOG NUMBER: HCC4W15D010SL-HM40525827-41MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.0	9.6
10°-20°	320.1	24.5
20°-30°	399.2	30.5
30°-40°	294.1	22.5
40°-50°	120.9	9.3
50°-60°	35.3	2.7
60°-70°	9.1	0.7
70°-80°	2.8	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	844.3	64.6
0°-40°	1138.3	87.1
0°-60°	1294.6	99.0
0°-90°	1307.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1307.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1372	
5°	1338	125
15°	1145	320
25°	878	399
35°	469	294
45°	149	121
55°	36	35
65°	9	9
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P579830  
CATALOG NUMBER: HCC4W15D010SL-HM40525827-41MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1371.9
2.5°	1357.7
5°	1338.1
7.5°	1302.5
10°	1250.1
12.5°	1198.5
15°	1145.2
17.5°	1085.6
20°	1019.0
22.5°	949.6
25°	877.5
27.5°	797.5
30°	704.1
32.5°	591.2
35°	468.6
37.5°	360.1
40°	270.3
42.5°	200.0
45°	149.4
47.5°	110.3
50°	80.0
52.5°	55.1
55°	35.6
57.5°	21.4
60°	16.0
62.5°	11.6
65°	8.9
67.5°	6.3
70°	4.4
72.5°	3.5
75°	2.6
77.5°	1.8
80°	0.9
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)