

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579829

Luminaire Tested: **HCC4W15D010SL-HM40525827-41WDWB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579829  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W15D010SL-HM40525827-41WDWB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1435.2 lumens  
Efficiency: N/A  
Efficacy: 102.5 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579829  
CATALOG NUMBER: HCC4W15D010SL-HM40525827-41WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P579829

CATALOG NUMBER: HCC4W15D010SL-HM40525827-41WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90		
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80		
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72		
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65		
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59		
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54		
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49		
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46		
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42		
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	117820
5°	118381
10°	119199
15°	120393
20°	118385
25°	112933
30°	102605
35°	82757
40°	57435
45°	37696
50°	25272
55°	17978
60°	15369
65°	17658
70°	18934
75°	18205
80°	16408
85°	15143



TEST NUMBER: P579829  
 CATALOG NUMBER: HCC4W15D010SL-HM40525827-41WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.1	6.3
10°-20°	264.8	18.5
20°-30°	378.4	26.4
30°-40°	338.0	23.6
40°-50°	173.4	12.1
50°-60°	78.8	5.5
60°-70°	58.8	4.1
70°-80°	40.0	2.8
80°-90°	11.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	734.4	51.2
0°-40°	1072.4	74.7
0°-60°	1324.6	92.3
0°-90°	1435.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1435.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	955	
5°	956	91
15°	943	265
25°	830	378
35°	550	338
45°	216	173
55°	84	79
65°	60	59
75°	38	40
85°	11	12
90°	0	



TEST NUMBER: P579829

CATALOG NUMBER: HCC4W15D010SL-HM40525827-41WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	955.2
2.5°	951.7
5°	956.1
7.5°	956.1
10°	951.7
12.5°	947.2
15°	942.8
17.5°	929.4
20°	901.9
22.5°	868.1
25°	829.8
27.5°	781.8
30°	720.4
32.5°	642.2
35°	549.6
37.5°	450.9
40°	356.7
42.5°	278.3
45°	216.1
47.5°	169.0
50°	131.7
52.5°	103.1
55°	83.6
57.5°	70.3
60°	62.3
62.5°	60.5
65°	60.5
67.5°	58.7
70°	52.5
72.5°	45.4
75°	38.2
77.5°	30.2
80°	23.1
82.5°	16.9
85°	10.7
87.5°	4.4
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)