

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579876

Luminaire Tested: **HCC4W15D010SL-HM40525835-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579876
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W15D010SL-HM40525835-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1487.5 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579876
CATALOG NUMBER: HCC4W15D010SL-HM40525835-41WDW

Luminous Intensity Polar Plot





TEST NUMBER: P579876

CATALOG NUMBER: HCC4W15D010SL-HM40525835-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			89
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			78
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			69
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62			62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			56
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			51
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39			39
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36			36

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	118918	118918	118918
5°	118616	118753	118753
10°	117245	117370	117245
15°	115847	115847	115847
20°	111087	111349	111481
25°	103910	104046	104318
30°	93105	93390	93390
35°	75590	76192	76343
40°	57048	57370	57515
45°	43696	43522	43522
50°	35999	35807	35807
55°	30902	30687	30687
60°	27580	27309	27309
65°	25917	25917	25917
70°	24127	24127	24127
75°	21875	22399	21875
80°	20599	19889	20599
85°	16841	16841	16841



TEST NUMBER: P579876
 CATALOG NUMBER: HCC4W15D010SL-HM40525835-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.8	6.1
10°-20°	254.2	17.1
20°-30°	349.3	23.5
30°-40°	314.1	21.1
40°-50°	198.4	13.3
50°-60°	129.5	8.7
60°-70°	87.8	5.9
70°-80°	49.5	3.3
80°-90°	13.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	694.3	46.7
0°-40°	1008.4	67.8
0°-60°	1336.4	89.8
0°-90°	1487.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1487.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	964	964	964	964	964	
5°	958	958	959	959	959	91
15°	907	907	907	907	907	254
25°	764	764	764	766	766	348
35°	502	504	506	508	507	313
45°	250	250	250	250	250	199
55°	144	144	143	144	143	130
65°	89	89	89	89	89	88
75°	46	47	47	47	46	49
85°	12	12	12	12	12	14
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579876

CATALOG NUMBER: HCC4W15D010SL-HM40525835-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	964.1	964.1	964.1	964.1	964.1
2.5°	959.1	959.1	959.1	959.1	959.1
5°	958.0	958.0	959.1	959.1	959.1
7.5°	951.1	952.1	952.1	952.1	952.1
10°	936.1	936.1	937.1	937.1	936.1
12.5°	922.1	922.1	922.1	923.1	922.1
15°	907.2	907.2	907.2	907.2	907.2
17.5°	881.3	882.2	882.2	882.2	882.2
20°	846.3	848.3	848.3	849.3	849.3
22.5°	806.4	807.4	808.4	809.4	808.4
25°	763.5	764.5	764.5	766.5	766.5
27.5°	713.6	714.6	716.5	716.5	716.5
30°	653.7	654.7	655.7	655.7	655.7
32.5°	582.8	582.8	584.9	585.8	584.9
35°	502.0	504.0	506.0	508.0	507.0
37.5°	425.1	427.2	428.2	428.2	429.1
40°	354.3	356.3	356.3	358.3	357.2
42.5°	298.3	297.4	297.4	299.4	298.3
45°	250.5	249.5	249.5	249.5	249.5
47.5°	215.6	214.6	214.6	214.6	214.6
50°	187.6	186.6	186.6	186.6	186.6
52.5°	164.6	163.7	163.7	163.7	162.7
55°	143.7	143.7	142.7	143.7	142.7
57.5°	124.7	124.7	124.7	124.7	124.7
60°	111.8	110.7	110.7	110.7	110.7
62.5°	99.8	99.8	99.8	99.8	99.8
65°	88.8	88.8	88.8	88.8	88.8
67.5°	77.9	76.9	77.9	77.9	76.9
70°	66.9	65.8	66.9	66.9	66.9
72.5°	55.9	55.9	55.9	56.8	55.9
75°	45.9	47.0	47.0	47.0	45.9
77.5°	37.0	38.0	37.0	37.0	37.0
80°	29.0	28.0	28.0	28.0	29.0
82.5°	20.0	20.0	20.0	20.0	20.0
85°	11.9	11.9	11.9	11.9	11.9
87.5°	5.0	5.0	5.0	5.0	5.0
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)