

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579882

Luminaire Tested: **HCC4S15D010MB-HM40525840-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579882
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S15D010MB-HM40525840-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1330.5 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579882
CATALOG NUMBER: HCC4S15D010MB-HM40525840-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P579882
 CATALOG NUMBER: HCC4S15D010MB-HM40525840-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132695
5°	132831
10°	133064
15°	135014
20°	131642
25°	123521
30°	109256
35°	83089
40°	52346
45°	30056
50°	15946
55°	6623
60°	1776
65°	1488
70°	1118
75°	953
80°	710
85°	1415



TEST NUMBER: P579882
 CATALOG NUMBER: HCC4S15D010MB-HM40525840-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.0	7.7
10°-20°	296.1	22.3
20°-30°	413.2	31.1
30°-40°	340.0	25.6
40°-50°	140.1	10.5
50°-60°	31.5	2.4
60°-70°	5.0	0.4
70°-80°	1.9	0.1
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	811.3	61.0
0°-40°	1151.3	86.5
0°-60°	1322.9	99.4
0°-90°	1330.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1330.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1076	
5°	1073	102
15°	1057	296
25°	908	413
35°	552	340
45°	172	140
55°	31	32
65°	5	5
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P579882
CATALOG NUMBER: HCC4S15D010MB-HM40525840-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1075.8
2.5°	1070.7
5°	1072.8
7.5°	1068.7
10°	1062.4
12.5°	1059.3
15°	1057.3
17.5°	1038.9
20°	1002.9
22.5°	957.8
25°	907.6
27.5°	847.1
30°	767.1
32.5°	668.7
35°	551.8
37.5°	433.8
40°	325.1
42.5°	237.0
45°	172.3
47.5°	123.0
50°	83.1
52.5°	52.3
55°	30.8
57.5°	15.3
60°	7.2
62.5°	6.1
65°	5.1
67.5°	4.1
70°	3.1
72.5°	2.0
75°	2.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)