

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592631

Luminaire Tested: **HCC4S15D010SL-HM40525850-41PSMDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592631
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S15D010SL-HM40525850-41PSMDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1450.5 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592631
CATALOG NUMBER: HCC4S15D010SL-HM40525850-41PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P592631
 CATALOG NUMBER: HCC4S15D010SL-HM40525850-41PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89		
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78		
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70		
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63		
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44		
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40		
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125998
5°	125204
10°	122543
15°	119831
20°	114290
25°	105802
30°	92036
35°	69491
40°	50366
45°	39353
50°	33639
55°	29117
60°	26815
65°	24545
70°	22937
75°	21017
80°	19676
85°	18823



TEST NUMBER: P592631
 CATALOG NUMBER: HCC4S15D010SL-HM40525850-41PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	6.6
10°-20°	262.9	18.1
20°-30°	353.5	24.4
30°-40°	290.6	20.0
40°-50°	178.5	12.3
50°-60°	123.5	8.5
60°-70°	84.2	5.8
70°-80°	46.9	3.2
80°-90°	14.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	711.8	49.1
0°-40°	1002.5	69.1
0°-60°	1304.5	89.9
0°-90°	1450.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1450.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1022	
5°	1011	96
15°	938	263
25°	777	353
35°	462	291
45°	226	178
55°	135	124
65°	84	84
75°	44	47
85°	13	15
90°	0	



TEST NUMBER: P592631
CATALOG NUMBER: HCC4S15D010SL-HM40525850-41PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1021.5
2.5°	1014.3
5°	1011.2
7.5°	1000.0
10°	978.4
12.5°	958.9
15°	938.4
17.5°	908.7
20°	870.7
22.5°	825.6
25°	777.4
27.5°	718.9
30°	646.2
32.5°	556.9
35°	461.5
37.5°	379.4
40°	312.8
42.5°	261.5
45°	225.6
47.5°	198.0
50°	175.3
52.5°	154.9
55°	135.4
57.5°	121.0
60°	108.7
62.5°	96.4
65°	84.1
67.5°	73.8
70°	63.6
72.5°	53.3
75°	44.1
77.5°	34.9
80°	27.7
82.5°	20.5
85°	13.3
87.5°	7.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)